


Common Mode Choke

TCK-096


Order Code	TCK-096
Inductance (each winding)	160 μH ±35% (at 100 kHz / 100 mV)
Impedance (DCR)	7 mΩ max.
Rated Current	7.84 A max.
Rated Voltage	500 VDC max. (between windings)
Operating Temperature	-40°C to +105°C
RoHS Exemptions	No Exemptions



Impedance Curve




Outline Dimensions



Dimensions [mm]	
Α	12.5 max.
В	12.5 max.
С	10.7 max.
D	2.5 min
E	7.62 ±0.2
F	7.62 ±0.2
G	ø 0.6 ±0.1

All specifications valid at +25°C, unless otherwise stated.



Specifications can be changed without notice.