


Common Mode Choke

TCK-103


Order Code	TCK-103
Inductance (each winding)	285 μH ±35% (100 kHz / 100 mV)
Impedance (DCR)	6 mΩ max.
Rated Current	16 A max.
Rated Voltage	500 VDC max. (between windings)
Operating Temperature	-40°C to +105°C
RoHS Exemptions	No Exemptions



Impedance Curve




Outline Dimensions



Dimensions [mm]	
Α	16.0 max.
В	16.0 max.
С	15 max.
D	3.6±0.3
E	10.0 ±0.3
F	7.4 ±0.3
G	ø 0.8

All specifications valid at +25°C, unless otherwise stated.



Specifications can be changed without notice.