



Order Code	TCK-191
Inductance	1 $\mu$ H $\pm$ 20% (at 100 kHz / 1 V)
Impedance (DCR)	3 m $\Omega$ max.
Rated Current	19 A max.
Operating Temperature	-40°C to +125°C
RoHS Exemptions	No Exemptions




Impedance Curve



Outline Dimensions



PCB PATTERN



Dimensions [mm]	
A	10.0 $\pm$ 0.5
B	10.0 $\pm$ 0.5
C	4.2 max.
D	11.7 max.
E	2.0 $\pm$ 0.7
F	3.0 $\pm$ 0.7
G	5.4
H	13.6
I	4.1

All specifications valid at +25°C, unless otherwise stated.