



Characteristic Curves - Output Derating vs. Ambient Temperature


THL 15-2410WI without Heat-Sink




THL 15-2410WI with Heat-Sink




THL 15-2411WI without Heat-Sink




THL 15-2411WI with Heat-Sink




THL 15-2412WI without Heat-Sink




THL 15-2412WI with Heat-Sink




THL 15-2413WI without Heat-Sink




THL 15-2413WI with Heat-Sink




THL 15-2415WI without Heat-Sink




THL 15-2415WI with Heat-Sink




THL 15-2422WI without Heat-Sink




THL 15-2422WI with Heat-Sink




THL 15-2423WI without Heat-Sink




THL 15-2423WI with Heat-Sink



THL 15-4810WI without Heat-Sink




THL 15-4810WI with Heat-Sink




All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.


THL 15-4811WI without Heat-Sink




THL 15-4811WI with Heat-Sink




THL 15-4812WI without Heat-Sink




THL 15-4812WI with Heat-Sink




THL 15-4813WI without Heat-Sink




THL 15-4813WI with Heat-Sink



THL 15-4815WI without Heat-Sink




THL 15-4815WI with Heat-Sink




All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.


THL 15-4822WI without Heat-Sink



THL 15-4822WI with Heat-Sink



THL 15-4823WI without Heat-Sink



THL 15-4823WI with Heat-Sink

