



Output Voltage Adjustment

Output voltage set point adjustment allows the user to increase or decrease the output voltage set point of the single output module. This is accomplished by connecting an external resistor between the Trim pin and either the +Vout or -Vout pins. With an external resistor between the Trim and -Vout pin, the output voltage set point increases. With an external resistor between the Trim and +Vout pin, the output voltage set point decreases.

Connection of trim up resistor



Connection of trim down resistor



Trim-Tables for single output converters

TEN 40-xx10N & TEN 40-xx10WIN										
Trim-Up										
	1 %	2 %	3 %	4 %	5 %	6 %	7 %	8 %	9 %	10 %
Vout [V]	3.333	3.366	3.399	3.432	3.465	3.498	3.531	3.564	3.597	3.630
R_u [kOhm]	60.84	27.40	16.25	10.68	7.34	5.11	3.51	2.32	1.39	0.65
Trim-Down										
	1 %	2 %	3 %	4 %	5 %	6 %	7 %	8 %	9 %	10 %
Vout [V]	3.267	3.234	3.201	3.168	3.135	3.102	3.069	3.036	3.003	2.970
R_p [kOhm]	72.61	32.55	19.20	12.52	8.51	5.84	3.94	2.51	1.39	0.50

TEN 40-xx11N & TEN 40-xx11WIN										
Trim-Up										
	1 %	2 %	3 %	4 %	5 %	6 %	7 %	8 %	9 %	10 %
Vout [V]	5.05	5.10	5.15	5.20	5.25	5.30	5.35	5.40	5.45	5.50
R_u [kOhm]	106.87	47.76	28.06	18.21	12.30	8.36	5.55	3.44	1.79	0.48
Trim-Down										
	1 %	2 %	3 %	4 %	5 %	6 %	7 %	8 %	9 %	10 %
Vout [V]	4.95	4.90	4.85	4.80	4.75	4.70	4.65	4.60	4.55	4.50
R_p [kOhm]	138.88	62.41	36.92	24.18	16.53	11.44	7.79	5.06	2.94	1.24

Trim-Tables for single output converters (continued)

TEN 40-xx12N & TEN 40-xx12WIN										
Trim-Up										
	1 %	2 %	3 %	4 %	5 %	6 %	7 %	8 %	9 %	10 %
V_{out} [V]	12.12	12.24	12.36	12.48	12.60	12.72	12.84	12.96	13.08	13.20
R_U [kOhm]	351.00	157.50	93.00	60.75	41.40	28.50	19.29	12.37	7.00	2.70
Trim-Down										
	1 %	2 %	3 %	4 %	5 %	6 %	7 %	8 %	9 %	10 %
V_{out} [V]	11.88	11.76	11.64	11.52	11.40	11.28	11.16	11.04	10.92	10.80
R_D [kOhm]	413.55	184.55	108.22	70.05	47.15	31.88	20.98	12.80	6.44	1.35

TEN 40-xx13N & TEN 40-xx13WIN										
Trim-Up										
	1 %	2 %	3 %	4 %	5 %	6 %	7 %	8 %	9 %	10 %
V_{out} [V]	15.15	15.30	15.45	15.60	15.75	15.90	16.05	16.20	16.35	16.50
R_U [kOhm]	422.77	189.89	112.26	73.44	50.15	34.63	23.54	15.22	8.75	3.58
Trim-Down										
	1 %	2 %	3 %	4 %	5 %	6 %	7 %	8 %	9 %	10 %
V_{out} [V]	14.85	14.70	14.55	14.40	14.25	14.10	13.95	13.80	13.65	13.50
R_D [kOhm]	530.73	238.61	141.24	92.56	63.35	43.87	29.96	19.53	11.41	4.92

TEN 40-xx15N & TEN 40-xx15WIN										
Trim-Up										
	2 %	4 %	6 %	8 %	10 %	12 %	14 %	16 %	18 %	20 %
V_{out} [V]	24.48	24.96	25.44	25.92	26.40	26.88	27.36	27.84	28.32	28.80
R_U [kOhm]	243.70	108.50	63.43	40.90	27.38	18.37	11.93	7.10	3.34	0.34
Trim-Down										
	1 %	2 %	3 %	4 %	5 %	6 %	7 %	8 %	9 %	10 %
V_{out} [V]	23.76	23.52	23.28	23.04	22.80	22.56	22.32	22.08	21.84	21.60
R_D [kOhm]	333.39	148.80	87.26	56.50	38.04	25.73	16.94	10.35	5.22	1.12