

INSTALLATION INSTRUCTIONS

TML 100 Series Switching Power Supply

Order Code	Output Power max.	Output 1
TML 100-112C	85 Watt	12Vdc / 7080mA
TML 100-115C	85 Watt	15Vdc / 5660mA
TML 100-124C	100 Watt	24Vdc / 4200mA
TML 100-148C	100 Watt	48Vdc / 2100mA

The product is also available as PCB mount version (without "C" in the order code).

Total output power must not exceed specified max output power. Check min. load requirements in the datasheet.

Input Voltage Range:	90 – 264Vac / 47 – 63Hz 120 – 370Vdc	Case Temp.	+95°C max.
Input current:	<2A typ at Vin = 115Vac <1A typ at Vin = 230Vac	Load Derating:	above +50°C of 3.75%/°K
Output voltage accuracy	±2.0%	Terminal for wiring:	Screw type terminal: Wires 2.05mm ² max Recommended tightening torque 0.29Nm (2.6lb.in.)
Operating temperature range:	-25°C - +70°C max	Case material:	Plastic Resin + Fiberglass UL 94V-0 flammability rating

Safety Instructions:

- Before installation read these instructions carefully and completely. This installation instruction cannot claim for every possible example of installation, operation or maintenance. Further information's are obtainable from your local distributor office or from the product data sheet which can be downloaded from the Internet at <http://tracopower.com>.
- The power supplies are constructed in accordance with the safety requirements of IEC/EN/UL62368-1. They fulfil the requirements of the Low Voltage Directive (LVD) and carries the CE-mark. They are UL and cUL approved in accordance with UL62368-1 (recognised).
- Before any installation, maintenance or modification work ensure that the main switch is switched off and prevented from being switched on again. In case of non-observance touching at any alive components or improper dealing with this power supply can result in death, severe personal injury or substantial property damage. The successful and safe operation is dependent on proper storage, handling, installation and operation.
- Compliance with the relevant national regulations (in the USA, Europe and the other countries) must be ensured. Before operation is started the following conditions must be ensured:
 - ❖ Connection to mains supply in compliance with national regulations (VDE0100 and EN50178).
 - ❖ By use of stranded wires, all strands must be fastened in the terminal blocks.
 - ❖ Power supply and mains cables must be sufficiently fused.
 - ❖ All output wires must be rated for the power supply output current and must be connected with the correct polarity.
 - ❖ Sufficient cooling must be ensured.
 - ❖ Keep away from fire and water

- **Never work on the power supply if power is supplied!** Risk of electric arcs and electrical shock which can cause death, severe personal injury or substantial property damage.
- **Warning:** Hazardous voltages and components storing a very substantial amount of energy are present in this power supply during normal operating conditions. However, these are inaccessible. Improper handling may result in an electric shock or serious burns!

Installation Instructions:

- This power supply is designed for professional indoor systems. In operation the power supply must not be accessible. It may be installed and put into service by qualified personnel only.
- The correct mounting position for optimal cooling performance must be observed. Observe power derating (see data sheet).
- **Recycling:** The unit contains elements which are suitable for recycling, and components which need special disposal. You are therefore requested to make sure that the power supply will be recycled by the end of its service life.