


Features

- ◆ High power density
- ◆ DIP-24 metal package
- ◆ Wide 2:1 input range
- ◆ Very high efficiency up to 88%
- ◆ I/O isolation 1500V
- ◆ Input filter to meet EN 55022, class A
- ◆ Remote On/Off
- ◆ Shielded metal case with insulated Baseplate
- ◆ Continuous short-circuit protection
- ◆ Operating temp. range -40°C to $+85^{\circ}\text{C}$ (with derating)
- ◆ Lead free design, RoHS compliant
- ◆ 3-year product warranty



The THD-12 series is a range of high performance, isolated 12W dc/dc converters. They come in a low profile, DIP-24 package with standard industry pin-out. Overload and overvoltage protection as well as remote On/Off are included as standard. Built-in filters for both input and output minimizes the need of external filtering. Full SMD-design with exclusive use of ceramic capacitors guarantees a high reliability and long product lifetime. Typical applications for these converters are industrial electronics, instrumentation, data communication systems and battery operated equipment with limited space available on the PCB.

Models

Order code	Input voltage range	Output voltage	Output current max.	Efficiency typ.
THD 12-1209	9 – 18 VDC (nominal 12 VDC)	2.5 VDC	3'500 mA	82 %
THD 12-1210		3.3 VDC	3'500 mA	84 %
THD 12-1211		5.1 VDC	2'400 mA	86 %
THD 12-1212		12 VDC	1'000 mA	86 %
THD 12-1222		± 12 VDC	± 500 mA	87 %
THD 12-1223		± 15 VDC	± 400 mA	87 %
THD 12-2409	18 – 36 VDC (nominal 24 VDC)	2.5 VDC	3'500 mA	83 %
THD 12-2410		3.3 VDC	3'500 mA	85 %
THD 12-2411		5.1 VDC	2'400 mA	87 %
THD 12-2412		12 VDC	1'000 mA	87 %
THD 12-2422		± 12 VDC	± 500 mA	88 %
THD 12-2423		± 15 VDC	± 400 mA	88 %
THD 12-4809	36 – 75 VDC (nominal 48 VDC)	2.5 VDC	3'500 mA	83 %
THD 12-4810		3.3 VDC	3'500 mA	85 %
THD 12-4811		5.1 VDC	2'400 mA	87 %
THD 12-4812		12 VDC	1'000 mA	87 %
THD 12-4822		± 12 VDC	± 500 mA	88 %
THD 12-4823		± 15 VDC	± 400 mA	88 %

General Specifications


Temperature ranges	- Operating - Case temperature - Storage	-40°C to +85°C +100°C max. -55°C to +105°C
Derating		2.5 %/K above 65°C
Thermal inpedance	- Natural convection	20°C/W
Humidity (non condensing)		5 % to 95 % rel H max.
Reliability, calculated MTTF (MIL-HDBK-217F, @ 25°C, ground benign)		>750'000 h
Thermal shock & vibration		MIL-STD-810F
Isolation voltage (60sec)	- Input/Output	1'500 VDC
Isolation capacity	- Input/Output	1'200 pF typ.
Isolation resistance	- Input/Output (500 VDC)	>1'000 MOhm
Switching frequency		400 kHz typ. (pulse width modulation PWM)
Safety standards (operational Insulation)		UL 60950-1, EN 60950-1, IEC 60950-1
Safety approvals		www.ul.com -> certifications -> File E188913
Remote On/Off	- On: - Off: - Off idle current:	3.0 ... 12 VDC or open circuit (referenced to -Vin) 0 ... 1.2 VDC or short circuit pin 1 and pin 2/3 2.5 mA

Physical Specifications

Casing material	nickel coated copper
Baseplate material	non conductive FR4
Potting material	epoxy (UL94V-0 rated)
Weight	18 g (0.62 oz)
Soldering temperature	max. 265°C / 10 sec.

Application note: www.tracopower.com/products/thd12-application.pdf

Outline Dimensions



Pin-Out

Pin	Single	Dual
1	Remote On/Off	Remote On/Off
2	-Vin (GND)	-Vin (GND)
3	-Vin (GND)	-Vin (GND)
9	No pin	Common
11	ntc.	-Vout
14	+Vout	+Vout
16	-Vout	Common
22	+Vin (Vcc)	+Vin (Vcc)
23	+Vin (Vcc)	+Vin (Vcc)

ntc. = not to connect

Dimensions in [mm], () = Inch
Pin diameter $\varnothing 0.5 \pm 0.1$ (0.02 \pm 0.004)
Tolerances ± 0.5 (± 0.02)
Pin pich tolerances ± 0.25 (± 0.01)

Specifications can be changed any time without notice.