

Industrial Power Supplies

TIS Series, 50-600 Watt

Features

- ◆ Switch mode power supplies for **DIN-rail mount**
- 6 power ranges with 2, 3, 6, 12, 20 and 24 A output current (24 VDC models)
- Selectable 115/230 VAC input
- Very low ripple and noise
- EMI complies with EN 61000-6-3 and EN 61000-6-4
- Operating temp. range –25°C to +70°C
- For system operation available with built-in functions:
 - **RED:** Redundancy module for N+1 Systems with true current sharing
 - Signal module with AC-powerfail, power good signal and external On/Off control
 - UDS: DC-UPS module for uninterruptable battery backed-up power systems
- Worldwide safety approvals incl. class I, div. 2 location
- Easy snap-on mount on DIN-rails or chassis mount
- 3-year product warranty















The switching power supplies of the TIS series have been particularly designed for applications in industrial process control systems and with machine tools. Excellent specifications and high immunity against electrical disturbances guarantee reliable power for sensitive loads in rugged industrial environments. With the help of optional function modules specific requirements for system applications can be easily realized with a standard model. With the UDS module the power supplies can be extended to a perfect DC-UPS with automatic battery-backup. This function is very often required in applications where a time delayed shutdown of a system is necessary. To monitor and control the power supply a signal module can be installed. For parallel operation with active power sharing a redundancy option is available. This flexibility makes the TIS series power supplies a cost effective solution for many industrial applications.

| Models | | | | |
|---------------------------|---|--------------|----------------|----------------|
| Order Code | Input Voltage | Output Power | Output Voltage | Output Current |
| (includes terminal plugs) | nom. | max. | nom. | max. |
| TIS 50-112 | 115-240 VAC | | 12 VDC | 3.5 A |
| TIS 50-124 | universal input | 50 W | 24 VDC | 2.0 A |
| TIS 75-112 | | | 12 VDC | 6.0 A |
| TIS 75-124 | 115/230 VAC | 75 W | 24 VDC | 3.0 A |
| TIS 75-148 | selectable | | 48 VDC | 1.5 A |
| TIS 150-124 | 115/230 VAC | | 24 VDC | 6.0 A |
| TIS 150-148 | selectable | 150 W | 48 VDC | 3.0 A |
| TIS 300-124 | 115/000 \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ | | 24 VDC | 12.0 A |
| TIS 300-148 | 115/230 VAC | 300 W | 48 VDC | 6.0 A |
| TIS 300-172 | selectable | | 72 VDC | 4.2 A |
| TIS 500-124-115 | 115 VAC | 500 W | 24 VDC | 20.0 A |
| TIS 500-124-230 | 230 VAC | 500 W | 24 VDC | 20.0 A |
| TIS 600-124 | 115/000 \ (A.C. | | 24 VDC | 24.0 A |
| TIS 600-148 | 115/230 VAC | 600 W | 48 VDC | 12.0 A |
| TIS 600-172 | selectable | | 72 VDC | 8.5 A |



Industrial Power Supplies TIS Series 50-600 Watt

| Input Specifications | | | |
|--|--|---|--|
| Input voltage range | | | |
| Input frequency | | 47 – 63 Hz | |
| Input current at full load (typ.) | TIS 50: TIS 75: TIS 150: TIS 300: TIS 500: TIS 600: | 1.3 A 0.75 A 2.7 A 1.6 A 4.9 A 2.9 A 6.0 A 4.3 A | |
| Recommended circuit breaker, characteristic C or fuse, slow blow typ | TIS 50: TIS 75: TIS 150: TIS 300: TIS 500: TIS 600: | 15.0 A | |
| Output Specifications | | | |
| Output voltage adj. range | 12 VDC models: 24 VDC models: 48 VDC models: 72 VDC models: | 48 – 52 VDC | |
| Regulation – Input variation – Load variation (10–90%) | TIS 50, TIS 75, TIS 150: TIS 300, TIS 500, TIS 600: | 0.2 % 1.0 % 0.3 % (2.0 % in parallel operation) | |
| Ripple and noise (20MHz bandwidth) | | <50 mV pk-pk | |
| Electronic short circuit protection | | current limitation at 110 % typ. (constant current, automatic restart) | |
| Over voltage protection, trigger point at | | 140 % typ. Vout nom. | |
| Hold-up time | TIS 50 TIS 300: TIS 500: TIS 600: | min. 20 ms min. 40 ms | |



Industrial Power Supplies TIS Series 50-600 Watt

| Temperature ranges | Operating (ambient temp.) | | -25°C to +70°C | |
|--|---|---|--|--|
| remperatore ranges | - Derating above 50°C (122°F) | | 2 %/K | |
| | - Storage (non operating) | | -25°C to +85°C | |
| Humidity (non condensing) | | | 95 % rel. H max. | |
| Pollution degree | | | 2 | |
| Temperature coefficient | | | 0.02 %/K | |
| Altitude during operation | | | 2′000 m max. | |
| Switching frequency | | | 80 kHz typ. (pulse width modulation) | |
| Efficiency | | TIS 50 TIS 300: TIS 500: TIS 600: | 90 % typ. | |
| Isolation | | | according to IEC/EN 60950, UL 60950, UL 508 | |
| Reliability, calculated MTBF (MILHDBK-217F, at +25°C, | ground benign) | | 450'000 h / 420'000 h 420'000 h / 360'000 h 340'000 h / 300'000 h | |
| Safety standards | | | IEC/EN 60950-1 (SELV, except 72 VDC models) UL/cUL 60950-1, UL 508, UL/cUL 1604 | |
| Safety approvals | – CB report – UL approvals | | for IEC 60950, IEC 62368-1 UL/cUL 60950, File e181381 UL 62368-1 UL/cUL 508, File e210002 UL/cUL 1604, File e213613 not for TIS 50 & 500 (Class I, Div. 2, Groups A, B, C and D hazardous locations | |
| | CSA certificateCertification documents | | www.ul.com -> certifications UL 60950-1, CSA 60950-1 www.tracopower.com/overview/tis | |
| Electromagnetic compatibil | ity (EMC), Emissions - Conducted RI suppression on inp - Radiated RI suppression | out | EN 61000-6-3 / EN 61000-6-4 EN 55011 class B, EN 55022 class B, FCC part 15, level B EN 55011 class A, EN 55022 class A, FCC part 15, level A | |
| Electromagnetic compatibil | ity (EMC), Immunity - Electrostatic discharge (ESD) - Radiated RF field immunity - Electrical fast transient / burst imi - Surge immunity - Immunity to conducted RF disturb - Power frequency field immunity | , | EN 61000-6-2 IEC/EN 61000-4-2 | |
| Safety class | | | degree of electrical protection 1 (IEC 536) | |
| Case protection | | | IP 20 (IEC 529) | |
| Environment | – Vibration – Shock | | IEC 60068-2-6; 1 gn, 200 sweeps, each axis IEC 60068-2-27; 15 gn, 11 ms, each axis | |
| Enclosure material | | | aluminium (chassis) / zinc plated steel (cover) | |
| Mounting (snap-on with self | locking spring) | | for 35 mm DIN-rails as per EN 50022 | |
| Connection | | | detachable screw terminal block (plugs included) (TIS 600: fixed screw terminal block) | |

Instruction manual can be downloaded under:

www.tracopower.com/overview/tis

All specifications valid at nominal input voltage, full load and +25 °C after warm-up time unless otherwise stated.




Power Supplies with Redundancy Function

With this option a parallel operation of up to 5 units is possible. Decoupling diodes and current share lines allow to build true N+1 redundant systems with active current sharing for all units. This function also includes an alarm relay to signal a single unit failure.

This option is available for TIS 150 W, TIS 300 W and TIS 600 W models.

Please note: This option cannot be combined with other options.

| Models | | | | | | | | |
|---------------------------|---------------|--------------|----------------|----------------|--|--|--|--|
| Order Code | Input Voltage | Output Power | Output Voltage | Output Current | | | | |
| (includes terminal plugs) | | max. | nom. | max. | | | | |
| TIS 150-124 RED | 115/230 VAC | 150 \ | 24 VDC | 6.0 A | | | | |
| TIS 150-148 RED | selectable | 150 W | 48 VDC | 3.0 A | | | | |
| TIS 300-124 RED | 115/230 VAC | 200 \ | 24 VDC | 12 A | | | | |
| TIS 300-148 RED | selectable | 300 W | 48 VDC | 6.0 A | | | | |
| TIS 600-124 RED | 115/230 VAC | (00) | 24 VDC | 24 A | | | | |
| TIS 600-148 RED | selectable | 600 W | 48 VDC | 12 A | | | | |



Specifications

Rating per relay contact

60 VDC /0.36 A max.

Instruction manual for RED option can be downloaded under: www.tracopower.com/overview/tis




Power Supplies with Powerfail Functions

These models provide 3 functions required in many process control system applications:

- AC-Powerfail signal (relay contact)
- ◆ Power Good signal (relay contact)
- Remote On/Off

| Models | | | | |
|---------------------------|---------------|--------------|----------------|----------------|
| Order Code | Input Voltage | Output Power | Output Voltage | Output Current |
| (includes terminal plugs) | | max. | nom. | max. |
| TIS 150-124 SIG | 115/230 VAC | 150 W | 24 VDC | 6.0 A |
| TIS 150-148 SIG | selectable | 130 11 | 48 VDC | 3.0 A |
| TIS 300-124 SIG | 115/230 VAC | 300 W | 24 VDC | 12 A |
| TIS 300-148 SIG | selectable | 300 11 | 48 VDC | 6.0 A |
| TIS 600-124 SIG | 115/230 VAC | 600 W | 24 VDC | 24 A |
| TIS 600-148 SIG | selectable | 000 ** | 48 VDC | 12 A |



| Specifications | |
|--|---|
| Power Good signal trigger point | models with 24 Vout: >22.8 VDC ±0.5 V relay B closed (pin 4 - pin 3) models with 48 Vout: >45.6 VDC ±1.0 V relay B closed (pin 4 - pin 3) |
| AC-Powerfail signal | Vin <93 resp. <187 VAC relay A closed (pin 7 – pin 6) |
| Raiting per relay contact | 60 VDC /0.36 A max. |
| Remote On/Off - ○n - ○ff | short circuit con 3 pin 1 and pin 2 open circuit con 3 pin 1 and pin 2 |

Instruction manual for SIG option can be downloaded under: www.tracopower.com/overview/tis



DC-UPS-System



In addition to the standard power supply function, these models include a professional battery management system to charge and monitor an external battery. In the event of a power failure the battery is switched automatically and without any interruption to the DC output. Once mains power is available again, the battery is switched off. The backup time is limited only by battery capacity and load. Charge current and voltage can be adjusted to values as required by battery type. Power fail and low battery alarm signals

are available via two independent relay contacts. During normal operation the battery status is monitored by periodically loading the battery for a short time. If a cell resistance is high, there is a relay alarm is available. The battery is fully protected under any operational conditions. The power supply is short circuit protected even in battery backup operation but, for safety reasons, the battery should be fitted with a fast blow fuse. Battery mode can be activated by interconnecting pin 7 and 8.

| Models | | | | |
|-----------------|---------------|--------------|----------------|-------------------|
| Order Code 1) | Input Voltage | Output Power | Output Voltage | Output Current 2) |
| | | max. | nom. | max. |
| TIS 300-124 UDS | 115/230 VAC | 300 W | 24 VDC | 12 A |
| | selectable | | | |
| TIS 600-124 UDS | 115/230 VAC | 600 W | 24 VDC | 24 A |
| | selectable | | | |

¹⁾ Includes terminal plugs, does not include batteries

External Batteries

For external batteries we recommend:

Two Panasonic LC-R123R4PG in series for 3.4 Ah: www.tracopower.com/products/tsp-panas_034.pdf Two Panasonic LC-R127R2PG1 in series for 7.2 Ah: www.tracopower.com/products/tsp-panas_072.pdf


Mounting Devices for Batteries

Order Code:

TIS 24-32AF Frame & wiring for two Panasonic LC-R123R4PG batteries **TIS 24-70AF** Frame & wiring for two Panasonic LC-R127R2PG1 batteries

²⁾ reduce max. output current by battery charging current

DC-UPS-System




| Specifications | | | |
|---------------------------|--|--------------------------------------|---|
| Charging current (factor | y set) | TIS 300-124 UDS: TIS 600-124 UDS: | |
| Adjustment range of cha | arging current | TIS 300-124 UDS: TIS 600-124 UDS: | |
| Holding current for char | ged battery at voltage 27.3 VDC | | <50 mA |
| Overload or short circuit | t during battery operation | | system switches off |
| AC-Powerfail signal | | | Vin <93 or <187 VAC relay A closed (pin 2 – pin 3) |
| Low battery signal | Battery voltage below 22 VRaiting per relay contact | | relay B closed (pin 5 – pin 6) 60 VDC /0.36 A max. |

Supporting documents: www.tracopower.com/overview/tis


Case Dimensions

TIS 50 models




Weight: 0.41 kg (0.9 lb)

TIS 75 models



Weight: 0.48 kg (1.06 lb)

TIS 150 models



Weight: 0.80 kg (1.76 lb)


| Connectors (Included in shipment) | | | | | | |
|-----------------------------------|-----------------------------------|--|--|--|--|--|
| TIS PLUG-1 | Connector Set for TIS 50/75/150 | | | | | |
| TIS PLUG-1-RED | Connector Set for TIS 150-1xx RED | | | | | |

Connector Set for TIS 300-1xx UDS

Connector Set for TIS 500

Case Dimensions


TIS 300 models



TIS PLUG-3-UDS

TIS PLUG-5

TIS 500 models




Weight: 1.9 kg (4.19 lb)

Dimensions in [mm], () = Inch Tolerances: ± 0.5 (± 0.02)

Outline Dimensions mm (inches)

TIS 600 models




Weight: 2.0 kg (4.41 lb)

| Connectors (Included in shipment) | | | | | |
|--|-----------------------------------|--|--|--|--|
| TIS PLUG-6-RED Connector Set for TIS 600-1xx RED | | | | | |
| TIS PLUG-6-UDS | Connector Set for TIS 600-1xx UDS | | | | |

Optional Mounting Systems


Wall mounting kit



| Models | Order code | Α | В | С | D | E |
|---------|------------|------------|-------------|------------|--------------|--------------|
| TIS 75 | MK-75 * | 37 (1.46) | 14.5 (0.57) | _ | 134.5 (5.30) | 150.5 (5.93) |
| TIS 150 | MK-150 * | 132 (5.20) | 13.5 (0.53) | 105 (4.13) | 134.5 (5.30) | 150.5 (5.93) |
| TIS 300 | MK-300 * | 132 (5.20) | 13.5 (0.53) | 105 (4.13) | 134.5 (5.30) | 150.5 (5.93) |
| TIS 500 | MK-500 * | 132 (5.20) | 13.5 (0.53) | 105 (4.13) | 134.5 (5.30) | 150.5 (5.93) |
| TIS 600 | MK-600 * | 190 (7.48) | 37.5 (1.48) | 115 (4.53) | 197.0 (7.76) | 207.0 (8.15) |

Note * End of life

Rugged DIN-Rail mounting kit




| Models | Order code | Α | В | С |
|---------|--------------|------------|------------|-----------|
| TIS 150 | RMK-150 | 150 (5.91) | 115 (4.53) | 35 (1.38) |
| TIS 300 | RMK-300 | 200 (7.87) | 165 (6.50) | 35 (1.38) |
| TIS 500 | RMK-300 | 200 (7.87) | 165 (6.50) | 35 (1.38) |
| TIS 600 | (standard) * | 180 (7.09) | 165 (6.50) | 15 (0.59) |


^{*} included in standard shipping



Outline Dimensions mm (inches)

TIS 24-32AF (Frame & wiring, excluding batteries)





TIS 24-70AF (Frame & wiring, excluding batteries)

