Industrial Power Supplies

TBL-BC Series, 60 Watt



Features

- Uninterruptible switch mode power supply for DIN-rail mount
- Battery management system included
- Uninterrupted 24 VDC / 60 W
- For Alarm equipment compliant EN 50131
- External battery size free selectable
- Adjustable output voltage
- Short circuit and overload protection
- Easy snap-on mounting on DIN-rail
- 3-year product warranty



The TBL-BC power supply is a uninterruptible DIN-Rail switch mode power supply designed for application in alarm equipment, building automation or other security relevant systems. It guarantees continued operation in the case of a mains power failure.

The unit charges the external battery at an optimum charge voltage to suit the battery temperature using an external NTC temperature sensor. An alarm output will indicate if there is a problem with the battery voltage, the battery temperature or the mains input voltage.

Models					
Order Code	Output Power	Output Voltage*	Output Current **	Efficiency	
	(max.)	(nom.)	(max.)	(typ.)	
TBL 060-124BC	60 W	24 VDC	2.2 A	84 %	

* The Battery charging voltage is factory set to 27,6 VDC at 25°C

** reduce max. output current by battery charging current

Industrial Power Supplies TBL-BC Series 60 Watt

Input Specifica	tions			
Input voltage	– nominal – AC auto ra	nge		100 – 120 / 220 – 240 VAC 85 – 132 / 187 – 264 VAC
Input frequency				47 – 63 Hz
Input current (at full	load)			Vin = 115 VAC Vin = 230 VAC 1.4 A typ. 0.7 A typ.
Harmonic limits				EN 61000-3-2, Class A
Output Specific	cations			
Output voltage adj. range			26.0 – 29.5 VDC, factory set: 27.6 VDC at 25°C	
Voltage drift (see graph)		- maxim - minimu 30 VDC	ium vo um vol	-54 mV/°C voltage at -10°C: 29.5 VDC oltage at +55°C: 26.0 VDC
		29 VDC		adjustable output voltage
	Output voltage v battery temperat	s 28 VDC		27.6 VDC of 25°C factory set
	, ,	27 VDC		adjustable output voltage
		25 VDC -10	0°C	0°C 10°C 20°C 30°C 40°C 50°C 60°C
Output current max. 2.2 A - Reduce output power by desired battery charging current. Maximum output power must part avecade 60 W/				
Ripple and noise (20	OMHz bandwidth)			<50 mV pk-pk
Overload and short circuit protection current limitation at 2.5 A constant current (automatic recovery) applies to both, load and battery charge o				current limitation at 2.5 A constant current (automatic recovery) applies to both, load and battery charge output
Overvoltage protection at 31,2 V				at 31,2 V
Voltage differance at mains failure			0.3 V typ. (max 1.0 V for 1 sec.)	
Regulation – Input variation – Load variation (10–100 %)			0.04 % max. 0.2 % max.	
Signal output			Open collector 60 VDC max., 35 mA max. sink current	
LED indicator	Signal output	Status		Condition
Constant green	closed	Mains and battery	ok	
Flash green	open	Mains fail, battery ok Inpu		Input voltage below 80 VAC, power from battery
Constant red	open	Battery voltage fail Battery voltage		Battery voltage below 23.8 VDC (activation range: 23.2 - 24.4)
Flash red	open	Battery temperature fail Battery temperature exceeded a		Battery temperature exceeded 65°C (or temperature sensor connection is open or short circuited)

Industrial Power Supplies TBL-BC Series 60 Watt

General Specification	15	
Temperature ranges	– Operating – Storage (non operating)	–10°C to +60°C max. –20°C to +70°C
Power derating		2.5 %/K above +60°C
Humidity (non condensing)		99 % rel. H
Switching frequency		70 kHz typ. (fixed)
Safety standards	 Information technology equipment Electrical equipment for machines Electronic equipment for power installation Transformer safety for bell and chime transformers 	IEC/EN 60950-1, UL 60950-1 EN 60204-1 EN 50178 EN 61558-2-16
Safety approvals	 CB report CSA certification SIQ certificate Certification documents 	IEC/EN 60950-1 UL 60950-1, CSA 60950-1-03 IEC/EN 60950-1 www.tracopower.com/overview/tbl-bc
Electromagnetic compatibilit	y (EMC), emissions – Conducted RI suppression on input – Radiated RI suppression	EN 61000-6-3 /EN 61000-6-4 EN 55011 class B, EN 55022 class B EN 55011 class A, EN 55022 class A
Electromagnetic compatibilit	 y (EMC), immunity Electrostatic discharge (ESD) Radiated RF field immunity Electrical fast transient / burst immunity Surge immunity line – ground Surge immunity line – line Surge immunity output Immunity to conducted RF disturbances Power frequency field immunity 	EN 61000-6-2 EN54-4, EN 50130-4 EN54-4, EN 50130-4 EN 61000-4-5 2 kV EN 61000-4-5 1 kV EN 61000-4-5 0.5 kV EN 61000-4-6 10 V EN 61000-4-8 30 A/m
Protection class		class II as per IEC/EN 61140
Case protection		IP 20 (IEC 60529)
Environment	– Vibration acc. IEC 60068-2-6; – Shock acc. IEC 60068-2-27	3 axis, sine sweep, 10 – 55 Hz, 0.075 mm 3 axis, 15 g half sine, 11 ms
Enclosure material		plastic FR2010-110C (UL 94V-0 rated)
Mounting		DIN-rails as per EN 50022-35x15/7.5 (snap-on with self-locking spring)
Connection		screw terminals with combi-type screw heads for wire size 0.5 – 2.5 mm ²
Installation instructions		www.tracopower.com/overview/tbl-bc

All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.

Industrial Power Supplies TBL-BC Series 60 Watt

Dattery Supervision & UPS Function	
Under voltage lockout (Vuvl)	21.0 - 22,5 VDC, Battery will be disconnected if it is short circuited or voltage drops below Vuvl (As a battery can artificially recover itself, it will remain disconnected until mains recover)
Active battery test - draws 1.2 A during 2 sec.	at battery voltage: >25.5 VDC Battery voltage fail, if voltage drops below 23.8 VDC during this test
Passive battery test - draws no current	at battery voltage: Vuvl – 25.5 VDC Battery voltage fail, if voltage is below 23.8 V
Test routine	2 sec. every 60 sec. only if mains is ok
Battery temperature supervision	NTC: K164/4.7k/K, Siemens Matsushita: B57164-K472-K
Battery charge characteristics	I-V curve

In the transition from mains to battery operation and vice versa, the output is not interrupted and the difference between Battery Voltage (Vbatt) and Output Voltage (Vo) is typically no more than 0.3 V. To optimize battery charging, the battery charging voltage is adjusted to suit the battery temperature by means of an NTC temperature sensor which must be placed near the battery. The charge voltage falls with increasing temperature. The unit incorporates full automatic monitoring for the presence and condition of the battery. Two different battery tests are carried out (passive or active) depending on the battery voltage. Both types of test are carried out once every 60 seconds and the tests last ~2 seconds. If the battery voltage is between ~21.4V and ~25.5V a passive battery test is carried out which only tests the battery voltage but does not draw any current from the battery. Between 25.5V and the maximum battery voltage, an active battery test is carried out in which a current of ~1.2A is drawn from the battery through an internal load for ~2s. If the battery voltage is determined to be below ~23.8 V after any of these tests, then a battery fail notification is given. The battery tests are only carried while the mains voltage is ok. The unit also produces a failure notification in the event of a disconnected or short-circuited battery. In the event of a battery failure in any of these modes, the LED will turn constant RED and a built in open-Collector circuit stops sinking current from to the FAIL output pin. In the case of a mains fail, if the battery voltage is detected to be below ~21V min. then it is automatically disconnected from the load to prevent a deep-discharge and subsequent long-term damage to the battery. Note that after it has disconnected, the battery voltage may rise above 21V once more, however in this case, the switch will not open again as the battery has not truly recovered. The switch will not open again until the mains has recovered and the battery then goes straight into charge mode. The input terminals,»L» and «N», the output terminals «+24V», «OV», «+BATT» and «FAIL» and the temperature sensor terminals «S1» and «S2» are clearly marked on the hood label.





Case Dimensions



Weight: 410 g (14.46 oz)

Dimensions	in [mm], ()	= Inch
Tolerances:	±0.5 mm (±0.02)

J1 (input)		J2 (output)	
1	AC (L)	1	+Vout
2	AC (N)	2	GND (0V)
		3	+Batt
		4	Fail

J3 (temp. sense)		
1	S1	
2	S2	

Battery Temperature Sensor - not included				
Order code	Description	NTC Model		
TBL-BC-TS1	Battery sensor (NTC) with 2 m connection line	Siemens Matsushita: B57164-K472-K		

Specifications can be changed without notice! Make sure you are using the latest documentation, downloadable at www.tracopower.com