



TEST REPORT

FOR
DC to DC CONVERTER
MODEL : TRV 1-2411M

SERIES MODEL : Refer to item 5.1 for more details.

REPORT NUMBER: 4789666248A-EN-E1-V0

ISSUE DATE: Nov. 11, 2020

Prepared for
TRACO ELECTRONIC AG
Sihlbruggstrasse 111 CH-6340 Baar Switzerland

Prepared by
Underwriters Laboratories Taiwan Co., Ltd.,
Building B and Building E, No. 372-7, Sec. 4, Zhongxing Rd., Zhudong Township,
Hsinchu County, Taiwan
Tel: +886.2.2896.7790
Fax: +886.3.583.7948
Website: www.ul.com



The results reported herein have been performed in accordance with the laboratory's terms of accreditation. This report shall not be reproduced except in full without the written approval of the Laboratory. The results in this report are responsible of the test sample(s) provided by the client only and are not to be used to indicate applicability to other similar products.

Revision History

Rev.	Issue Date	Revisions	Revised By
--	Nov. 11, 2020	Initial Issue	Sally Lu

Summary of Test Results				
EMISSION (EN 60601-1-2:2015 standards)				
Standard	Test Item	Limit	Result	Remark
CISPR 11 Ed 5.1 EN55011: 2009+A1 : 2010	Conducted disturbance at mains terminals ports	Class B	N/A	Note 1, Note 5
	Patient-coupled cable conducted emission	24dBuA	N/A	Note 2, Note 5
	Radiated disturbance below 1GHz	Class B	PASS	Note 4, Note 5
	Radiated disturbance above 1 GHz	Class B	N/A	Note 3, Note 5
IEC 61000-3-2:2014	Harmonic current disturbance	Class A	N/A	Note 1, Note 5
IEC 61000-3-3:2013	Voltage Fluctuations & Flicker	Refer to chapter 6.4.1	N/A	Note 1, Note 5

Note: (1) Since the EUT does not connect to mains power network directly, the test is unnecessary.

Note: (2) There is no patient-coupled cable, so the test is unnecessary.

Note: (3) For Group 1, in the frequency range 1 to 18GHz limits are not specified.

Note: (4) Customers add countermeasure components to the fixture board. For the corresponding components, please refer to the appendix III.

Note: (5) Please refer to original report no.: 4789565714A-EN-E1-V1.

Summary of Test Results					
IMMUNITY (EN 60601-1-2:2015 standards)					
Professional healthcare facility environment					
Basic Standard	Test Item	Test Level	Criteria	Result	Remark
IEC 61000-4-2:2008	Electrostatic discharge immunity	Contact ±8 kV Air ±15 kV	Clause 7.1	PASS	Note 6
IEC 61000-4-3: 2006+ A1:2007+A2:2010	Radiated, radio frequency electromagnetic field immunity	3V/m 80%, 1kHz, AM 80MHz~2.7GHz	Clause 7.1	PASS	
	Proximity fields from RF wireless communications equipment	See page 6	Clause 7.1	PASS	
IEC 61000-4-4:2012	Electrical fast transient/burst immunity	2.0kV(AC Mains) 1kV(Signal Lines) 5/50ns, 100kHz	Clause 7.1	PASS (Note 5)	
IEC 61000-4-5: 2014 + A1: 2017	Surge immunity	2.0kV(Common) 1.0kV(Differential) 1.2/50us	Clause 7.1	PASS (Note 5)	
IEC 61000-4-6: 2013+ COR1: 2015	Immunity to conducted disturbances, induced by radio-frequency fields	3V(rms) 80%, 1kHz AM. 0.15MHz~80MHz 6 V(rms) in ISM bands between 0,15 MHz and 80 MHz.(Note1)	Clause 7.1	PASS	
IEC 61000-4-8:2009	Power frequency magnetic field immunity	50Hz, 30 A/m	Clause 7.1	PASS	
	Power frequency magnetic field immunity (Short duration)	50Hz, 1000A/m, 1s (r.m.s) by client request	Clause 7.1	PASS	
IEC 61000-4-11:2004+ A1: 2017	Voltage dips, short interruptions and voltage variations immunity	Voltage dips, 0% residual for 0.5 cycle (Note 3)	Clause 7.1	N/A (Note 4)	
		Voltage dips, 0% residual for 1cycle (Note 3)	Clause 7.1		
		Voltage dips, 70% residual for 25/30 cycle (Note 2,3)	Clause 7.1		
		Voltage interruptions For 250/300 cycle (NOTE 2,3)	Clause 7.1		

Note: (1) The ISM (industrial, scientific and medical) bands between 0,15 MHz and 80 MHz are 6,765 MHz to 6,795 MHz; 13,553 MHz to 13,567 MHz; 26,957 MHz to 27,283 MHz; and 40,66 MHz to 40,70 MHz. The amateur radio bands between 0,15 MHz and 80 MHz are 1,8 MHz to 2,0 MHz, 3,5 MHz to 4,0 MHz, 5,3 MHz to 5,4 MHz, 7 MHz to 7,3 MHz, 10,1 MHz to 10,15 MHz, 14 MHz to 14,2 MHz, 18,07 MHz to 18,17 MHz, 21,0 MHz to 21,4 MHz, 24,89 MHz to 24,99 MHz, 28,0 MHz to 29,7 MHz and 50,0 MHz to 54,0 MHz.

Note: (2) 25/30 or 250/300 means 25 or 250 periods at 50 Hz or 30 or 300 periods at 60 Hz.

Note: (3) For ME EQUIPMENT and ME SYSTEMS that have multiple voltage settings or auto ranging voltage capability, the test shall be performed at the minimum and maximum RATED input voltage. ME EQUIPMENT and ME SYSTEMS with a RATED input voltage range of less than 25 % of the highest RATED input voltage shall be tested at one RATED input voltage within the range.

Note: (4) Since the EUT does not connect to mains power network directly, the test is unnecessary.

Note: (5) Customers add countermeasure components to the fixture board. For the corresponding components, please refer to the appendix III.

Note: (6) Please refer to original report no.: 4789565714A-EN-E1-V1.

Test specifications for ENCLOSURE PORT IMMUNITY to RF wireless communications equipment						
Test frequency	Band	Service	Modulation	Maximum power	Distance	IMMUNITY TEST LEVEL
385	380 – 390	TETRA 400	Pulse modulation 18 Hz	1,8	0,3	27
450	430 – 470	GMRS 460, FRS 460	FM \pm 5 kHz deviation 1 kHz sine	2	0,3	28
710	704 – 787	LTE Band 13, 17	Pulse modulation 217 Hz	0,2	0,3	9
745						
780						
810	800 – 960	GSM 800/900, TETRA 800, iDEN 820, CDMA 850, LTE Band 5	Pulse modulation 18 Hz	2	0,3	28
870						
930						
1720	1700 – 1990	GSM 1800; CDMA 1900; GSM 1900; DECT; LTE Band 1, 3, 4, 25; UMTS	Pulse modulation 217 Hz	2	0,3	28
1845						
1970						
2450	2400 – 2570	Bluetooth, WLAN,802.11 b/g/n, RFID 2450, LTE Band 7	Pulse modulation 217 Hz	2	0,3	28
5240	5100 – 5800	WLAN 802.11 a/n	Pulse Modulation 217 Hz	0,2	0,3	9
5500						
5785						

NOTE: If necessary to achieve the IMMUNITY TEST LEVEL, the distance between the transmitting antenna and the ME EQUIPMENT or ME SYSTEM may be reduced to 1 m. The 1 m test distance is permitted by IEC 61000-4-3.

TABLE OF CONTENTS

1. ATTESTATION OF TEST RESULTS	9
2. TEST METHODOLOGY	10
3. FACILITIES AND ACCREDITATION	10
4. CALIBRATION AND UNCERTAINTY	11
4.1. Measuring Instrument Calibration	11
4.2. Measurement Uncertainty	11
5. EQUIPMENT UNDER TEST	13
5.1. Description of EUT	13
5.2. Test Mode	15
5.3. EUT Configuration Test Setup	16
5.4. Monitoring of EUT for All Immunity Test	16
5.5. Accessory	16
5.6. Block diagram showing the configuration of system tested	17
5.7. Description of support units	19
5.8. Measuring Instrument List	20
6. EMISSION TEST	23
6.1. Radiated Disturbance Measurement	23
6.1.1. Limits of radiated disturbance measurement	23
6.1.2. Test Procedure	25
6.1.3. Test Setup and Configuration	26
6.1.4. Test Result	27
7. IMMUNITY TEST	29
7.1. Performance Criteria	29
7.2. Electrostatic Discharge Immunity Test	30
7.2.1. Test Specification	30
7.2.2. Test Procedure	30
7.2.3. Test Setup and Configuration	31
7.2.4. Test Result	32
7.3. Radio Frequency Electromagnetic Field Immunity Test	34
7.3.1. Test Specification	34
7.3.2. Test Procedure	34
7.3.3. Test Setup and Configuration	35
7.3.4. RS proximity fields from RF Wireless Communication Test Specification	36
7.3.5. Test Procedure	36
7.3.6. Test Setup and Configuration	36
7.3.7. Test Result	37

7.4.	Electrical Fast Transient/Burst Immunity Test	38
7.4.1.	Test Specification	38
7.4.2.	Test Procedure	38
7.4.3.	Test Setup and Configuration	39
7.4.4.	Test Result	40
7.5.	Surge Immunity Test.....	41
7.5.1.	Test Specification	41
7.5.2.	Test Procedure	41
7.5.3.	Test Setup and Configuration	42
7.5.4.	Test Result	43
7.6.	Immunity to Conducted Disturbances Induced by RF Fields	44
7.6.1.	Test Specification	44
7.6.2.	Test Procedure	44
7.6.3.	Test Setup and Configuration	45
7.6.4.	Test Result	46
7.7.	Power frequency magnetic field immunity Test	47
7.7.1.	Test Specification	47
7.7.2.	Test Procedure	47
7.7.3.	Test Setup and Configuration	48
7.7.4.	Test Results.....	49
Appendix I: Photographs of EMC Test Configuration.....		51
Appendix II: Photographs of the EUT.....		57
Appendix III: Countermeasure file for EMI, EFT and Surge		58

1. ATTESTATION OF TEST RESULTS

COMPANY NAME: TRACO ELECTRONIC AG
Sihlbruggstrasse 111 CH-6340 Baar Switzerland

EUT DESCRIPTION: DC to DC CONVERTER

MODEL: TRV 1-2411M

SERIES MODEL : Refer to item 5.1 for more details

DATE of TESTED: Jul. 24, 2020 ~ Nov. 2, 2020
(Refer to report no. 4789565714A-EN-E1-V1.)

APPLICABLE STANDARDS	
STANDARDS	TEST RESULTS
EN 60601-1-2:2015	PASS

Underwriters Laboratories Taiwan Co., Ltd. tested the above equipment in accordance with the requirements set forth in the above standards. All indications of Pass/Fail in this report are opinions expressed by Underwriters Laboratories Taiwan Co., Ltd. based on interpretations and/or observations of test results. The test results show that the equipment tested is capable of demonstrating compliance with the requirements as documented in this report.


Note: The results documented in this report apply only to the tested sample, under the conditions and modes of operation as described herein. This document may not be altered or revised in any way unless done so by Underwriters Laboratories Taiwan Co., Ltd. and all revisions are duly noted in the revisions section. Any alteration of this document not carried out by Underwriters Laboratories Taiwan Co., Ltd. will constitute fraud and shall nullify the document. This report must not be used by the client to claim product certification, approval, or endorsement by NVLAP, NIST, any agency of the Federal Government, or any agency of any government.

Prepared By:



Sally Lu Date : Nov. 11, 2020
Project Handler

Approved and Authorized By:



Roy Chen Date : Nov. 11, 2020
Operations Manager

2. TEST METHODOLOGY

All tests were performed in accordance with the procedures documented in the reference standards listed in summary of test results page 3 and page 4.

3. FACILITIES AND ACCREDITATION

Test Location	Underwriters Laboratories Taiwan Co., Ltd.,
Address	Building B and Building E, No. 372-7, Sec. 4, Zhongxing Rd., Zhudong Township, Hsinchu County, Taiwan
Description	All measurement facilities use to collect the measurement data are located at Building B and Building E, No. 372-7, Sec. 4, Zhongxing Rd., Zhudong Township, Hsinchu County, Taiwan

4. CALIBRATION AND UNCERTAINTY

4.1. Measuring Instrument Calibration

The measuring equipment utilized to perform the tests documented in this report has been calibrated in accordance with the manufacturer's recommendations, and is traceable to recognized national standards.

4.2. Measurement Uncertainty

Where relevant, the following measurement uncertainty levels have been estimated for tests performed on the apparatus:

Electromagnetic interference:

Test Item	Measurement Frequency Range	K	U(dB)
966-1 Test Site			
Radiated disturbance below 1 GHz	30MHz ~ 1000MHz	2	5.7

Electromagnetic sensitivity:

Test Item	Measurement Frequency Range	K	U(dB)
Radiated, radio frequency electromagnetic field immunity	80MHz ~ 1000MHz	2	1.9
Immunity to conducted disturbances, induced by radio-frequency fields (CDN)	0.15MHz ~ 80MHz	2	2.4

Test Item	K	Voltage(%)	Rise Time(%)	First Peak Current (%)	Current @ 30ns (%)	Current @ 60ns (%)
Electrostatic discharge immunity	2	2.6	6.9	3.9	4.0	4.0

Test Item	K	Peak Voltage(%)	Rise Time(%)	Pulse width(%)	Burst duration & Period (%)	Repetition rate (%)
Electrical fast transient/burst immunity	2	1.0	2.4	5.1	0.74	0.22

Test Item	K	Phase Shifting (%)	Voltage (%)	Current (%)	Front Time & Duration(For waveform of the surge voltage)(%)	Front Time & Duration(For waveform of the surge current)(%)
Surge immunity	2	0.31	3.6	2.7	1.5	5.9

For test date: Aug. 21, 2020

Test Item	K	Magnetic field Strength(%)	Current (mA/A)
Power Frequency Magnetic Field Immunity Test	2	1.0	31

For test date: Nov. 2, 2020

Test Item	K	Magnetic field Strength(%)
Power Frequency Magnetic Field Immunity Test	2	10.0

5. EQUIPMENT UNDER TEST

5.1. Description of EUT

EUT Name:	DC to DC CONVERTER
Model:	TRV 1-2411M
Series Model:	TRV 1-0510M, TRV 1-0511M, TRV 1-0512M, TRV 1-0513M, TRV 1-0521M, TRV 1-0522M, TRV 1-0523M, TRV 1-1210M, TRV 1-1211M, TRV 1-1212M, TRV 1-1213M, TRV 1-1221M, TRV 1-1222M, TRV 1-1223M, TRV 1-1510M, TRV 1-1511M, TRV 1-1512M, TRV 1-1513M, TRV 1-1521M, TRV 1-1522M, TRV 1-1523M, TRV 1-2410M, TRV 1-2412M, TRV 1-2413M, TRV 1-2421M, TRV 1-2422M, TRV 1-2423M
Power Rating :	24Vdc from DC source
Group :	Group 1
Condition of EUT:	Production unit
Environments:	Home healthcare environment
DATE of Sample Received:	Jul. 21, 2020

Note :

1. This report was issued base on original report which report number is 4789565714A-EN-E1-V1, the differences were only change models' name and the applicant. There is no additional test shall be verified. For the test data, copied from original report 4789565714A-EN-E1-V1 show on this report.

2. The models difference table as below:

Model Number	Input Range	Output Voltage
	VDC	VDC
TRV 1-0510M	4.5 ~ 5.5	3.3
TRV 1-0511M	4.5 ~ 5.5	5
TRV 1-0512M	4.5 ~ 5.5	12
TRV 1-0513M	4.5 ~ 5.5	15
TRV 1-0521M	4.5 ~ 5.5	±5
TRV 1-0522M	4.5 ~ 5.5	±12
TRV 1-0523M	4.5 ~ 5.5	±15
TRV 1-1210M	9.6 ~ 14.4	3.3
TRV 1-1211M	9.6 ~ 14.4	5
TRV 1-1212M	9.6 ~ 14.4	12
TRV 1-1213M	9.6 ~ 14.4	15
TRV 1-1221M	9.6 ~ 14.4	±5
TRV 1-1222M	9.6 ~ 14.4	±12
TRV 1-1223M	9.6 ~ 14.4	±15
TRV 1-1510M	12 ~ 18	3.3
TRV 1-1511M	12 ~ 18	5
TRV 1-1512M	12 ~ 18	12
TRV 1-1513M	12 ~ 18	15
TRV 1-1521M	12 ~ 18	±5
TRV 1-1522M	12 ~ 18	±12
TRV 1-1523M	12 ~ 18	±15
TRV 1-2410M	19.2 ~ 28.8	3.3
TRV 1-2411M	19.2 ~ 28.8	5
TRV 1-2412M	19.2 ~ 28.8	12
TRV 1-2413M	19.2 ~ 28.8	15
TRV 1-2421M	19.2 ~ 28.8	±5
TRV 1-2422M	19.2 ~ 28.8	±12
TRV 1-2423M	19.2 ~ 28.8	±15

Note: The customer only provided TRV 1-2411M, TRV 1-2423M, for the EMI pretest and choose the worst mode do the EMI and EMS final test.

5.2. Test Mode

The Pre-test modes:

Mode	Description	Radiated Emission
Mode 1	Full Load (TRV 1-2411M)	v
Mode 2	Full Load (TRV 1-2423M)	v

After pre-testing, the final test mode was displayed as below table.

Test Items		Test Mode
Emission	Radiated Emission	Mode 1
Immunity	Electrostatic Discharge	Mode 1
	Radio Frequency Electromagnetic Field	Mode 1
	Electrical Fast Transients	Mode 1
	Surge immunity	Mode 1
	Conducted disturbances immunity	Mode 1
	Power frequency magnetic field	Mode 1

5.3. EUT Configuration Test Setup

For Radiated Emission test :

- a. The EUT was linked to resistance load with full load during the testing.
- b. Power on the EUT and run test.

For Immunity test :

- a. The EUT was linked to resistance load with full load and the resistance load was connected with a meter during the testing.
- b. Power on the EUT and run test.

5.4. Monitoring of EUT for All Immunity Test


Audio	N/A
Visual	Monitor the output voltage through the meter.

5.5. Accessory


N/A

5.6. Block diagram showing the configuration of system tested


For Radiated Emission test:



For Immunity - RS, ESD, PFMF, CS test:



For Immunity - Surge, EFT test:



5.7. Description of support units

The EUT has been tested as an independent unit together with other necessary accessories or support units. The following support units or accessories were used to form a representative test configuration during the tests.

Item	Equipment	Mfr/Brand	Model/Type No.	Series No.	FCC ID	Note
A	Fixture board 1	N/A	N/A	N/A	N/A	Provided by the customer
B	Fixture board 2	N/A	N/A	N/A	N/A	Provided by the customer
C	Fixture board 3	N/A	N/A	N/A	N/A	Provided by the customer
D	Power supply	EA	EA-PSI 9500-20	N/A	N/A	N/A
E	Power supply	GW INSTEK	GPD-2303S	GEQ902325	N/A	Provided by the customer
F	Meter	CNSCKJ	C85C17-V	N/A	N/A	N/A

Item	Connection	Shielded Type	Note
1	Power Wire *2	Non-shielded	Provided by the customer Length: 0.1 m
2	Power Wire	Non-shielded	Length: 0.3 m

5.8. Measuring Instrument List

Instrument					
Equipment	Manufacturer	Model No.	Serial No.	Last Cal.	Expired date
Radiated Disturbance					
966-1					
EMI Test Receiver	Rohde & Schwarz	ESR7	101755	2019/12/4	2020/12/3
Loop Antenna	ETS Lindgren	6502	00213440	2019/12/19	2020/12/18
Trilog-Broadband Antena with 5dB Attenuator	SCHWARZBECK	VULB 9168 & N-6-05	9168-773 & AT-N0539	2020/2/11	2021/2/9
Double Ridged Guide Horn Antenna	SCHWARZBECK	BBHA 9120 D	1686	2019/12/27	2020/12/25
Preamplifier	EMC Instrument	EMC330E	980404	2020/6/4	2021/6/3
Preamplifier	EMC Instrument	EMC051835BE	980407	2020/1/15	2021/1/13
Cables	UltraPhase&EMC Instrument	A1K50-UP0358-A1K50-1500&EMC106-NM-SM-2500/8000	170111-3&170104/170223	2020/2/5	2021/2/3
Measurement Software	Farad	EZ-EMC Ver: UL-3A1	N/A	N/A	N/A

Instrument					
Equipment	Manufacturer	Model No.	Serial No.	Last Cal.	Expired date
Electrostatic discharge					
ESD Generator	TESEQ	NSG 437	1125	2019/12/9	2020/12/7
Barometer	TFA	DIVA PLUS	35.1078.10.IT	2020/6/12	2021/6/11
Radio frequency electromagnetic field immunity					
RF and Microwave Signal Generator	Rohde & Schwarz	SMB100A	113793	2020/2/26	2021/2/24
Power amplifier	Milmega	80RF1000-300	1077558	N/A	N/A
Directional coupler	Werlatone	C8719-20	111759	N/A	N/A
Antenna	AR	ATR80M6G	346008	N/A	N/A
Antenna	SCHWARZBECK	STLP 9149	00441	N/A	N/A
RF switch	OSP	OSP	N/A	N/A	N/A
Power Meter	Rohde & Schwarz	NRP2	105524	2019/10/21	2020/10/19
Power Sensor	Rohde & Schwarz	NRP-Z91	103732	2019/10/21	2020/10/19
Power Sensor	Rohde & Schwarz	NRP-Z91	103733	2019/10/21	2020/10/19
Sound Calibrator	Bruel&Kjaer	Type 4231	3016784	2019/12/5	2020/12/4
Audio Analyzer	Rohde & Schwarz	UPV	104227	2019/11/27	2020/11/25
Pressure-field 1/2" Microphone	Bruel&Kjaer	Type 4192	3069928	2020/03/13	2021/3/11
Mouth Simulator	Bruel&Kjaer	Type 4227	3078961	2020/03/06	2021/3/05
GPS signal generator	Keysight Technologies	N5172B	MY56200315	2020/1/14	2021/1/13
Radio Communication Analyzer	Rohde & Schwarz	CMW500	161254	2019/12/13	2020/12/11
Measurement Software	Rohde & Schwarz	EMC32, VER.10.20.01	N/A	N/A	N/A
Electrical fast transient					
Ultra Compact Simulator	EM TEST	UCS 500N7	P1628180275	2019/12/12	2020/12/10
Capacitive Coupling Clamp	EM TEST	HFK	P1642185790	2019/11/27	2020/11/25
Measurement Software	TESEQ	IEC.control, VER.7.1.5	N/A	N/A	N/A

Instrument					
Equipment	Manufacturer	Model No.	Serial No.	Last Cal.	Expired date
Surge					
Ultra Compact Simulator	EM TEST	UCS 500N7	P1628180275	2019/12/12	2020/12/10
Telecom Surge Generator	EM TEST	TSurge7	P1620180015	2019/12/11	2020/12/9
Coupling and Decoupling Network	EM TEST	CNV 508T5	P1637184038	2019/12/16	2020/12/14
Coupling and Decoupling Network	TESEQ	CDN HSS-2	45091	2019/12/16	2020/12/14
Measurement Software	TESEQ	IEC.control, VER.7.1.5	N/A	N/A	N/A
Immunity to conducted disturbances, induced by radio-frequency fields					
Signal Generator	Rohde & Schwarz	SMC100A	105811	2019/10/24	2020/10/22
Power amplifier	Rohde & Schwarz	BBA150-A125B125	102340	N/A	N/A
Coupling and Decoupling Network	TESEQ	CDN M016	45073	2020/3/13	2021/3/12
Coupling and Decoupling Network	TESEQ	CDN T2-10	45003	2020/3/13	2021/3/12
Coupling and Decoupling Network	TESEQ	CDN T4-10	44939	2020/3/13	2021/3/12
Coupling and Decoupling Network	TESEQ	CDN T8-10	49203	2019/12/23	2020/12/21
EM Injection Clamp	TESEQ	CAL 801A & KEMZ 801A	75454.1, 75454.2 & 45181	2020/3/18	2021/3/17
Current injection Probe	TESEQ	CIP 9136A	44618	2019/9/20	2020/9/18
Power - Sensor	Rohde & Schwarz	NRP-Z91	103730	2019/12/5	2020/12/3
Power - Sensor	Rohde & Schwarz	NRP-Z91	103731	2019/12/5	2020/12/3
Sound Calibrator	Bruel&Kjaer	Type 4231	3016784	2019/12/5	2020/12/4
Audio Analyzer	Rohde & Schwarz	UPV	104227	2019/11/27	2020/11/25
Radio Communication Analyzer	Rohde & Schwarz	CMW500	161254	2019/12/13	2020/12/11
Pressure-field 1/2" Microphone	Bruel&Kjaer	Type 4192	3069928	2020/03/13	2021/3/11
Mouth Simulator	Bruel&Kjaer	Type 4227	3078961	2020/03/06	2021/3/05
Measurement Software	Rohde & Schwarz	EMC32, VER.10.20.01	N/A	N/A	N/A
Power frequency magnetic field immunity					
Ultra Compact Simulator	EM TEST	UCS 500N7	P1628180275	2019/12/12	2020/12/10
Current Transformer	EM TEST	MC 2630	P1644186773	2019/11/15	2020/11/13
Magnetic Field Test Antena	EM TEST	MS 100N	P1627181324	2019/11/15	2020/11/13
Current Transformer	EM TEST	MFT100	P2025241594	2020/9/4	2021/9/3
Motorized Variac	EM TEST	MV 2616 (varic NX1-260-16)	P1643186426	2019/12/11	2020/12/9

6. EMISSION TEST

6.1. Radiated Disturbance Measurement

6.1.1. Limits of radiated field disturbance measurement

FREQUENCY (MHz)	<input type="checkbox"/> Group 1 Class A ≤ 20 kVA		<input checked="" type="checkbox"/> Group 1 Class B	
	<input type="checkbox"/> At 10m	<input type="checkbox"/> At 3m	<input type="checkbox"/> At 10m	<input checked="" type="checkbox"/> At 3m
	Quasi-peak dB μ V/m	Quasi-peak dB μ V/m	Quasi-peak dB μ V/m	Quasi-peak dB μ V/m
30 – 230	40	50	30	40
230 – 1000	47	57	37	47

FREQUENCY (MHz)	<input type="checkbox"/> Group 2 Class A ≤ 20 kVA		FREQUENCY (MHz)	<input type="checkbox"/> Group 2 Class B		
	<input type="checkbox"/> At 3m			<input type="checkbox"/> At 3m		
	Magnetic Field Quasi-peak* dB μ A/m	Electric Field Quasi-peak* dB μ V/m		Magnetic Field Quasi-peak* dB μ A/m	Electric Field	
				Quasi-peak* dB μ V/m	Average* dB μ V/m	
0.15 – 0.49	82	-	0.15 - 30	39 - 3	-	-
0.49 – 1.705	72	-				
1.705 – 2.194	77	-				
2.194 – 3.95	68	-				
3.95 – 11	43.5 – 28.5*	-				
11 – 20	28.5	-				
20 – 30	18.5	-				
30 - 47	-	78	30 – 80.872	-	40	35
47 – 53.91	-	60				
53.91 – 54.56	-	60				
54.56 – 68	-	60				
68 – 80.872	-	73				
80.872 – 81.848	-	88	80.872 – 81.848	-	60	55
81.848 – 87	-	73	81.848 – 134.786	-	40	35
87 – 134.786	-	70	134.786 – 136.414	-	60	55
134.786 – 136.414	-	80				
136.414 – 156	-	70				
156 – 174	-	84				
174 – 188.7	-	60				
188.7 – 190.979	-	70	136.414 – 230	-	40	35
190.979 – 230	-	60				
230 – 400	-	70				
400 – 470	-	73				
470 – 1000	-	70	230 - 1000	-	47	42


NOTE:

- (1) The limit for radiated test was performed according to EN55011.
- (2) The tighter limit applies at the band edges.
- (3) The test result calculated as following:
Measurement Value = Reading Level + Correct Factor,
Correct Factor = Antenna Factor + Cable Loss - Amplifier Gain(if use),
Margin Level = Measurement Value - Limit Value.
- (4) For Group 2 at 3m distance radiated magnetic field test, EUT shall be meet the small equipment requirement.
- (5) The average limits apply to magnetron driven equipment only. If magnetron driven equipment exceeds the quasi-peak limit at certain frequencies, then the measurement shall be repeated at these frequencies with the average detector, and the average limits specified in this table apply.
- (6) The limit of " * " marked band means the limitation decreases linearly with the logarithm of the frequency in the range.

6.1.2. Test Procedure

- a. The measuring distance of at 3m shall be used for measurements at frequency from 30 to 1000MHz.
- b. The EUT was placed on the top of a rotating table 0.8 meters above the ground at a 3 meter chamber. The table was rotated 360 degrees to determine the position of the highest radiation.
- c. The height of the equipment shall be set at 0.8 m; the height of the test antenna shall vary between 1 m to 4 m. Both horizontal and vertical polarizations of the antenna are set to make the measurement.
- d. The initial step in collecting radiated emission data is a spectrum analyzer peak detector mode pre-scanning the measurement frequency range. Significant peaks are then marked and then Quasi Peak detector mode re-measured.
- e. If the Peak Mode measured value compliance with and lower than Quasi Peak Mode Limit, the EUT shall be deemed to meet QP Limits and then no additional QP Mode measurement performed.
- f. For the actual test configuration, please refer to the related Item:EUT Test Photos.


6.1.3. Test Setup and Configuration



For the actual test configuration, please refer to Appendix I: Photographs of the Test Configuration.


6.1.4. Test Result

Test Mode:	Mode 1	Temperature:	25°C
Test Voltage:	24Vdc from DC source	Humidity:	55%RH
Tested By:	Edison Lin	Test Date:	Jul. 24, 2020



Test Mode:	Mode 1	Temperature:	25°C
Test Voltage:	24Vdc from DC source	Humidity:	55%RH
Tested By:	Edison Lin	Test Date:	Jul. 24, 2020

30-1000MHz Polarization: Vertical



No.	Frequency (MHz)	Reading (dBuV/m)	Correct dB/m	Result (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Remark
1	45.8975	47.45	-11.45	36.00	40.00	-4.00	QP
2	68.3975	51.39	-13.74	37.65	40.00	-2.35	QP
3	87.8820	44.61	-17.62	26.99	40.00	-13.01	peak
4	243.0857	40.33	-12.39	27.94	47.00	-19.06	peak
5	728.4457	32.96	-0.04	32.92	47.00	-14.08	peak
6	999.0945	28.71	5.29	34.00	47.00	-13.00	peak

Remark:
 Result = Reading + Correct
 Correct Factor = Antenna Factor + Cable Loss - Amplifier Gain
 Margin = Result - Limit

7. IMMUNITY TEST

7.1. Performance Criteria

According to EN 60601-1-2 standard, the general performance criteria as following:

Type of test	Reaction of ME EQUIPMENT or ME SYSTEM during test	How to continue with testing
Transient(a)	The ME EQUIPMENT or ME SYSTEM is permanently damaged. However, BASIC SAFETY and ESSENTIAL PERFORMANCE continue to be provided.	The test sequence shall be repeated two times with this IMMUNITY TEST LEVEL and polarity. The ME EQUIPMENT or ME SYSTEM passes the test if it continues to provide its BASIC SAFETY and ESSENTIAL PERFORMANCE. If any equipment is damaged, it can continue to be used for the IMMUNITY test for this specific phenomenon, as long as it can be proven (e.g. by RISK MANAGEMENT, engineering analysis, experience, redundancy) that the ability of the ME EQUIPMENT or ME SYSTEM to provide its BASIC SAFETY and ESSENTIAL PERFORMANCE can still be determined while using the damaged equipment. If a PORT of the ME EQUIPMENT or ME SYSTEM is damaged and the ME EQUIPMENT or ME SYSTEM has multiple identical ports, the test shall not be repeated on any of the identical ports. To test the next non-identical PORT, the ME EQUIPMENT or ME SYSTEM shall be restored to normal operation. To continue with the IMMUNITY test of the next EM phenomenon, the ME EQUIPMENT or ME SYSTEM shall be restored to normal operation.
	The ME EQUIPMENT or ME SYSTEM is permanently damaged. BASIC SAFETY or ESSENTIAL PERFORMANCE does not continue to be provided.	The ME EQUIPMENT or ME SYSTEM has failed the test.
Continuous(b)	The ME EQUIPMENT or ME SYSTEM is permanently damaged. However, BASIC SAFETY and ESSENTIAL PERFORMANCE continue to be provided.	The test sequence shall be repeated two times with this IMMUNITY TEST LEVEL and polarity or frequency. BASIC SAFETY and ESSENTIAL PERFORMANCE shall continue to be provided. To continue with the next frequency step the ME EQUIPMENT or ME SYSTEM shall be restored to normal operation.
	The ME EQUIPMENT or ME SYSTEM is permanently damaged. BASIC SAFETY or ESSENTIAL PERFORMANCE does not continue to be provided.	The ME EQUIPMENT or ME SYSTEM has failed the test.
(a) Tests according to IEC 61000-4-2, IEC 61000-4-4, IEC 61000-4-5 and IEC 61000-4-11		
(b) Tests according to IEC 61000-4-3, IEC 61000-4-6 and IEC 61000-4-8		

7.2. Electrostatic Discharge Immunity Test

7.2.1. Test Specification

Standard:	IEC 60601-1-2、 EN 60601-1-2 (refer to IEC/EN 61000-4-2)
Colleteral Standard:	N/A
Discharge Impedance:	330(1±10%)Ω / 150(1±10%)pF
Discharge Voltage:	Air Discharge: ±2kV/±4kV/±8kV/±15kV (Direct)
Polarity:	Contact Discharge: ±2kV/±4kV/±8kV (Direct/Indirect)
	10 times each polarity
Discharge mode of operation:	Single discharges
Discharge Period:	1 second minimum
Repeat test time:	2 times


Note: (1) The test performed of laboratory was according to the client requirements.

7.2.2. Test Procedure

The test generator necessary to perform direct and indirect application of discharges to the EUT in the following manner:

- a. Contact discharge was applied to conductive surfaces and coupling planes of the EUT.
During the test, it was performed with single discharges. For the single discharge time between successive single discharges was at least 1 second. On each pre-selected point at least 10 single discharges (in the most sensitive polarity) shall be applied. Test shall be performed at a maximum repetition rate of one discharge per second.
Vertical Coupling Plane (VCP):
The coupling plane, of dimensions 0.5m x 0.5m, is placed parallel to, and positioned at a distance 0.1m from, the EUT, with the Discharge Electrode touching the coupling plane. The four faces of the EUT will be performed with electrostatic discharge.
Horizontal Coupling Plane (HCP):
The coupling plane is placed under to the EUT. The generator shall be positioned vertically at a distance of 0.1m from the EUT, with the Discharge Electrode touching the coupling plane. The four faces of the EUT will be performed with electrostatic discharge.
- b. Air discharges at insulation surfaces of the EUT.
It was at least ten single discharges with positive and negative at the same selected point.
- c. For the actual test configuration, please refer to the related Item :EUT Test Photos.

7.2.3. Test Setup and Configuration





For the actual test configuration, please refer to Appendix I: Photographs of the Test Configuration.

7.2.4. Test Result

Test Mode:	Mode 1	Temperature:	25°C
Test Voltage:	24Vdc from DC source	Humidity:	45%RH
Discharge of times:	Air: 10 times Contact: 10 times	ATM pressure:	1025 hpa
Tested By:	Rupert Huang	Test Date:	Aug. 25, 2020

Mode	Air Discharge								Contact Discharge							
	2kV		4kV		8kV		15kV		2kV		4kV		8kV		-kV	
Location	+	-	+	-	+	-	+	-	+	-	+	-	+	-	-	-
1~20	PASS	PASS	PASS	PASS	PASS	PASS	PASS	PASS	ND	ND	ND	ND	ND	ND	-	-
Criteria	Please refer to 7.1															
Results	PASS															
Note	There was no abnormal situation during the test compared with initial operation. Pass means that the test performance criteria meet Criteria A which identical with EN 55035. ND: No Discharge, No Arcing; Meets criteria but unable to obtain an electrostatic discharge (ESD) at this test point.															

Mode	HCP Discharge								VCP Discharge							
	2kV		4kV		8kV		-kV		2kV		4kV		8kV		-kV	
Location	+	-	+	-	+	-	+	-	+	-	+	-	+	-	+	-
front	PASS	PASS	PASS	PASS	PASS	PASS	-	-	PASS	PASS	PASS	PASS	PASS	PASS	-	-
rear	PASS	PASS	PASS	PASS	PASS	PASS	-	-	PASS	PASS	PASS	PASS	PASS	PASS	-	-
left	PASS	PASS	PASS	PASS	PASS	PASS	-	-	PASS	PASS	PASS	PASS	PASS	PASS	-	-
right	PASS	PASS	PASS	PASS	PASS	PASS	-	-	PASS	PASS	PASS	PASS	PASS	PASS	-	-
Criteria	Please refer to 7.1															
Results	PASS															
Note	There was no abnormal situation during the test compared with initial operation. Pass means that the test performance criteria meet Criteria A which identical with EN 55035.															



7.3. Radio Frequency Electromagnetic Field Immunity Test

7.3.1. Test Specification

Standard:	IEC 60601-1-2、 EN 60601-1-2 (refer to IEC/EN 61000-4-3)
Colleteral Standard:	N/A
Frequency Range:	80 MHz to 2700MHz
Field Strength:	10V/m (unmodulated)
Modulation:	80%, AM(1 KHz)
Frequency Step:	1% of fundamental
Polarity of Antenna	Vertical and Horizontal
Test Distance:	3 meters
Antenna Height:	1.55 meters
Dwell Time:	3 s
Repeat test time:	2 times


Note: (1) The test performed of laboratory was according to the client requirements.

7.3.2. Test Procedure

The test procedure was in accordance with IEC/EN 61000-4-3.

- a. The testing was performed in a fully anechoic chamber. The transmit antenna was located at a distance of 3 meters from the EUT.
- b. The frequency range is swept from 80 MHz to 2700MHz with the signal 80% amplitude modulated with a 1 KHz sine wave. The rate of sweep did not exceed 1.5×10^{-3} decade/s. Where the frequency range is swept incrementally, the step size was 1% of fundamental.
- c. The dwell time at each frequency shall be not less than the time necessary for the EUT to be able to respond.
- d. The field strength level 80 MHz to 2700MHz was 3V/m.
- e. The test was performed with the EUT exposed to both vertically and horizontally polarized fields on each of the four sides.

7.3.3. Test Setup and Configuration



For the actual test configuration, please refer to Appendix I: Photographs of the Test Configuration.

7.3.4. RS proximity fields from RF Wireless Communication Test Specification

Standard:	IEC 60601-1-2、 EN 60601-1-2 (refer to IEC/EN 61000-4-3)
Colleteral Standard:	N/A
Frequency Range:	See page 5
Field Strength:	
Modulation:	
Polarity of Antenna	Vertical and Horizontal
Test Distance:	3 meters
Dwell Time:	3 s

7.3.5. Test Procedure

The test procedure was in accordance with IEC/EN 61000-4-3.

- a. The testing was performed in a fully anechoic chamber. The transmit antenna was located at a distance of 3 meters from the EUT.
- b. The test frequency is according to page 5 table
- c. The dwell time at each frequency shall be not less than the time necessary for the EUT to be able to respond.
- d. The field strength and modulation are according to page 5 table.
- e. The test was performed with the EUT exposed to both vertically and horizontally polarized fields on each of the four sides.

7.3.6. Test Setup and Configuration

Please refer to Clause 7.3.3.

7.3.7. Test Result

Test Mode:	Mode 1	Temperature:	22°C
Test Voltage:	24Vdc from DC source	Humidity:	58%RH
Tested By:	Rupert Huang	Test Date:	Aug. 11, 2020

Freq. Range (MHz)	Position (Face)	Polarity (H & V)	Field Strength (V/m)	Criteria	Results
80~2700	Front	H&V	10V/m	Please refer to 7.1	PASS
80~2700	Left	H&V	10V/m	Please refer to 7.1	PASS
80~2700	Rear	H&V	10V/m	Please refer to 7.1	PASS
80~2700	Right	H&V	10V/m	Please refer to 7.1	PASS
385	Front/ Left/ Rear/ Right	H&V	27V/m	Please refer to 7.1	PASS
450	Front/ Left/ Rear/ Right	H&V	28V/m	Please refer to 7.1	PASS
710	Front/ Left/ Rear/ Right	H&V	9V/m	Please refer to 7.1	PASS
745	Front/ Left/ Rear/ Right	H&V	9V/m	Please refer to 7.1	PASS
780	Front/ Left/ Rear/ Right	H&V	9V/m	Please refer to 7.1	PASS
810	Front/ Left/ Rear/ Right	H&V	28V/m	Please refer to 7.1	PASS
870	Front/ Left/ Rear/ Right	H&V	28V/m	Please refer to 7.1	PASS
930	Front/ Left/ Rear/ Right	H&V	28V/m	Please refer to 7.1	PASS
1720	Front/ Left/ Rear/ Right	H&V	28V/m	Please refer to 7.1	PASS
1845	Front/ Left/ Rear/ Right	H&V	28V/m	Please refer to 7.1	PASS
1970	Front/ Left/ Rear/ Right	H&V	28V/m	Please refer to 7.1	PASS
2450	Front/ Left/ Rear/ Right	H&V	28V/m	Please refer to 7.1	PASS
5240	Front/ Left/ Rear/ Right	H&V	9V/m	Please refer to 7.1	PASS
5500	Front/ Left/ Rear/ Right	H&V	9V/m	Please refer to 7.1	PASS
5785	Front/ Left/ Rear/ Right	H&V	9V/m	Please refer to 7.1	PASS
Note	There was no abnormal situation during the test compared with initial operation. Pass means that the test performance criteria meet Criteria A which identical with EN 55035.				

7.4. Electrical Fast Transient/Burst Immunity Test

7.4.1. Test Specification


Standard:	IEC 60601-1-2、 EN 60601-1-2 (refer to IEC/EN 61000-4-4)
Colleteral Standard:	N/A
Test Voltage:	2 kV for AC Mains and DC port, 1kV for signal
Polarity:	Positive and Negative
Impulse Frequency:	100 KHz
Impulse wave shape:	5/50 Tr/Th ns
Burst Duration:	0.75ms
Burst Period:	300ms
Test Duration:	1 Minute
Repeat test time:	2 times

Note: (1) The test performed of laboratory was according to the client requirements.

7.4.2. Test Procedure

- a. The EUT was tested with 1000 volt discharges to the AC power input leads, 500 volt discharges to the signal/control ports.
- b. Both positive and negative polarity discharges were applied.
- c. Table-top equipment and equipment normally mounted on ceilings or walls as well as built-in equipment shall be tested with the EUT located $(0,1 \pm 0,01)$ m above the ground reference plane.
- d. The EUT and the auxiliary equipment were placed on a table of 0.8 m heights above a metal ground reference plane. The size of ground plane is greater than 0.8m×1m and project beyond the EUT by at least 0.1m on all sides. The ground plane is connected to the protective earth. The minimum distance between the EUT and all other conductive structures (including the generator, AE and the walls of a shielded room), except the ground reference plane, shall be more than 0,5 m.
- e. The duration time of each test sequential was 1 minute.
- f. The transient/burst waveform was in accordance with IEC/EN 61000-4-4, 5/50ns.

7.4.3. Test Setup and Configuration



For the actual test configuration, please refer to Appendix I: Photographs of the Test Configuration.

7.4.4. Test Result

Test Mode:	Mode 1	Temperature:	22°C
Test Voltage:	24Vdc from DC source	Humidity:	58%RH
Tested By:	Rupert Huang	Test Date:	Aug. 21, 2020

Test Port		Test Levels (kV)						Criteria	Results
		+0.5	-0.5	+1.0	-1.0	+2.0	-2.0		
DC Power port	+	-	-	-	-	PASS	PASS	Please refer to 7.1	PASS
	-	-	-	-	-	PASS	PASS	Please refer to 7.1	PASS
	+ & -	-	-	-	-	PASS	PASS	Please refer to 7.1	PASS
Note		There was no abnormal situation during the test compared with initial operation. Pass means that the test performance criteria meet Criteria A which identical with EN 55035.							

7.5. Surge Immunity Test

7.5.1. Test Specification


Standard:	IEC 60601-1-2、 EN 60601-1-2 (refer to IEC/EN 61000-4-5)
Colleteral Standard:	N/A
Waveform:	1.2/50 (8/20) Tr/Th μ s
Test Voltage:	0.5, 1, 2 kV
Polarity:	Positive and Negative
Phase Angle:	0°/90°/180°/270°
Repetition Rate:	1 per minute
Discharge Times:	5
Repeat test time:	2 times

Note: (1) The test performed of laboratory was according to the client requirements.

7.5.2. Test Procedure

- a. The EUT and the auxiliary equipment were placed on a table of 0.8m heights above a metal ground reference plane. The size of ground plane is greater than 1m×1m and project beyond the EUT by at least 0.1m on all sides. The ground plane is connected to the protective earth. The length of power cord between the coupling device and the EUT shall not exceed 2 meters (provided by the manufacturer).
- b. The EUT was connected to the power mains through a coupling device that directly couples the surge interference signal. The surge noise was applied synchronized to the voltage phase at the zero crossing and the peak value of the AC voltage wave (positive and negative).
- c. The surges were applied line to line and line(s) to earth. When testing line to earth the test voltage was applied successively between each of the lines and earth. Steps up to the test level specified increased the test voltage. All lower levels including the selected test level were tested. The polarity of each surge level included positive and negative test pulses.
- d. If EUT was included telecom port and connected to outdoor directly, test shall be applied to line to earth test using 10/700 surge wave form. If the wave form affects the functioning of high speed data port, the test shall be carried out using 1.2/50 wave form do the test.

7.5.3. Test Setup and Configuration



For the actual test configuration, please refer to Appendix I: Photographs of the Test Configuration.

7.5.4. Test Result

Test Mode:	Mode 1	Temperature:	22°C
Test Voltage:	24Vdc from DC source	Humidity:	58%RH
Tested By:	Rupert Huang	Test Date:	Aug. 21, 2020

Wave Form EUT Ports Tested	1.2/50(8/20)Ti/Th us						Criteria	Results
	Polarity	Phase	Voltage					
			0.5kV	1kV	2kV	-kV		
DC power port + to -	+	-	PASS	PASS	-	-	Please refer to 7.1	PASS
	-	-	PASS	PASS	-	-		
Note	There was no abnormal situation during the test compared with initial operation. Pass means that the test performance criteria meet Criteria A which identical with EN 55035.							

Customer Request:

Wave Form EUT Ports Tested	1.2/50(8/20)Ti/Th us						Criteria	Results
	Polarity	Phase	Voltage					
			0.5kV	1kV	2kV	-kV		
DC power port + to -	+	-	-	-	PASS	-	Please refer to 7.1	PASS
	-	-	-	-	PASS	-		
Note	There was no abnormal situation during the test compared with initial operation. Pass means that the test performance criteria meet Criteria A which identical with EN 55035.							

7.6. Immunity to Conducted Disturbances Induced by RF Fields

7.6.1. Test Specification


Standard:	IEC 60601-1-2、 EN 60601-1-2 (refer to IEC/EN 61000-4-6)
Colleteral Standard:	N/A
Frequency Range:	0.15-80MHz
Field Strength:	3V, 6V (unmodulated, r.m.s.)
Modulation:	80% AM (1 kHz)
Frequency Step:	1% of fundamental
Dwell Time:	3 s
Repeat test time:	2 times

Note: (1) The test performed of laboratory was according to the client requirements.

7.6.2. Test Procedure

- a. The EUT shall be tested within its intended operating and climatic conditions.
- b. The test shall be performed with the test generator connected to each of the coupling and decoupling devices in turn, while the other non-excited RF input ports of the coupling devices are terminated by a 50-ohm load resistor.
- c. The frequency range is swept from 150 kHz to 80 MHz, using the signal level established during the setting process and with a disturbance signal of 80% amplitude. The signal is modulated with a 1 kHz sine wave, pausing to adjust the RF signal level or the switch coupling devices as necessary. The step size shall not exceed 1% of the start and thereafter 1% of the preceding frequency value where the frequency is swept incrementally.
- d. The dwell time at each frequency shall not be less than the time necessary for the EUT to be exercised, and able to respond. Sensitive frequencies such as clock frequencies and harmonics or frequencies of dominant interest, shall be analyzed separately.
- e. For professional healthcare environment shall be test additional 6V ISM band which test spot frequency as state in the report page 4.
- f. Attempts should be made to fully exercise the EUT during test, and to fully interrogate all exercise modes selected for susceptibility.

7.6.3. Test Setup and Configuration



For the actual test configuration, please refer to Appendix I: Photographs of the Test Configuration.

7.6.4. Test Result

Test Mode:	Mode 1	Temperature:	22°C
Test Voltage:	24Vdc from DC source	Humidity:	58%RH
Tested By:	Rupert Huang	Test Date:	Aug. 19, 2020

Test Ports (Mode)	Freq. Range (MHz)	Field Strength	CDN	Criteria	Results
DC Power Port	0.15 ---80	3V	M016(M2)	Please refer to 7.1	PASS
DC Power Port	ISM bands	6V	M016(M2)	Please refer to 7.1	PASS
DC Power Port	Amateur band	6V	M016(M2)	Please refer to 7.1	PASS
Note	There was no abnormal situation during the test compared with initial operation. Pass means that the test performance criteria meet Criteria A which identical with EN 55035.				

Customer Request:

Test Ports (Mode)	Freq. Range (MHz)	Field Strength	CDN	Criteria	Results
DC Power Port	0.15 ---80	10V	M016(M2)	Please refer to 7.1	PASS
Note	There was no abnormal situation during the test compared with initial operation. Pass means that the test performance criteria meet Criteria A which identical with EN 55035.				

7.7. Power frequency magnetic field immunity Test

7.7.1. Test Specification


Standard:	IEC 60601-1-2、 EN 60601-1-2 (refer to IEC/EN 61000-4-8)
Collateral Standard:	N/A
Frequency Range:	50 Hz
Field Strength:	30 A/m 100 A/m for Continuous (Client request) 1000 A/m for short duration (Client request)
Axis:	X, Y, Z
Observation Time:	1 minute 1s for short duration
Inductance Coil:	Rectangular type, 1mx1m
Repeat test time:	2 times

Note: (1) The test performed of laboratory was according to the client requirements.

7.7.2. Test Procedure

- a. The EUT and support equipment, are placed on a table that is 0.8 meter above a metal ground plane measured 1m*1m min. and 0.65mm thick min.
- b. The equipment cabinets shall be connected to the safety earth directly on the GRP via the earth terminal of the EUT.
- c. The cables supplied or recommended by the equipment manufacturer shall be used 1 meter of all cables used shall be exposed to the magnetic field.
- d. The EUT with coil shall be leave all magnetic material and wall 1m away in any axis during the test.
- e. The cable length from generator to coil shall be less than 2m
- f. The background noise shall be 20dB less than test field strength.
- g. Test shall be applied to three axis X, Y, Z and disturbance over 1 minute and short term disturbance over 1 to 3 seconds.
- h. All cables shall be exposed to the magnetic field for 1m of their length.
- i. For magnetic field strength less than or equal to 30A/m the transformer shall be used MC 2630, for magnetic strength greater than 30A/m, the transformer shall be used MFT 100.

7.7.3. Test Setup and Configuration



For the actual test configuration, please refer to Appendix I: Photographs of the Test Configuration.

7.7.4. Test Results

Test Mode:	Mode 1	Temperature:	22°C
Test Voltage:	24Vdc from DC source	Humidity:	58%RH
Tested By:	Rupert Huang	Test Date:	Aug. 21, 2020

Level	Magnetic Field Strength (A/m)	Criteria	Results		
			X	Y	Z
1	1	-	-	-	-
2	3	-	-	-	-
3	10	-	-	-	-
4	30	Please refer to 7.1	PASS	PASS	PASS
5	100	-	-	-	-
X	Special	-	-	-	-
Note	There was no abnormal situation during the test compared with initial operation. Pass means that the test performance criteria meet Criteria A which identical with EN 55035.				

Test Mode:	Mode 1	Temperature:	22°C
Test Voltage:	24Vdc from DC source	Humidity:	58%RH
Tested By:	Rupert Huang	Test Date:	Nov. 2, 2020

Customer Request:


Level	Magnetic Field Strength (A/m)	Criteria	Results		
			X	Y	Z
1	1	-	-	-	-
2	3	-	-	-	-
3	10	-	-	-	-
4	30	-	-	-	-
5	100	Please refer to 7.1	PASS	PASS	PASS
X	Special	-	-	-	-
Note	There was no abnormal situation during the test compared with initial operation. Pass means that the test performance criteria meet Criteria A which identical with EN 55035.				

(Short Term: 1s):



Level	Magnetic Field Strength (A/m)	Criteria	Results		
			X	Y	Z
4	300	-	-	-	-
5	1000	Please refer to 7.1	PASS	PASS	PASS
X	Special	-	-	-	-
Note	There was no abnormal situation during the test compared with initial operation. Pass means that the test performance criteria meet Criteria A which identical with EN 55035.				

Appendix I: Photographs of EMC Test Configuration



Radiated Disturbance
Below 1GHz




Electrostatic Discharge Immunity




Radio Frequency Electromagnetic Field Immunity




Electrical Fast Transient/ Surge Immunity



Immunity to conducted disturbances induced by RF fields



Power frequency magnetic field immunity Test




Appendix II: Photographs of the EUT

Please see the photographs of EUT in the test report no.: 4789565714-EP.


END OF REPORT

Appendix III: Countermeasure file for EMI, EFT and Surge

For EMI test requirements/Class B




Single Output




Dual Output

Model	C1	C2	C3、C4	L1
TRV 1-05Vin	22uF/25V 1206 MLCC	22uF/25V 1206 MLCC	47pF/300VAC Y2	2.2uH
TRV 1-12Vin TRV 1-15Vin TRV 1-24Vin	10uF/50V 1206 MLCC	10uF/50V 1206 MLCC	47pF/300VAC Y2	10uH

For Electrical Fast transient & Surge Immunity test requirements



Model	C1	L	C2	D1	C3	C4
TRV 1-05Vin Dual Output	1000uF/35v /KZM	10uH	1000uF/35v /KZM	SMDJ5.0A	22uF/25V /MLCC	22uF/25V /MLCC
TRV 1-05Vin Single Output	1000uF/35v /KZM	10uH	1000uF/35v /KZM	SMDJ5.0A	22uF/25V /MLCC	N/A



Model	C1	C2	D1	C3	C4
TRV 1-12Vin, 15Vin, 24Vin Dual Output	1000uF/35v /KZM	330uF/50v/KY	SMDJ30A	22uF/25V /MLCC	22uF/25V /MLCC
TRV 1-12Vin, 15Vin, 24Vin Single Output	1000uF/35v /KZM	330uF/50v/KY	SMDJ30A	22uF/25V /MLCC	N/A