

CE EMC Test Report

Report No.: CE970201A04E

Test Model: TMP 15105 - *multiple listing on page 10*

Received Date: Feb. 1, 2008

Test Date: Mar. 27 ~ Apr. 9, 2008 & Oct. 3 ~ 5, 2016

Issued Date: Nov. 28, 2016

Applicant: TRACO ELECTRONIC AG

Address: SIHLBRUGGSTRASSE 111 CH-6340 BAAR, SWITZERLAND

Issued By: Bureau Veritas Consumer Products Services (H.K.) Ltd., Taoyuan Branch

Lab Address: No. 47-2, 14th Ling, Chia Pau Vil., Lin Kou Dist., New Taipei City, Taiwan
(R.O.C.)



This report is for your exclusive use. Any copying or replication of this report to or for any other person or entity, or use of our name or trademark, is permitted only with our prior written permission. This report sets forth our findings solely with respect to the test samples identified herein. The results set forth in this report are not indicative or representative of the quality or characteristics of the lot from which a test sample was taken or any similar or identical product unless specifically and expressly noted. Our report includes all of the tests requested by you and the results thereof based upon the information that you provided to us. You have 60 days from date of issuance of this report to notify us of any material error or omission caused by our negligence, provided, however, that such notice shall be in writing and shall specifically address the issue you wish to raise. A failure to raise such issue within the prescribed time shall constitute your unqualified acceptance of the completeness of this report, the tests conducted and the correctness of the report contents. Unless specific mention, the uncertainty of measurement has been explicitly taken into account to declare the compliance or non-compliance to the specification. The report must not be used by the client to claim product certification, approval, or endorsement by TAF or any government agencies.

Table of Contents

Release Control Record	5
1 Certificate of Conformity.....	6
2 Summary of Test Results	7
2.1 Measurement Uncertainty	8
2.2 Modification Record.....	8
3 General Information.....	9
3.1 Features of EUT	9
3.2 General Description of EUT	9
3.3 Operating Modes of EUT and Determination of Worst Case Operating Mode	10
3.4 Test Program Used and Operation Descriptions.....	11
3.5 Primary Clock Frequencies of Internal Source	11
4 Configuration and Connections with EUT.....	12
4.1 Connection Diagram of EUT and Peripheral Devices.....	12
4.2 Configuration of Peripheral Devices and Cable Connections.....	13
5 Conducted Emission from the AC Mains Power Port - EN 61000-6-3	14
5.1 Limits	14
5.2 Test Instruments	14
5.3 Test Arrangement	15
5.4 Test Results (1)	16
5.5 Test Results (2)	18
5.6 Test Results (3)	20
5.7 Test Results (4)	22
5.8 Test Results (5)	24
5.9 Test Results (6)	26
5.10 Test Results (7)	28
5.11 Test Results (8)	30
5.12 Test Results (9)	32
5.13 Test Results (10)	34
5.14 Test Results (11).....	36
5.15 Test Results (12)	38
5.16 Test Results (13)	40
5.17 Test Results (14)	42
5.18 Test Results (15)	44
5.19 Test Results (16)	46
5.20 Test Results (17)	48
5.21 Test Results (18)	50
5.22 Test Results (19)	52
5.23 Test Results (20)	54
6 Conducted Emission from the AC Mains Power Port - EN 55032.....	56
6.1 Limits	56
6.2 Test Instruments	56
6.3 Test Arrangement	57
6.4 Test Results (1)	58
6.5 Test Results (2)	60

7 Radiated Emission at Frequencies up to 1GHz - EN 61000-6-3	62
7.1 Limits	62
7.2 Test Instruments	62
7.3 Test Arrangement	63
7.4 Test Results (1)	64
7.5 Test Results (2)	66
7.6 Test Results (3)	68
8 Radiated Emission at Frequencies up to 1GHz - EN 55032.....	70
8.1 Limits	70
8.2 Test Instruments	70
8.3 Test Arrangement	71
8.4 Test Results	72
9 Harmonics Current Measurement	74
9.1 Limits	74
9.2 Classification of Equipment	74
9.3 Test Instruments	74
9.4 Test Arrangement	75
9.5 Test Results (1)	76
9.6 Test Results (2)	76
9.7 Test Results (3)	76
10 Voltage Fluctuations and Flicker Measurement	77
10.1 Limits	77
10.2 Test Instruments	77
10.3 Test Arrangement	77
10.4 Test Results (1)	78
10.5 Test Results (2)	79
10.6 Test Results (3)	80
11 Immunity Test	81
11.1 General Immunity Requirements	81
11.2 Performance Criteria	83
12 Electrostatic Discharge Immunity Test (ESD).....	84
12.1 Test Specification	84
12.2 Test Instruments	84
12.3 Test Arrangement	84
12.4 Test Results (1)	86
12.5 Test Results (2)	88
13 Radiated, Radio-frequency, Electromagnetic Field Immunity Test (RS)	90
13.1 Test Specification	90
13.2 Test Instruments	90
13.3 Test Arrangement	91
13.4 Test Results	92
14 Electrical Fast Transient/Burst Immunity Test (EFT).....	93
14.1 Test Specification	93
14.2 Test Instruments	93
14.3 Test Arrangement	94
14.4 Test Results (1)	95
14.5 Test Results (2)	95
14.6 Test Results (3)	95

15 Surge Immunity Test.....	96
15.1 Test Specification.....	96
15.2 Test Instruments	96
15.3 Test Arrangement	97
15.4 Test Results	99
16 Immunity to Conducted Disturbances Induced by RF Fields (CS).....	100
16.1 Test Specification.....	100
16.2 Test Instruments	100
16.3 Test Arrangement	101
16.4 Test Results	102
17 Power Frequency Magnetic Field Immunity Test.....	103
17.1 Test Specification.....	103
17.2 Test Instruments	103
17.3 Test Arrangement	103
17.4 Test Results	105
18 Voltage Dips and Interruptions	106
18.1 Test Specification.....	106
18.2 Test Instruments	106
18.3 Test Arrangement	107
18.4 Test Results	108
19 Pictures of Test Arrangements	109
19.1 Conducted Emission from the AC Mains Power Port - EN 61000-6-3.....	109
19.2 Conducted Emission from the AC Mains Power Port - EN 55032	110
19.3 Radiated Emission at Frequencies up to 1GHz - EN 61000-6-3	111
19.4 Radiated Emission at Frequencies up to 1GHz - EN 55032.....	112
19.5 Harmonics Current, Voltage Fluctuations and Flicker Measurement.....	113
19.6 Electrostatic Discharge Immunity Test (ESD)	115
19.7 Radio-frequency, Electromagnetic Field Immunity Test (RS).....	117
19.8 Electrical Fast Transient/Burst Immunity Test (EFT).....	120
19.9 Surge Immunity Test.....	122
19.10 Conducted Disturbances Induced by RF Fields (CS)	123
19.11 Power Frequency Magnetic Field Immunity Test (PBMF)	125
19.12 Voltage Dips and Interruptions	127
Appendix – Information on the Testing Laboratories	129

Release Control Record

Issue No.	Description	Date Issued
CE970201A04E	Original release.	Nov. 28, 2016

1 Certificate of Conformity

Product: AC/DC Power Modules

Brand:



Test Model: TMP 15105 - *multiple listing on page 10*

Sample Status: R&D sample

Applicant: TRACO ELECTRONIC AG

Test Date: Mar. 27 ~ Apr. 9, 2008 & Oct. 3 ~ 5, 2016

Standards: EN 61000-6-3:2007+ A1:2011

EN 55032:2012 +AC:2013, Class B

EN 61000-3-2:2014

EN 61000-3-3:2013

EN 61000-6-1:2007

EN 55024:2010

IEC 61000-4-2:2008 ED. 2.0

IEC 61000-4-3:2010 ED. 3.2

IEC 61000-4-4:2012 ED. 3.0

IEC 61000-4-5:2014 ED. 3.0

IEC 61000-4-6:2013 ED. 4.0

IEC 61000-4-8:2009 ED. 2.0

IEC 61000-4-11:2004 ED. 2.0

The above equipment has been tested by **Bureau Veritas Consumer Products Services (H.K.) Ltd., Taoyuan Branch**, and found compliance with the requirement of the above standards. The test record, data evaluation & Equipment Under Test (EUT) configurations represented herein are true and accurate accounts of the measurements of the sample's EMC characteristics under the conditions specified in this report.

Prepared by : Alice Chang , **Date:** Nov. 28, 2016

Alice Chang / Specialist

Approved by : Henry Lai , **Date:** Nov. 28, 2016

Henry Lai / Director

2 Summary of Test Results

Emission				
Standard	Clause	Test Item	Result/Remarks	Verdict
EN 61000-6-3: 2007+ A1: 2011	5.1	Mains terminal disturbance voltage	Minimum passing Class B margin is -4.53 dB at 0.548 MHz	Pass
	5.2	Asymmetric mode conducted emission at telecommunication ports	Without telecom port of the EUT	N/A
	6.1	Radiated disturbance 30-1000 MHz	Minimum passing Class B margin is -2.62 dB at 51.36 MHz	Pass
	6.2	Radiated emission above 1GHz	Not applicable because the EUT's highest frequency is below 108 MHz	N/A
EN 55032:2012 +AC:2013	A.3	Conducted emission from the AC mains power port	Minimum passing Class B margin is -0.27 dB at 0.39609 MHz	Pass
	A.3	Asymmetric mode conducted emission at telecommunication ports	Without telecom port of the EUT	N/A
	A.2	Radiated emission 30-1000 MHz	Minimum passing Class B margin is -0.97 dB at 95.69 MHz	Pass
	A.2	Radiated emission above 1GHz	Not applicable because the EUT's highest frequency is below 108 MHz	N/A
EN 61000-3-2:2014	-	Harmonic current emissions	The power consumption of EUT is less than 75W and no limits apply.	Pass
EN 61000-3-3:2013	-	Voltage fluctuations and flicker	$P_{st} \leq 1.0$ $d_{max} \leq 4\%$ $P_{lt} \leq 0.65$ $d_c \leq 3.3\%$ $T_{max} \leq 500ms$	Pass

Immunity (EN 61000-6-1:2007 & EN 55024:2010)			
Basic standard	Test Item	Result/Remarks	Verdict
IEC 61000-4-2:2008 ED. 2.0	Electrostatic discharges (ESD)	Performance Criterion A	Pass
IEC 61000-4-3:2010 ED. 3.2	Continuous radiated disturbances (RS)	Performance Criterion A	Pass
IEC 61000-4-4:2012 ED. 3.0	Electrical fast transients (EFT)	Performance Criterion B	Pass
IEC 61000-4-5:2014 ED. 3.0	Surges	Performance Criterion A	Pass
IEC 61000-4-6:2013 ED. 4.0	Continuous conducted disturbances (CS)	Performance Criterion A	Pass
IEC 61000-4-8:2009 ED. 2.0	Power-frequency magnetic fields (PFMF)	Performance Criterion A	Pass
IEC 61000-4-11:2004 ED. 2.0	Voltage dips and interruptions	Voltage Dips: i) 0% residual – Performance Criterion A ii) 70% residual – Performance Criterion A Voltage Interruptions: i) 0% residual – Performance Criterion B	Pass

Note:

- There is no deviation to the applied test methods and requirements covered by the scope of this report.
- The above IEC basic standards are applied with latest version if customer has no special requirement.
- N/A: Not Applicable.

2.1 Measurement Uncertainty

Where relevant, the following measurement uncertainty levels have been estimated for tests performed on the EUT as specified in CISPR 16-4-2:

The listed uncertainties are the worst case uncertainty for the entire range of measurement. Please note that the uncertainty values are provided for informational purposes only and are not used in determining the PASS/FAIL results.

<For EN 61000-6-3>

Measurement	Expended Uncertainty (k=2) (±)	Maximum allowable uncertainty (±)
Conducted emission from AC mains power port using AMN, 150kHz ~ 30MHz	2.55 dB	3.4 dB (U_{cispr})
Radiated emission, 30MHz ~ 1GHz	3.74 dB	6.3 dB (U_{cispr})

<For EN 55032>

Measurement	Expended Uncertainty (k=2) (±)	Maximum allowable uncertainty (±)
Conducted emission from AC mains power port using AMN, 150kHz ~ 30MHz	2.78 dB	3.4 dB (U_{cispr})
Radiated emission, 30MHz ~ 1GHz	4.88 dB	6.3 dB (U_{cispr})

2.2 Modification Record

There were no modifications required for compliance.

3 General Information

3.1 Features of EUT

The tests reported herein were performed according to the method specified by TRACO ELECTRONIC AG, for detailed feature description, please refer to the manufacturer's specifications or user's manual.

3.2 General Description of EUT

Product	AC/DC Power Modules
Brand	TRACO® POWER
Test Model	TMP 15105 - <i>multiple listing as below</i>
Model Difference	Refer to table as below
Sample Status	R&D sample
Operating Software	N/A
Power Supply Rating	Refer to table as below
Accessory Device	N/A
Data Cable Supplied	N/A

Note:

1. This report is base on ADT report with Reference No.: CE970201A04.
The original report was issued by Advance Data Technology Corp. (ADT Corp.) on Apr. 16, 2008.
ADT Corp. is one of Bureau Veritas family and she has fully transferred all its test facilities, staffs & service system to Bureau Veritas Consumer Products Services (Hong Kong) Limited, Taoyuan Branch in 2008.
2. This report is issued for following reason:
 - ◆ Upgraded test standard to latest version.
 - ◆ Deleted standard: EN55022
 - ◆ Added standard: EN55032 & EN55024
3. The EUT is an AC/DC Power Modules (AC 2-pin), and it has the following models, which are identical to each other except for their rating differences , as the following:

Model No.	Specification		
	AC I/P	DC O/P	
TMP 15105, TMP 15105C	100-240V, 380mA, 50-60Hz	5VDC/3000mA	Single output
TMP 15112, TMP 15112C		12VDC/1250mA	Single output
TMP 15115, TMP 15115C		15VDC/1000mA	Single output
TMP 15124, TMP 15124C		24VDC/625mA	Single output
TMP 15148, TMP 15148C		48VDC/310mA	Single output
TMP 15212, TMP 15212C		±12VDC/ ±625mA	Dual output
TMP 15215, TMP 15215C		±15VDC/ ±500mA	Dual output
TMP 15252, TMP 15252C		5VDC/1500mA, 12VDC/625mA	Dual output
TMP 15512, TMP 15512C		5VDC/2000mA, ±12VDC/±200mA	Triple output
TMP 15515, TMP 15515C		5VDC/2000mA, ±15VDC/±150mA	Triple output

4. For a more detailed features description, please refer to the manufacturer's specifications or the User's Manual.

3.3 Operating Modes of EUT and Determination of Worst Case Operating Mode

1. The EUT was pre-tested under operating and standby condition and the worst emission level was found under **operating condition**.
2. For radiated emission evaluation (only for standard EN 55032), 230Vac/50Hz & 110Vac/60Hz had been covered during the pre-test. The worst data was found at **110Vac/60Hz** and recorded in the applied test report.
3. During the test, the above models were pre-tested, and the worst radiated emission levels were found on **Model: TMP-15105, TMP-15252C, TMP-15512C**, therefore according as per pre-test result and client's requirement, the final test modes were as the following:

Test Item	Test Mode	Model No.	Test Condition	Input power
Conducted Test <For EN 61000-6-3>	Mode 1	TMP 15105	Full load	230V/ 50Hz
	Mode 2	TMP 15112		
	Mode 3	TMP 15115		
	Mode 4	TMP 15124		
	Mode 5	TMP 15148		
	Mode 6	TMP 15212		
	Mode 7	TMP 15215		
	Mode 8	TMP 15252		
	Mode 9	TMP 15512		
	Mode 10	TMP 15515		
	Mode 11	TMP 15105C		
	Mode 12	TMP 15112C		
	Mode 13	TMP 15115C		
	Mode 14	TMP 15124C		
	Mode 15	TMP 15148C		
	Mode 16	TMP 15212C		
	Mode 17	TMP 15215C		
	Mode 18	TMP 15252C		
	Mode 19	TMP 15512C		
	Mode 20	TMP 15515C		
Radiated Test <For EN 61000-6-3>	Mode 1	TMP 15105	Full load	230V/ 50Hz
	Mode 16	TMP 15252C		
	Mode 19	TMP 15512C		
Conducted Test <For EN 55032>	Mode 1	TMP 15105	Full load	110V/ 60Hz 230V/ 50Hz
Radiated Test <For EN 55032>	Mode 1	TMP 15105	Full load	110V/ 60Hz
Harmonic, Flicker, Immunity Tests <Except for Surge>	Mode 1	TMP 15105	Full load	230V/ 50Hz
	Mode 16	TMP 15252C		
	Mode 19	TMP 15512C		
Surge Test	Mode 1	TMP 15105	Full load	230V/ 50Hz

3.4 Test Program Used and Operation Descriptions

- ◆ **For Conducted & Radiated tests:**

Set the EUT under full resistor load.

- ◆ **For Harmonics, Flicker tests:**

Connected a resistor load to DC output port of EUT to make EUT have maximum power consumption.

- ◆ **For Immunity tests:**

Connected a resistor load to DC output port of EUT to make EUT have maximum power consumption and then multimeter was used to monitor voltage of output.


3.5 Primary Clock Frequencies of Internal Source

The highest frequency generated or used within the EUT or on which the EUT operates or tunes is below 108MHz, provided by TRACO ELECTRONIC AG, for detailed internal source, please refer to the manufacturer's specifications.


4 Configuration and Connections with EUT

4.1 Connection Diagram of EUT and Peripheral Devices


Emission tests (Harmonics & Flicker included):



Harmonics, Flicker tests:



Immunity tests:



4.2 Configuration of Peripheral Devices and Cable Connections

Emission tests (Harmonics & Flicker included):

ID	Product	Brand	Model No.	Serial No.	FCC ID	Remarks
A.	DUMMY LOAD	N/A	N/A	N/A	N/A	Supplied by client

Note: All power cords of the above support units are non-shielded (1.8m).

ID	Descriptions	Qty.	Length (m)	Shielding (Yes/No)	Cores (Qty.)	Remarks
1.	DC cable	1	0.2	N	0	Supplied by client
2.	AC power cord	1	1.8	N	0	Supplied by client

Note: The core(s) is(are) originally attached to the cable(s).

Harmonics & Flicker, Immunity tests:

ID	Product	Brand	Model No.	Serial No.	FCC ID	Remarks
A.	DUMMY LOAD	N/A	N/A	N/A	N/A	Supplied by client
B.	Multimeter	YFE	YF-370A	N/A	N/A	Provided by Lab

Note: All power cords of the above support units are non-shielded (1.8m).

ID	Descriptions	Qty.	Length (m)	Shielding (Yes/No)	Cores (Qty.)	Remarks
1.	DC cable	1	0.2	N	0	Supplied by client
2.	AC power cord	1	1.8	N	0	Supplied by client
3.	Data cable	1	0.5	N	0	Provided by Lab

Note: The core(s) is(are) originally attached to the cable(s).

5 Conducted Emission from the AC Mains Power Port - EN 61000-6-3

5.1 Limits

Standard	Frequency range (MHz)	Quasi-peak dB(uV)	Average dB(uV)
EN 61000-6-3	0.15 - 0.5	66 - 56	56 - 46
	0.50 - 5.0	56	46
	5.0 - 30.0	60	50

NOTE: (1) The lower limit shall apply at the transition frequencies.

(2) The limit decreases in line with the logarithm of the frequency in the range of 0.15 to 0.50 MHz.

5.2 Test Instruments

DESCRIPTION & MANUFACTURER	MODEL NO.	SERIAL NO.	CALIBRATED UNTIL
ROHDE & SCHWARZ Test Receiver	ESCS30	834115/016	Jan. 06, 2009
SCHWARZBECK Artificial Mains Network (For EUT)	NSLK 8128	8128-244	Jul. 25, 2008
LISN With Adapter (for EUT)	AD10	C03Ada-001	Jul. 25, 2008
EMCO L.I.S.N. (For peripherals)	3825/2	9504-2359	Jun. 27, 2008
Software	ADT_Cond_V7.3.5	NA	NA
Software	ADT_ISN_V7.3.5	NA	NA
RF cable (JYEBAO)	5D-FB	Cable-C03.01	Jan. 09, 2009
LYNICS Terminator (For EMCO LISN)	0900510	E1-01-300	Jan. 27, 2009
LYNICS Terminator (For EMCO LISN)	0900510	E1-01-301	Jan. 27, 2009

NOTE: 1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.

2. The test was performed in ADT Shielded Room No. 3.


3. The VCCI Site Registration No. C-274.

4. Test date: Mar. 27 ~ Apr. 9, 2008

5.3 Test Arrangement

- a. The EUT was placed 0.4 meters from the conducting wall of the shielded room with EUT being connected to the power mains through a line impedance stabilization network (LISN). Other support units were connected to the power mains through another LISN. The two LISNs provide 50 Ohm/ 50uH of coupling impedance for the measuring instrument.
- b. Both lines of the power mains connected to the EUT were checked for maximum conducted interference.
- c. The test results of conducted emissions at mains ports are recorded of six worst margins for quasi-peak (mandatory) [and average (if necessary)] values against the limits at frequencies of interest unless the margin is 20 dB or greater.

Note: The resolution bandwidth and video bandwidth of test receiver is 9kHz for quasi-peak detection (QP) and average detection (AV) at frequency 0.15MHz-30MHz.



Note:

1. Support units were connected to second LISN.
2. Both of LISNs (AMN) are 80cm from EUT and at least 80cm from other units and other metal planes support units.

For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.


5.4 Test Results (1)

Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 1		

Phase Of Power : Line (L)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.271	0.20	48.58	-	48.78	-	61.08	51.08	-12.30	-
2	0.404	0.20	49.35	41.38	49.55	41.58	57.77	47.77	-8.22	-6.19
3	0.552	0.20	44.36	-	44.56	-	56.00	46.00	-11.44	-
4	0.810	0.20	44.93	-	45.13	-	56.00	46.00	-10.87	-
5	2.352	0.22	41.82	-	42.04	-	56.00	46.00	-13.96	-
6	4.867	0.34	28.62	-	28.96	-	56.00	46.00	-27.04	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 1		

Phase Of Power : Neutral (N)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.271	0.20	48.54	-	48.74	-	61.08	51.08	-12.34	-
2	0.402	0.20	48.72	40.76	48.92	40.96	57.80	47.80	-8.88	-6.84
3	0.533	0.20	48.96	35.59	49.16	35.79	56.00	46.00	-6.84	-10.21
4	1.681	0.20	42.91	-	43.11	-	56.00	46.00	-12.89	-
5	2.402	0.22	42.72	-	42.94	-	56.00	46.00	-13.06	-
6	4.258	0.31	33.61	-	33.92	-	56.00	46.00	-22.08	-
7	5.816	0.39	31.96	-	32.35	-	60.00	50.00	-27.65	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.



5.5 Test Results (2)


Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 2		

Phase Of Power : Line (L)

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.162	0.16	46.45	-	46.61	-	65.38	55.38	-18.76	-
2	0.276	0.20	48.47	-	48.67	-	60.93	50.93	-12.26	-
3	0.404	0.20	49.41	41.45	49.61	41.65	57.77	47.77	-8.16	-6.12
4	0.677	0.20	45.17	-	45.37	-	56.00	46.00	-10.63	-
5	1.656	0.20	42.49	-	42.69	-	56.00	46.00	-13.31	-
6	2.352	0.22	41.88	-	42.10	-	56.00	46.00	-13.90	-
7	4.934	0.35	30.81	-	31.16	-	56.00	46.00	-24.84	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 2		

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.216	0.20	40.42	-	40.62	-	62.96	52.96	-22.34	-
2	0.267	0.20	47.56	-	47.76	-	61.20	51.20	-13.44	-
3	0.404	0.20	47.92	40.66	48.12	40.86	57.77	47.77	-9.65	-6.91
4	0.560	0.20	49.16	35.88	49.36	36.08	56.00	46.00	-6.64	-9.92
5	0.966	0.20	44.33	-	44.53	-	56.00	46.00	-11.47	-
6	1.816	0.20	43.30	-	43.50	-	56.00	46.00	-12.50	-
7	2.477	0.22	42.46	-	42.68	-	56.00	46.00	-13.32	-
8	5.876	0.39	32.15	-	32.54	-	60.00	50.00	-27.46	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.



5.6 Test Results (3)


Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 3		

Phase Of Power : Line (L)

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.274	0.20	48.30	-	48.50	-	61.01	51.01	-12.51	-
2	0.404	0.20	49.27	41.38	49.47	41.58	57.77	47.77	-8.30	-6.19
3	0.814	0.20	45.67	-	45.87	-	56.00	46.00	-10.13	-
4	1.648	0.20	43.46	-	43.66	-	56.00	46.00	-12.34	-
5	2.371	0.22	41.97	-	42.19	-	56.00	46.00	-13.81	-
6	5.168	0.36	29.31	-	29.67	-	60.00	50.00	-30.33	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 3		

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.162	0.16	46.67	-	46.83	-	65.38	55.38	-18.54	-
2	0.272	0.20	47.92	-	48.12	-	61.05	51.05	-12.93	-
3	0.404	0.20	48.62	41.22	48.82	41.42	57.77	47.77	-8.95	-6.35
4	0.545	0.20	49.64	41.13	49.84	41.33	56.00	46.00	-6.16	-4.67
5	0.947	0.20	44.67	-	44.87	-	56.00	46.00	-11.13	-
6	1.785	0.20	43.66	-	43.86	-	56.00	46.00	-12.14	-
7	2.492	0.22	42.82	-	43.04	-	56.00	46.00	-12.96	-
8	5.254	0.36	33.37	-	33.73	-	60.00	50.00	-26.27	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.



5.7 Test Results (4)


Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 4		

Phase Of Power : Line (L)

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.189	0.19	43.28	-	43.47	-	64.07	54.07	-20.60	-
2	0.276	0.20	48.01	-	48.21	-	60.93	50.93	-12.72	-
3	0.814	0.20	45.66	-	45.86	-	56.00	46.00	-10.14	-
4	1.680	0.20	42.63	-	42.83	-	56.00	46.00	-13.17	-
5	2.363	0.22	41.43	-	41.65	-	56.00	46.00	-14.35	-
6	5.051	0.35	28.86	-	29.21	-	60.00	50.00	-30.79	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 4		

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.150	0.15	48.26	-	48.41	-	66.00	56.00	-17.59	-
2	0.279	0.20	47.66	-	47.86	-	60.85	50.85	-12.99	-
3	0.420	0.20	47.73	36.16	47.93	36.36	57.46	47.46	-9.53	-11.10
4	0.548	0.20	49.58	41.27	49.78	41.47	56.00	46.00	-6.22	-4.53
5	0.955	0.20	44.77	-	44.97	-	56.00	46.00	-11.03	-
6	1.809	0.20	43.99	-	44.19	-	56.00	46.00	-11.81	-
7	2.598	0.23	42.71	-	42.94	-	56.00	46.00	-13.06	-
8	5.313	0.37	33.17	-	33.54	-	60.00	50.00	-26.46	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.



5.8 Test Results (5)


Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 5		

Phase Of Power : Line (L)

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.274	0.20	48.28	-	48.48	-	61.00	51.00	-12.52	-
2	0.412	0.20	49.28	42.01	49.48	42.21	57.61	47.61	-8.13	-5.40
3	0.834	0.20	45.94	33.53	46.14	33.73	56.00	46.00	-9.86	-12.27
4	1.637	0.20	43.56	-	43.76	-	56.00	46.00	-12.24	-
5	2.418	0.22	41.63	-	41.85	-	56.00	46.00	-14.15	-
6	4.363	0.32	32.93	-	33.25	-	56.00	46.00	-22.75	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 5		

Phase Of Power : Neutral (N)

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.158	0.16	47.19	-	47.35	-	65.55	55.55	-18.20	-
2	0.279	0.20	47.66	-	47.86	-	60.85	50.85	-12.99	-
3	0.405	0.20	48.44	41.71	48.64	41.91	57.75	47.75	-9.11	-5.84
4	0.541	0.20	49.47	41.19	49.67	41.39	56.00	46.00	-6.33	-4.61
5	0.822	0.20	44.69	-	44.89	-	56.00	46.00	-11.11	-
6	1.781	0.20	43.69	-	43.89	-	56.00	46.00	-12.11	-
7	2.570	0.23	42.66	-	42.89	-	56.00	46.00	-13.11	-
8	5.594	0.38	33.01	-	33.39	-	60.00	50.00	-26.61	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.



5.9 Test Results (6)


Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 6		

Phase Of Power : Line (L)

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.162	0.16	47.92	-	48.08	-	65.38	55.38	-17.29	-
2	0.278	0.20	44.46	-	44.66	-	60.89	50.89	-16.23	-
3	0.552	0.20	38.52	-	38.72	-	56.00	46.00	-17.28	-
4	1.109	0.20	38.89	-	39.09	-	56.00	46.00	-16.91	-
5	2.488	0.22	36.38	-	36.60	-	56.00	46.00	-19.40	-
6	3.668	0.28	33.29	-	33.57	-	56.00	46.00	-22.43	-
7	6.012	0.40	33.08	-	33.48	-	60.00	50.00	-26.52	-
8	10.512	0.61	30.96	-	31.57	-	60.00	50.00	-28.43	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 6		

Phase Of Power : Neutral (N)

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.213	0.20	42.40	-	42.60	-	63.08	53.08	-20.48	-
2	0.276	0.20	47.19	-	47.39	-	60.93	50.93	-13.54	-
3	0.416	0.20	45.85	-	46.05	-	57.54	47.54	-11.49	-
4	0.978	0.20	40.55	-	40.75	-	56.00	46.00	-15.25	-
5	2.387	0.22	39.58	-	39.80	-	56.00	46.00	-16.20	-
6	3.238	0.26	38.53	-	38.79	-	56.00	46.00	-17.21	-
7	6.043	0.40	32.32	-	32.72	-	60.00	50.00	-27.28	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.



5.10 Test Results (7)


Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 7		

Phase Of Power : Line (L)

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.154	0.15	49.49	-	49.64	-	65.79	55.79	-16.14	-
2	0.271	0.20	44.19	-	44.39	-	61.08	51.08	-16.69	-
3	0.404	0.20	42.92	-	43.12	-	57.77	47.77	-14.65	-
4	0.560	0.20	42.35	-	42.55	-	56.00	46.00	-13.45	-
5	1.094	0.20	41.62	-	41.82	-	56.00	46.00	-14.18	-
6	2.477	0.22	39.60	-	39.82	-	56.00	46.00	-16.18	-
7	4.656	0.33	36.55	-	36.88	-	56.00	46.00	-19.12	-
8	9.461	0.57	33.57	-	34.14	-	60.00	50.00	-25.86	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 7		

Phase Of Power : Neutral (N)

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.154	0.15	49.29	-	49.44	-	65.79	55.79	-16.34	-
2	0.278	0.20	47.32	-	47.52	-	60.89	50.89	-13.37	-
3	0.412	0.20	47.09	-	47.29	-	57.61	47.61	-10.32	-
4	0.563	0.20	43.27	-	43.47	-	56.00	46.00	-12.53	-
5	0.966	0.20	41.47	-	41.67	-	56.00	46.00	-14.33	-
6	2.379	0.22	40.17	-	40.39	-	56.00	46.00	-15.61	-
7	3.227	0.26	39.68	-	39.94	-	56.00	46.00	-16.06	-
8	5.027	0.35	34.17	-	34.52	-	60.00	50.00	-25.48	-
9	9.227	0.56	30.17	-	30.73	-	60.00	50.00	-29.27	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.



5.11 Test Results (8)


Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 8		

Phase Of Power : Line (L)

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.154	0.15	50.14	-	50.29	-	65.78	55.78	-15.49	-
2	0.271	0.20	45.21	-	45.41	-	61.08	51.08	-15.67	-
3	0.404	0.20	43.11	-	43.31	-	57.77	47.77	-14.46	-
4	0.560	0.20	43.25	-	43.45	-	56.00	46.00	-12.55	-
5	1.094	0.20	42.85	-	43.05	-	56.00	46.00	-12.95	-
6	2.477	0.22	40.12	-	40.34	-	56.00	46.00	-15.66	-
7	4.656	0.33	37.86	-	38.19	-	56.00	46.00	-17.81	-
8	9.461	0.57	34.25	-	34.82	-	60.00	50.00	-25.18	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 8		

Phase Of Power : Neutral (N)

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.166	0.17	48.13	-	48.30	-	65.17	55.17	-16.88	-
2	0.279	0.20	47.63	-	47.83	-	60.85	50.85	-13.02	-
3	0.408	0.20	48.51	38.45	48.71	38.65	57.69	47.69	-8.98	-9.04
4	0.559	0.20	44.58	-	44.78	-	56.00	46.00	-11.22	-
5	0.951	0.20	42.64	-	42.84	-	56.00	46.00	-13.16	-
6	2.348	0.22	40.98	-	41.20	-	56.00	46.00	-14.80	-
7	3.367	0.27	38.92	-	39.19	-	56.00	46.00	-16.81	-
8	5.918	0.40	36.34	-	36.74	-	60.00	50.00	-23.26	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.



5.12 Test Results (9)


Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 9		

Phase Of Power : Line (L)

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.162	0.16	48.97	-	49.13	-	65.38	55.38	-16.24	-
2	0.268	0.20	44.25	-	44.45	-	61.17	51.17	-16.72	-
3	0.555	0.20	43.98	-	44.18	-	56.00	46.00	-11.82	-
4	1.122	0.20	44.02	-	44.22	-	56.00	46.00	-11.78	-
5	2.520	0.23	41.62	-	41.85	-	56.00	46.00	-14.15	-
6	5.000	0.35	38.05	-	38.40	-	56.00	46.00	-17.60	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 9		

Phase Of Power : Neutral (N)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.189	0.19	45.40	-	45.59	-	64.08	54.08	-18.49	-
2	0.276	0.20	47.84	-	48.04	-	60.93	50.93	-12.89	-
3	0.408	0.20	48.65	38.54	48.85	38.74	57.69	47.69	-8.84	-8.95
4	0.836	0.20	43.56	-	43.76	-	56.00	46.00	-12.24	-
5	1.086	0.20	42.53	-	42.73	-	56.00	46.00	-13.27	-
6	2.391	0.22	41.98	-	42.20	-	56.00	46.00	-13.80	-
7	5.000	0.35	36.35	-	36.70	-	56.00	46.00	-19.30	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.



5.13 Test Results (10)


Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 10		

Phase Of Power : Line (L)

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.212	0.20	43.06	-	43.26	-	63.11	53.11	-19.85	-
2	0.408	0.20	44.41	-	44.61	-	57.69	47.69	-13.08	-
3	0.552	0.20	43.86	-	44.06	-	56.00	46.00	-11.94	-
4	1.102	0.20	43.52	-	43.72	-	56.00	46.00	-12.28	-
5	2.539	0.23	41.94	-	42.17	-	56.00	46.00	-13.83	-
6	4.992	0.35	37.81	-	38.16	-	56.00	46.00	-17.84	-
7	9.313	0.57	34.68	-	35.25	-	60.00	50.00	-24.75	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 10		

Phase Of Power : Neutral (N)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.163	0.16	48.49	-	48.65	-	65.30	55.30	-16.65	-
2	0.279	0.20	47.75	-	47.95	-	60.85	50.85	-12.90	-
3	0.420	0.20	48.96	37.09	49.16	37.29	57.46	47.46	-8.30	-10.17
4	0.563	0.20	45.31	-	45.51	-	56.00	46.00	-10.49	-
5	0.982	0.20	44.54	-	44.74	-	56.00	46.00	-11.26	-
6	2.391	0.22	43.02	-	43.24	-	56.00	46.00	-12.76	-
7	5.000	0.35	37.14	-	37.49	-	56.00	46.00	-18.51	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.



5.14 Test Results (11)


Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 11		

Phase Of Power : Line (L)

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.150	0.15	49.18	-	49.33	-	66.00	56.00	-16.67	-
2	0.267	0.20	46.23	-	46.43	-	61.20	51.20	-14.77	-
3	0.404	0.20	44.57	-	44.77	-	57.77	47.77	-13.00	-
4	0.681	0.20	41.82	-	42.02	-	56.00	46.00	-13.98	-
5	1.766	0.20	36.59	-	36.79	-	56.00	46.00	-19.21	-
6	2.664	0.23	34.91	-	35.14	-	56.00	46.00	-20.86	-
7	6.801	0.44	21.95	-	22.39	-	60.00	50.00	-37.61	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 11		

Phase Of Power : Neutral (N)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.166	0.17	46.59	-	46.76	-	65.18	55.18	-18.42	-
2	0.271	0.20	45.10	-	45.30	-	61.08	51.08	-15.78	-
3	0.545	0.20	44.75	-	44.95	-	56.00	46.00	-11.05	-
4	0.810	0.20	41.68	-	41.88	-	56.00	46.00	-14.12	-
5	2.621	0.23	39.15	-	39.38	-	56.00	46.00	-16.62	-
6	6.129	0.41	22.63	-	23.04	-	60.00	50.00	-36.96	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.



5.15 Test Results (12)


Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 12		

Phase Of Power : Line (L)

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.150	0.15	50.19	-	50.34	-	66.00	56.00	-15.66	-
2	0.173	0.17	47.22	-	47.39	-	64.79	54.79	-17.40	-
3	0.912	0.20	41.01	-	41.21	-	56.00	46.00	-14.79	-
4	1.992	0.20	44.66	-	44.86	-	56.00	46.00	-11.14	-
5	2.750	0.24	44.25	-	44.49	-	56.00	46.00	-11.51	-
6	4.770	0.34	39.49	-	39.83	-	56.00	46.00	-16.17	-
7	8.313	0.52	34.47	-	34.99	-	60.00	50.00	-25.01	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 12		

Phase Of Power : Neutral (N)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.170	0.17	48.03	-	48.20	-	64.98	54.98	-16.78	-
2	0.273	0.20	50.93	43.23	51.13	43.43	61.02	51.02	-9.89	-7.59
3	0.404	0.20	45.20	-	45.40	-	57.77	47.77	-12.37	-
4	0.814	0.20	45.06	-	45.26	-	56.00	46.00	-10.74	-
5	1.488	0.20	43.71	-	43.91	-	56.00	46.00	-12.09	-
6	1.910	0.20	44.68	-	44.88	-	56.00	46.00	-11.12	-
7	2.684	0.23	44.79	-	45.02	-	56.00	46.00	-10.98	-
8	5.000	0.35	40.16	-	40.51	-	56.00	46.00	-15.49	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.



5.16 Test Results (13)


Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 13		

Phase Of Power : Line (L)

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.150	0.15	48.34	-	48.49	-	66.00	56.00	-17.51	-
2	0.412	0.20	45.11	-	45.31	-	57.61	47.61	-12.30	-
3	0.564	0.20	46.58	36.44	46.78	36.64	56.00	46.00	-9.22	-9.36
4	1.145	0.20	45.09	-	45.29	-	56.00	46.00	-10.71	-
5	2.551	0.23	43.46	-	43.69	-	56.00	46.00	-12.31	-
6	4.501	0.33	40.82	-	41.15	-	56.00	46.00	-14.85	-
7	7.789	0.49	35.68	-	36.17	-	60.00	50.00	-23.83	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 13		

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.197	0.20	42.14	-	42.34	-	63.74	53.74	-21.40	-
2	0.275	0.20	47.09	-	47.29	-	60.97	50.97	-13.68	-
3	0.416	0.20	47.53	39.51	47.73	39.71	57.54	47.54	-9.81	-7.83
4	0.568	0.20	44.94	-	45.14	-	56.00	46.00	-10.86	-
5	0.838	0.20	44.76	-	44.96	-	56.00	46.00	-11.04	-
6	1.711	0.20	44.07	-	44.27	-	56.00	46.00	-11.73	-
7	2.501	0.23	42.34	-	42.57	-	56.00	46.00	-13.43	-
8	4.012	0.30	38.76	-	39.06	-	56.00	46.00	-16.94	-
9	6.496	0.42	34.86	-	35.28	-	60.00	50.00	-24.72	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.



5.17 Test Results (14)


Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 14		

Phase Of Power : Line (L)

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.151	0.15	44.57	-	44.72	-	65.93	55.93	-21.21	-
2	0.408	0.20	45.15	-	45.35	-	57.69	47.69	-12.34	-
3	0.537	0.20	46.21	36.74	46.41	36.94	56.00	46.00	-9.59	-9.06
4	0.810	0.20	44.02	-	44.22	-	56.00	46.00	-11.78	-
5	1.086	0.20	45.60	-	45.80	-	56.00	46.00	-10.20	-
6	2.285	0.21	44.21	-	44.42	-	56.00	46.00	-11.58	-
7	3.008	0.25	42.86	-	43.11	-	56.00	46.00	-12.89	-
8	4.355	0.32	41.62	-	41.94	-	56.00	46.00	-14.06	-
9	6.930	0.45	35.92	-	36.37	-	60.00	50.00	-23.63	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 14		

Phase Of Power : Neutral (N)

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.193	0.19	39.44	-	39.63	-	63.91	53.91	-24.27	-
2	0.404	0.20	49.57	41.71	49.77	41.91	57.77	47.77	-8.00	-5.86
3	0.545	0.20	45.69	-	45.89	-	56.00	46.00	-10.11	-
4	0.818	0.20	46.80	30.88	47.00	31.08	56.00	46.00	-9.00	-14.92
5	1.762	0.20	44.33	-	44.53	-	56.00	46.00	-11.47	-
6	2.992	0.25	44.63	-	44.88	-	56.00	46.00	-11.12	-
7	4.336	0.32	41.12	-	41.44	-	56.00	46.00	-14.56	-
8	6.910	0.45	34.56	-	35.01	-	60.00	50.00	-24.99	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.



5.18 Test Results (15)


Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 15		

Phase Of Power : Line (L)

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.185	0.19	45.98	-	46.17	-	64.25	54.25	-18.09	-
2	0.408	0.20	43.04	-	43.24	-	57.69	47.69	-14.45	-
3	0.951	0.20	38.48	-	38.68	-	56.00	46.00	-17.32	-
4	1.781	0.20	37.65	-	37.85	-	56.00	46.00	-18.15	-
5	3.719	0.29	35.34	-	35.63	-	56.00	46.00	-20.37	-
6	7.602	0.48	32.74	-	33.22	-	60.00	50.00	-26.78	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 15		

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.173	0.17	46.96	-	47.13	-	64.79	54.79	-17.66	-
2	0.388	0.20	37.79	-	37.99	-	58.10	48.10	-20.11	-
3	0.814	0.20	38.74	-	38.94	-	56.00	46.00	-17.06	-
4	1.094	0.20	39.50	-	39.70	-	56.00	46.00	-16.30	-
5	1.706	0.20	37.15	-	37.35	-	56.00	46.00	-18.65	-
6	2.469	0.22	36.41	-	36.63	-	56.00	46.00	-19.37	-
7	3.695	0.28	35.16	-	35.44	-	56.00	46.00	-20.56	-
8	7.645	0.48	28.94	-	29.42	-	60.00	50.00	-30.58	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.



5.19 Test Results (16)


Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 16		

Phase Of Power : Line (L)

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.166	0.17	47.93	-	48.10	-	65.18	55.18	-17.08	-
2	0.267	0.20	44.67	-	44.87	-	61.20	51.20	-16.33	-
3	0.403	0.20	45.60	-	45.80	-	57.79	47.79	-11.99	-
4	1.078	0.20	44.40	-	44.60	-	56.00	46.00	-11.40	-
5	2.434	0.22	43.57	-	43.79	-	56.00	46.00	-12.21	-
6	3.684	0.28	43.67	-	43.95	-	56.00	46.00	-12.05	-
7	5.574	0.38	40.69	-	41.07	-	60.00	50.00	-18.93	-
8	10.301	0.61	33.96	-	34.57	-	60.00	50.00	-25.43	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 16		

Phase Of Power : Neutral (N)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.150	0.15	50.17	-	50.32	-	66.00	56.00	-15.68	-
2	0.412	0.20	49.22	38.66	49.42	38.86	57.61	47.61	-8.19	-8.75
3	0.541	0.20	45.61	-	45.81	-	56.00	46.00	-10.19	-
4	0.951	0.20	46.35	32.24	46.55	32.44	56.00	46.00	-9.45	-13.56
5	2.441	0.22	45.83	26.06	46.05	26.28	56.00	46.00	-9.95	-19.72
6	3.695	0.28	44.58	-	44.86	-	56.00	46.00	-11.14	-
7	5.648	0.38	41.14	-	41.52	-	60.00	50.00	-18.48	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.



5.20 Test Results (17)


Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 17		

Phase Of Power : Line (L)

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.205	0.20	41.05	-	41.25	-	63.42	53.42	-22.17	-
2	0.392	0.20	44.98	-	45.18	-	58.02	48.02	-12.84	-
3	0.545	0.20	41.11	-	41.31	-	56.00	46.00	-14.69	-
4	1.762	0.20	36.57	-	36.77	-	56.00	46.00	-19.23	-
5	2.574	0.23	32.46	-	32.69	-	56.00	46.00	-23.31	-
6	11.445	0.63	25.78	-	26.41	-	60.00	50.00	-33.59	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 17		

Phase Of Power : Neutral (N)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.150	0.15	47.33	-	47.48	-	66.00	56.00	-18.52	-
2	0.267	0.20	44.97	-	45.17	-	61.20	51.20	-16.03	-
3	0.408	0.20	42.96	-	43.16	-	57.69	47.69	-14.53	-
4	0.923	0.20	38.31	-	38.51	-	56.00	46.00	-17.49	-
5	1.645	0.20	38.01	-	38.21	-	56.00	46.00	-17.79	-
6	3.055	0.25	34.81	-	35.06	-	56.00	46.00	-20.94	-
7	6.492	0.42	26.80	-	27.22	-	60.00	50.00	-32.78	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.



5.21 Test Results (18)


Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 18		

Phase Of Power : Line (L)

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.163	0.16	40.47	-	40.63	-	65.30	55.30	-24.67	-
2	0.255	0.20	32.15	-	32.35	-	61.58	51.58	-29.23	-
3	0.472	0.20	38.38	-	38.58	-	56.48	46.48	-17.90	-
4	0.935	0.20	29.96	-	30.16	-	56.00	46.00	-25.84	-
5	2.809	0.24	25.55	-	25.79	-	56.00	46.00	-30.21	-
6	4.020	0.30	24.14	-	24.44	-	56.00	46.00	-31.56	-
7	20.281	0.81	13.47	-	14.28	-	60.00	50.00	-45.72	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 18		

Phase Of Power : Neutral (N)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.209	0.20	35.55	-	35.75	-	63.26	53.26	-27.51	-
2	0.474	0.20	37.79	-	37.99	-	56.44	46.44	-18.45	-
3	0.935	0.20	29.84	-	30.04	-	56.00	46.00	-25.96	-
4	2.711	0.24	27.33	-	27.57	-	56.00	46.00	-28.43	-
5	3.996	0.30	25.42	-	25.72	-	56.00	46.00	-30.28	-
6	7.523	0.48	20.76	-	21.24	-	60.00	50.00	-38.76	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.



5.22 Test Results (19)


Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 19		

Phase Of Power : Line (L)

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.213	0.20	36.07	-	36.27	-	63.11	53.11	-26.84	-
2	0.474	0.20	38.71	-	38.91	-	56.44	46.44	-17.53	-
3	0.970	0.20	30.66	-	30.86	-	56.00	46.00	-25.14	-
4	2.742	0.24	25.02	-	25.26	-	56.00	46.00	-30.74	-
5	3.992	0.30	23.68	-	23.98	-	56.00	46.00	-32.02	-
6	6.707	0.44	17.57	-	18.01	-	60.00	50.00	-41.99	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 19		

Phase Of Power : Neutral (N)

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.154	0.15	41.77	-	41.92	-	65.80	55.80	-23.88	-
2	0.467	0.20	37.01	-	37.21	-	56.56	46.56	-19.35	-
3	1.126	0.20	29.93	-	30.13	-	56.00	46.00	-25.87	-
4	2.824	0.24	26.39	-	26.63	-	56.00	46.00	-29.37	-
5	4.230	0.31	23.58	-	23.89	-	56.00	46.00	-32.11	-
6	8.141	0.51	20.27	-	20.78	-	60.00	50.00	-39.22	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.



5.23 Test Results (20)


Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 20		

Phase Of Power : Line (L)

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.263	0.20	32.10	-	32.30	-	61.33	51.33	-29.03	-
2	0.478	0.20	38.81	-	39.01	-	56.37	46.37	-17.36	-
3	0.920	0.20	30.75	-	30.95	-	56.00	46.00	-25.05	-
4	2.742	0.24	25.21	-	25.45	-	56.00	46.00	-30.55	-
5	3.801	0.29	24.72	-	25.01	-	56.00	46.00	-30.99	-
6	8.383	0.52	15.99	-	16.51	-	60.00	50.00	-43.49	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	22°C, 78%RH, 1003mbar
Tested by	Aron Wang		
Test Mode	Mode 20		

Phase Of Power : Neutral (N)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.157	0.16	41.47	-	41.63	-	65.64	55.64	-24.02	-
2	0.481	0.20	37.01	-	37.21	-	56.33	46.33	-19.12	-
3	1.070	0.20	30.21	-	30.41	-	56.00	46.00	-25.59	-
4	2.820	0.24	26.90	-	27.14	-	56.00	46.00	-28.86	-
5	3.902	0.30	25.78	-	26.08	-	56.00	46.00	-29.92	-
6	7.090	0.45	19.87	-	20.32	-	60.00	50.00	-39.68	-

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
3. The emission levels of other frequencies were very low against the limit.
4. Margin value = Emission level - Limit value
5. Correction factor = Insertion loss + Cable loss
6. Emission Level = Correction Factor + Reading Value.



6 Conducted Emission from the AC Mains Power Port - EN 55032

6.1 Limits

EN 55032 Table clause	Frequency range (MHz)	Coupling device	Detector type / bandwidth	Class A limits (dBuV)
A8.1	0.15 - 0.5	AMN	Quasi-peak / 9kHz	79
	0.5 - 30.0			73
A8.2	0.15 - 0.5	AMN	Average / 9kHz	66
	0.5 - 30.0			60

EN 55032 Table clause	Frequency range (MHz)	Coupling device	Detector type / bandwidth	Class B limits (dBuV)
A9.1	0.15 - 0.5	AMN	Quasi-peak / 9kHz	66 - 56
	0.5 - 5			56
	5 - 30.0			60
A9.2	0.15 - 0.5	AMN	Average / 9kHz	56 - 46
	0.5 - 5			46
	5 - 30.0			50

6.2 Test Instruments

Description & Manufacturer	Model No.	Serial No.	Cal. Date	Cal. Due
ROHDE & SCHWARZ TEST RECEIVER	ESCS 30	100276	Apr. 12, 2016	Apr. 11, 2017
ROHDE & SCHWARZ Artificial Mains Network (for EUT)	ENV216	101197	May 04, 2016	May 03, 2017
LISN With Adapter (for EUT)	AD10	C10Ada-002	May 04, 2016	May 03, 2017
ROHDE & SCHWARZ Artificial Mains Network (for peripherals)	ESH3-Z5	100218	Nov. 25, 2015	Nov. 24, 2016
SCHWARZBECK Artificial Mains Network (For EUT)	NNLK8129	8129229	May 04, 2016	May 03, 2017
Software	Cond_V7.3.7.4	NA	NA	NA
RF cable (JYEBAO) With 10dB PAD	5D-FB	Cable-C10.01	Feb. 15, 2016	Feb. 14, 2017
SUHNER Terminator (For ROHDE & SCHWARZ LISN)	65BNC-5001	E1-011484	May 12, 2016	May 11, 2017
ROHDE & SCHWARZ Artificial Mains Network (For TV EUT)	ESH3-Z5	100220	Nov. 13, 2015	Nov. 12, 2016
LISN With Adapter (for TV EUT)	100220	N/A	Nov. 13, 2015	Nov. 12, 2016


Notes:

1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
2. The test was performed in Shielded Room No. 10.
3. The VCCI Site Registration No. C-1852.
4. Tested Date: Oct. 3, 2016.

6.3 Test Arrangement

- a. The EUT was placed 0.4 meters from the conducting wall of the shielded room with EUT being connected to the power mains through a line impedance stabilization network (LISN). Other support units were connected to the power mains through another LISN. The two LISNs provide 50 Ohm/ 50uH of coupling impedance for the measuring instrument.
- b. Both lines of the power mains connected to the EUT were checked for maximum conducted interference.
- c. The test results of conducted emissions at mains ports are recorded of six worst margins for quasi-peak (mandatory) [and average (if necessary)] values against the limits at frequencies of interest unless the margin is 20 dB or greater.

Note: The resolution bandwidth and video bandwidth of test receiver is 9kHz for quasi-peak detection (QP) and average detection (AV) at frequency 0.15MHz-30MHz.



- Note:**
1. Support units were connected to second LISN.
 2. The distance specified between EUT/AE and other metallic objects is ≥ 0.8 m in the measurement arrangement for table-top EUT.

For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

6.4 Test Results (1)


Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	110Vac, 60Hz	Environmental Conditions	25°C, 75%RH, 998mbar
Tested by	Vincent Lin		
Test Mode	Mode 1		

Phase Of Power : Line (L)

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.26328	9.70	34.81	30.15	44.51	39.85	61.33	51.33	-16.82	-11.48
2	0.40000	9.69	40.89	34.91	50.58	44.60	57.85	47.85	-7.27	-3.25
3	0.52372	9.70	35.48	25.81	45.18	35.51	56.00	46.00	-10.82	-10.49
4	0.68125	9.71	40.39	28.09	50.10	37.80	56.00	46.00	-5.90	-8.20
5	0.79844	9.72	33.89	20.76	43.61	30.48	56.00	46.00	-12.39	-15.52
6	0.91953	9.73	36.74	24.25	46.47	33.98	56.00	46.00	-9.53	-12.02
7	1.36328	9.75	37.46	21.75	47.21	31.50	56.00	46.00	-8.79	-14.50
8	1.46094	9.76	34.49	18.28	44.25	28.04	56.00	46.00	-11.75	-17.96
9	1.62891	9.77	39.25	23.29	49.02	33.06	56.00	46.00	-6.98	-12.94
10	1.76172	9.77	36.04	18.26	45.81	28.03	56.00	46.00	-10.19	-17.97
11	2.31250	9.79	36.21	17.81	46.00	27.60	56.00	46.00	-10.00	-18.40
12	2.71094	9.81	35.83	17.27	45.64	27.08	56.00	46.00	-10.36	-18.92
13	3.40234	9.84	35.17	20.20	45.01	30.04	56.00	46.00	-10.99	-15.96
14	4.23438	9.87	31.74	15.24	41.61	25.11	56.00	46.00	-14.39	-20.89
15	5.30469	9.88	31.28	15.67	41.16	25.55	60.00	50.00	-18.84	-24.45

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	110Vac, 60Hz	Environmental Conditions	25°C, 75%RH, 998mbar
Tested by	Vincent Lin		
Test Mode	Mode 1		

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.15000	9.70	36.09	6.32	45.79	16.02	66.00	56.00	-20.21	-39.98
2	0.26981	9.69	34.81	29.82	44.50	39.51	61.12	51.12	-16.62	-11.61
3	0.54067	9.70	37.62	28.77	47.32	38.47	56.00	46.00	-8.68	-7.53
4	0.67344	9.71	36.16	25.03	45.87	34.74	56.00	46.00	-10.13	-11.26
5	0.81543	9.72	39.27	26.41	48.99	36.13	56.00	46.00	-7.01	-9.87
6	0.95078	9.73	37.89	23.94	47.62	33.67	56.00	46.00	-8.38	-12.33
7	1.08594	9.73	37.77	23.62	47.50	33.35	56.00	46.00	-8.50	-12.65
8	1.22266	9.74	35.44	19.55	45.18	29.29	56.00	46.00	-10.82	-16.71
9	1.62500	9.75	37.09	20.68	46.84	30.43	56.00	46.00	-9.16	-15.57
10	1.89063	9.77	38.47	21.73	48.24	31.50	56.00	46.00	-7.76	-14.50
11	2.42188	9.79	34.49	15.78	44.28	25.57	56.00	46.00	-11.72	-20.43
12	2.83594	9.81	36.73	18.79	46.54	28.60	56.00	46.00	-9.46	-17.40
13	3.62109	9.84	33.32	15.31	43.16	25.15	56.00	46.00	-12.84	-20.85
14	4.71094	9.86	32.22	16.35	42.08	26.21	56.00	46.00	-13.92	-19.79

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value




6.5 Test Results (2)

Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	25°C, 75%RH, 998mbar
Tested by	Vincent Lin		
Test Mode	Mode 1		

Phase Of Power : Line (L)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.15000	9.70	38.37	8.19	48.07	17.89	66.00	56.00	-17.93	-38.11
2	0.26719	9.70	40.81	36.94	50.51	46.64	61.20	51.20	-10.69	-4.56
3	0.39609	9.69	44.16	37.97	53.85	47.66	57.93	47.93	-4.08	-0.27
4	0.54198	9.70	39.53	29.11	49.23	38.81	56.00	46.00	-6.77	-7.19
5	0.65000	9.71	37.20	26.19	46.91	35.90	56.00	46.00	-9.09	-10.10
6	0.80625	9.72	40.91	29.23	50.63	38.95	56.00	46.00	-5.37	-7.05
7	0.95087	9.74	39.36	24.29	49.10	34.03	56.00	46.00	-6.90	-11.97
8	1.07031	9.74	37.54	23.54	47.28	33.28	56.00	46.00	-8.72	-12.72
9	1.22410	9.75	36.92	19.43	46.67	29.18	56.00	46.00	-9.33	-16.82
10	1.62528	9.77	42.06	25.69	51.83	35.46	56.00	46.00	-4.17	-10.54
11	2.23438	9.79	39.36	21.48	49.15	31.27	56.00	46.00	-6.85	-14.73
12	2.72266	9.81	35.07	18.47	44.88	28.28	56.00	46.00	-11.12	-17.72
13	3.11719	9.83	37.72	22.73	47.55	32.56	56.00	46.00	-8.45	-13.44
14	3.49591	9.85	37.05	21.98	46.90	31.83	56.00	46.00	-9.10	-14.17
15	4.17578	9.87	35.29	19.68	45.16	29.55	56.00	46.00	-10.84	-16.45
16	4.99618	9.88	33.72	17.94	43.60	27.82	56.00	46.00	-12.40	-18.18

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	230Vac, 50Hz	Environmental Conditions	25°C, 75%RH, 998mbar
Tested by	Vincent Lin		
Test Mode	Mode 1		

No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.15000	9.70	35.16	4.92	44.86	14.62	66.00	56.00	-21.14	-41.38
2	0.39219	9.69	40.65	33.45	50.34	43.14	58.02	48.02	-7.68	-4.88
3	0.52891	9.70	42.59	34.30	52.29	44.00	56.00	46.00	-3.71	-2.00
4	0.80625	9.72	38.93	27.18	48.65	36.90	56.00	46.00	-7.35	-9.10
5	0.93125	9.73	41.84	29.08	51.57	38.81	56.00	46.00	-4.43	-7.19
6	1.08203	9.73	41.14	27.05	50.87	36.78	56.00	46.00	-5.13	-9.22
7	1.62891	9.76	39.99	21.46	49.75	31.22	56.00	46.00	-6.25	-14.78
8	1.73047	9.76	41.42	24.88	51.18	34.64	56.00	46.00	-4.82	-11.36
9	2.40234	9.79	39.53	21.31	49.32	31.10	56.00	46.00	-6.68	-14.90
10	2.88281	9.81	38.50	19.82	48.31	29.63	56.00	46.00	-7.69	-16.37
11	3.58594	9.84	36.77	17.47	46.61	27.31	56.00	46.00	-9.39	-18.69
12	4.26953	9.86	35.50	19.63	45.36	29.49	56.00	46.00	-10.64	-16.51
13	4.99744	9.87	32.64	16.15	42.51	26.02	56.00	46.00	-13.49	-19.98

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value



7 Radiated Emission at Frequencies up to 1GHz - EN 61000-6-3

7.1 Limits

Standard	Frequency range (MHz)	Quasi-peak dB(uV/m)
EN 61000-6-3	30 – 230	30
	230 – 1000	37

- NOTE:** (1) The lower limit shall apply at the transition frequencies.
(2) If the internal emission source(s) is operating at a frequency below 9kHz then measurements shall only be performed up to 230MHz.

7.2 Test Instruments


DESCRIPTION & MANUFACTURER	MODEL NO.	SERIAL NO.	CALIBRATED UNTIL
ROHDE & SCHWARZ TEST RECEIVER	ESVS 10	840241/010	Sep. 02, 2008
Schaffner BILOG Antenna	CBL6111C	2728	May 31, 2008
CT Turn Table	TT100	CT-080	NA
CT Tower	AT100	CT-080	NA
Software	ADT_Radiated_V7.6.15	NA	NA
ANRITSU RF Switches	MP59B	6100259081	Sep. 16, 2008
WOKEN RF cable	8D	CABLE-ST3-01	Sep. 16, 2008

- NOTE:** 1. The calibration interval of the above test instruments is 12 months. And the calibrations are traceable to NML/ROC and NIST/USA.
2. The test was performed in ADT Open Site No. 3.
3. The VCCI Site Registration No. is R-269.
4. Test date: Mar. 27 ~ Apr. 9, 2008

7.3 Test Arrangement

- a. The EUT was placed on the top of a rotating table 0.8 meters above the ground at an accredited test facility. The table was rotated 360 degrees to determine the position of the highest radiation.
- b. The EUT was set 10 meters away from the interference-receiving antenna, which was mounted on the top of a variable-height antenna tower.
- c. The antenna is a broadband antenna, and its height is varied from one meter to four meters above the ground to determine the maximum value of the field strength. Both horizontal and vertical polarizations of the antenna are set to make the measurement.
- d. For each suspected emission, the EUT was arranged to its worst case and then the antenna was tuned to heights from 1 meter to 4 meters and the rotatable table was turned from 0 degrees to 360 degrees to find the maximum reading.
- e. The test-receiver system was set to quasi-peak detect function and specified bandwidth with maximum hold mode when the test frequency is up to 1 GHz.

Note: The resolution bandwidth and video bandwidth of test receiver/spectrum analyzer is 120kHz for quasi-peak detection (QP) at frequency up to 1GHz.



For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.


7.4 Test Results (1)

Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Tested by	Ian Chang	Environmental Conditions	25°C, 60%RH, 1002mbar
Test Mode	Mode 1		

Antenna Polarity & Test Distance : Horizontal at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	52.33	25.46 QP	30.00	-4.54	4.00 H	93	17.31	8.15
2	112.52	22.46 QP	30.00	-7.54	4.00 H	273	10.49	11.97
3	136.53	20.09 QP	30.00	-9.91	4.00 H	353	7.59	12.50
4	162.47	18.67 QP	30.00	-11.33	4.00 H	313	6.06	12.61
5	179.45	20.47 QP	30.00	-9.53	4.00 H	19	9.68	10.79
6	216.46	18.81 QP	30.00	-11.19	4.00 H	157	5.77	13.04

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Tested by	Ian Chang	Environmental Conditions	25°C, 60%RH, 1002mbar
Test Mode	Mode 1		

Antenna Polarity & Test Distance : Vertical at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	58.08	24.64 QP	30.00	-5.36	2.00 V	176	17.87	6.77
2	119.55	23.27 QP	30.00	-6.73	1.00 V	217	10.60	12.67
3	148.41	23.48 QP	30.00	-6.52	1.00 V	291	10.64	12.84
4	191.33	21.65 QP	30.00	-8.35	1.00 V	19	10.37	11.28
5	211.80	19.07 QP	30.00	-10.93	1.00 V	271	6.42	12.65
6	244.14	25.01 QP	37.00	-11.99	1.00 V	191	9.68	15.33

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




7.5 Test Results (2)

Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Tested by	Ian Chang	Environmental Conditions	25°C, 60%RH, 1003mbar
Test Mode	Mode 16		

Antenna Polarity & Test Distance : Horizontal at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	51.98	27.11 QP	30.00	-2.89	4.00 H	47	18.88	8.23
2	115.67	21.33 QP	30.00	-8.67	4.00 H	74	9.05	12.28
3	139.68	21.91 QP	30.00	-8.09	4.00 H	0	9.45	12.46
4	167.08	20.12 QP	30.00	-9.88	4.00 H	49	8.10	12.02
5	179.69	20.37 QP	30.00	-9.63	4.00 H	105	9.60	10.77
6	211.56	19.24 QP	30.00	-10.76	4.00 H	226	6.61	12.63

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Tested by	Ian Chang	Environmental Conditions	25°C, 73%RH, 1003mbar
Test Mode	Mode 16		

Antenna Polarity & Test Distance : Vertical at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	51.36	27.38 QP	30.00	-2.62	1.00 V	346	19.00	8.38
2	110.34	23.66 QP	30.00	-6.34	1.00 V	190	11.90	11.76
3	136.53	22.94 QP	30.00	-7.06	1.00 V	317	10.44	12.50
4	139.68	25.12 QP	30.00	-4.88	1.00 V	260	12.66	12.46
5	192.06	22.83 QP	30.00	-7.17	1.00 V	108	11.52	11.31
6	211.56	20.07 QP	30.00	-9.93	1.00 V	196	7.44	12.63

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




7.6 Test Results (3)

Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Tested by	Ian Chang	Environmental Conditions	25°C, 60%RH, 1003mbar
Test Mode	Mode 19		

Antenna Polarity & Test Distance : Horizontal at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	52.07	23.03 QP	30.00	-6.97	4.00 H	76	14.82	8.21
2	112.60	23.44 QP	30.00	-6.56	4.00 H	283	11.46	11.98
3	139.16	17.78 QP	30.00	-12.22	4.00 H	229	5.31	12.47
4	163.90	16.99 QP	30.00	-13.01	4.00 H	0	4.56	12.43
5	217.28	18.45 QP	30.00	-11.55	4.00 H	244	5.35	13.10
6	293.30	21.28 QP	37.00	-15.72	4.00 H	0	5.69	15.59

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Tested by	Ian Chang	Environmental Conditions	25°C, 60%RH, 1003mbar
Test Mode	Mode 19		

Antenna Polarity & Test Distance : Vertical at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	56.78	25.25 QP	30.00	-4.75	1.00 V	0	18.17	7.08
2	69.56	25.82 QP	30.00	-4.18	1.00 V	187	18.51	7.31
3	114.63	24.97 QP	30.00	-5.03	1.00 V	173	12.79	12.18
4	137.53	21.99 QP	30.00	-8.01	1.00 V	235	9.50	12.49
5	211.50	18.42 QP	30.00	-11.58	1.00 V	308	5.80	12.62
6	243.00	24.24 QP	37.00	-12.76	1.00 V	199	9.00	15.24

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value



8 Radiated Emission at Frequencies up to 1GHz - EN 55032

8.1 Limits

For Class A Equipment

EN 55032 Table clause	Frequency range (MHz)	Distance (m)	Limits (dBuV/m)
A2.1	30 - 230	10	40
	230 - 1000		47
A2.2	30 - 230	3	50
	230 - 1000		57

For Class B Equipment

EN 55032 Table clause	Frequency range (MHz)	Distance (m)	Limits (dBuV/m)
A4.1	30 - 230	10	30
	230 - 1000		37
A4.2	30 - 230	3	40
	230 - 1000		47

8.2 Test Instruments

Description & Manufacturer	Model No.	Serial No.	Cal. Date	Cal. Due
ROHDE & SCHWARZ TEST RECEIVER	ESCI	100612	Nov. 23, 2015	Nov. 22, 2016
SCHAFFNER BILOG Antenna	CBL6111D	22263	Jan. 07, 2016	Jan. 06, 2017
ADT. Turn Table	TT100	0401	NA	NA
ADT. Tower	AT100	0401	NA	NA
Software	Radiated_V7.6.15.9.5	NA	NA	NA
ADT RF Switches BOX	EMH-011	08004	Mar. 01, 2016	Feb. 28, 2017
WOKEN RF cable With 5dB PAD	8D	CABLE-ST4-01	Mar. 30, 2016	Mar. 29, 2017

Notes:


1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
2. The test was performed in Open Site No. 4.
3. The VCCI Site Registration No. R-1038.
4. The FCC Site Registration No. 90426.
5. Tested Date: Oct. 3, 2016.

8.3 Test Arrangement

- a. The EUT was placed on the top of a rotating table 0.8 meters above the ground at an accredited test facility. The table was rotated 360 degrees to determine the position of the highest radiation.
- b. The EUT was set 10 meters away from the interference-receiving antenna, which was mounted on the top of a variable-height antenna tower.
- c. The antenna is a broadband antenna, and its height is varied from one meter to four meters above the ground to determine the maximum value of the field strength. Both horizontal and vertical polarizations of the antenna are set to make the measurement.
- d. For each suspected emission, the EUT was arranged to its worst case and then the antenna was tuned to heights from 1 meter to 4 meters and the rotatable table was turned from 0 degrees to 360 degrees to find the maximum reading.
- e. The test-receiver system was set to quasi-peak detect function and specified bandwidth with maximum hold mode when the test frequency is up to 1 GHz.

Note:

1. The resolution bandwidth and video bandwidth of test receiver/spectrum analyzer is 120kHz for quasi-peak detection (QP) at frequency up to 1GHz.
2. The measurement distance is the shortest horizontal distance between an imaginary circular periphery just encompassing this arrangement and the calibration point of the antenna.



For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.


8.4 Test Results

Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Tested by	Adam Chen	Environmental Conditions	26°C, 57%RH, 998mbar
Test Mode	Mode 1		

Antenna Polarity & Test Distance : Horizontal at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	33.31	21.09 QP	30.00	-8.91	4.00 H	132	25.85	-4.76
2	87.08	20.79 QP	30.00	-9.21	4.00 H	225	33.30	-12.51
3	95.96	21.42 QP	30.00	-8.58	4.00 H	138	32.84	-11.42
4	117.87	20.59 QP	30.00	-9.41	4.00 H	189	29.60	-9.01
5	135.09	20.79 QP	30.00	-9.21	4.00 H	301	29.69	-8.90
6	184.54	19.63 QP	30.00	-10.37	4.00 H	226	30.84	-11.21
7	216.67	19.60 QP	30.00	-10.40	4.00 H	175	30.15	-10.55

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Tested by	Adam Chen	Environmental Conditions	26°C, 57%RH, 998mbar
Test Mode	Mode 1		

Antenna Polarity & Test Distance : Vertical at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	35.77	22.84 QP	30.00	-7.16	1.00 V	78	28.99	-6.15
2	62.10	21.22 QP	30.00	-8.78	1.00 V	251	36.54	-15.32
3	88.21	25.90 QP	30.00	-4.10	1.56 V	113	38.39	-12.49
4	95.69	29.03 QP	30.00	-0.97	1.14 V	40	40.49	-11.46
5	109.79	24.01 QP	30.00	-5.99	1.00 V	168	33.76	-9.75
6	169.06	20.49 QP	30.00	-9.51	1.00 V	348	31.08	-10.59
7	188.54	22.88 QP	30.00	-7.12	1.00 V	194	34.20	-11.32
8	205.28	20.03 QP	30.00	-9.97	1.00 V	135	30.70	-10.67

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value



9 Harmonics Current Measurement

9.1 Limits

Limits for Class A equipment		Limits for Class D equipment		
Harmonic Order n	Max. permissible harmonics current A	Harmonic Order n	Max. permissible harmonics current per watt mA/W	Max. permissible harmonics current A
Odd harmonics			Odd Harmonics only	
3	2.30	3	3.4	2.30
5	1.14	5	1.9	1.14
7	0.77	7	1.0	0.77
9	0.40	9	0.5	0.40
11	0.33	11	0.35	0.33
13	0.21	13	0.30	0.21
$15 \leq n \leq 39$	$0.15 \times 15/n$	$15 \leq n \leq 39$	$3.85/n$	$0.15 \times 15/n$
Even harmonics				
2	1.08			
4	0.43			
6	0.30			
$8 \leq n \leq 40$	$0.23 \times 8/n$			

Notes: 1. Class A and Class D are classified according to section 5 of EN 61000-3-2.
 2. According to section 7 of EN 61000-3-2, the above limits for all equipment except for lighting equipment having an active input power > 75 W and no limits apply for equipment with an active input power up to and including 75 W.

9.2 Classification of Equipment

Class A	Class B	Class C	Class D
Balanced three-phase equipment; Household appliances excluding equipment as Class D; Tools excluding portable tools; Dimmers for incandescent lamps; Audio equipment; Equipment not specified in one of the three other classes.	Portable tools; Arc welding equipment which is not professional equipment.	Lighting equipment.	Equipment having a specified power less than or equal to 600 W of the following types: Personal computers and personal computer monitors; Television receivers; Refrigerators and freezers having one or more variable-speed drives to control compressor motor(s).


9.3 Test Instruments

DESCRIPTION & MANUFACTURER	MODEL NO.	SERIAL NO.	CALIBRATED UNTIL
EMC PARTNER EMC Emission Tester	HAR1000-1P	084	Apr. 25, 2008
Software	HARCS	NA	NA

- NOTE:** 1. The test was performed in EMS Room No. 1.
 2. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
 3. Test date: Mar. 27 ~ Apr. 9, 2008

9.4 Test Arrangement

- a. The EUT was placed on the top of a wooden table 0.8 meters above the ground and operated to produce the maximum harmonic components under normal operating conditions for each successive harmonic component in turn.
- b. The correspondent test program of test instrument to measure the current harmonics emanated from EUT is chosen. The measure time shall be not less than the time necessary for the EUT to be exercised.



For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

9.5 Test Results (1)

TEST MODE	Mode 1		
FUNDAMENTAL VOLTAGE/AMPERE	230.3Vrms/ 0.188Arms	POWER FREQUENCY	49.987Hz
POWER CONSUMPTION	20.59W	POWER FACTOR	0.477
ENVIRONMENTAL CONDITIONS	22deg. C, 71% RH, 999mbar	TESTED BY: Andy Cheng	

NOTE: Limits are not specified for equipment with a rated power of 75W or less
(other than lighting equipment).

9.6 Test Results (2)

TEST MODE	Mode 16		
FUNDAMENTAL VOLTAGE/AMPERE	230.3Vrms/ 0.201Arms	POWER FREQUENCY	50.000Hz
POWER CONSUMPTION	22.19W	POWER FACTOR	0.479
ENVIRONMENTAL CONDITIONS	23deg. C, 70% RH, 997mbar	TESTED BY: Andy Cheng	

NOTE: Limits are not specified for equipment with a rated power of 75W or less
(other than lighting equipment).

9.7 Test Results (3)

TEST MODE	Mode 19		
FUNDAMENTAL VOLTAGE/AMPERE	230.3Vrms/ 0.198Arms	POWER FREQUENCY	50.000Hz
POWER CONSUMPTION	21.72W	POWER FACTOR	0.477
ENVIRONMENTAL CONDITIONS	21deg. C, 70% RH, 997mbar	TESTED BY: Andy Cheng	

NOTE: Limits are not specified for equipment with a rated power of 75W or less
(other than lighting equipment).

10 Voltage Fluctuations and Flicker Measurement

10.1 Limits

Test item	Limit	Note
P_{st}	1.0	P_{st} : short-term flicker severity.
P_{lt}	0.65	P_{lt} : long-term flicker severity.
T_{max} (ms)	500	T_{max} : maximum time duration during the observation period that the voltage deviation $d(t)$ exceeds the limit for d_c .
d_{max} (%)	4	d_{max} : maximum absolute voltage change during an observation period.
d_c (%)	3.3	d_c : maximum steady state voltage change during an observation period.


10.2 Test Instruments

DESCRIPTION & MANUFACTURER	MODEL NO.	SERIAL NO.	CALIBRATED UNTIL
EMC PARTNER EMC Emission Tester	HAR1000-1P	084	Apr. 25, 2008
Software	HARCS	NA	NA

NOTE: 1. The test was performed in EMS Room No. 1.
 2. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
 3. Test date: Mar. 27 ~ Apr. 9, 2008

10.3 Test Arrangement

- a. The EUT was placed on the top of a wooden table 0.8 meters above the ground and operated to produce the most unfavorable sequence of voltage changes under normal operating conditions.
- b. During the flick measurement, the measure time shall include that part of whole operation cycle in which the EUT produce the most unfavorable sequence of voltage changes. The observation period for short-term flicker indicator is 10 minutes and the observation period for long-term flicker indicator is 2 hours.



For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

10.4 Test Results (1)

TEST MODE	Mode 1		
FUNDAMENTAL VOLTAGE/AMPERE	230.3Vrms/ 0.186Arms	POWER FREQUENCY	50.013Hz
OBSERVATION PERIOD (Tp)	10 min	POWER FACTOR	0.480
ENVIRONMENTAL CONDITIONS	22deg. C, 71% RH, 997mbar	TESTED BY: Andy Cheng	

TEST PARAMETER	MEASUREMENT VALUE	LIMIT	REMARKS
P _{st}	0.072	1.0	Pass
P _{lt}	0.072	0.65	Pass
d(t) (%)	0	3.3	Pass
d _{max} (%)	0	4	Pass
dc (%)	0	3.3	Pass

- NOTE:**
- (1) P_{st} means short-term flicker indicator.
 - (2) P_{lt} means long-term flicker indicator.
 - (3) d(t) means maximum time that not exceeds 500ms.
 - (4) d_{max} means maximum relative voltage change.
 - (5) dc means relative steady-state voltage change.

10.5 Test Results (2)

TEST MODE	Mode 16		
FUNDAMENTAL VOLTAGE/AMPERE	230.3Vrms/ 0.200Arms	POWER FREQUENCY	50.000Hz
OBSERVATION PERIOD (Tp)	10 min	POWER FACTOR	0.482
ENVIRONMENTAL CONDITIONS	23deg. C, 70% RH, 997mbar	TESTED BY: Andy Cheng	

TEST PARAMETER	MEASUREMENT VALUE	LIMIT	REMARKS
P _{st}	0.072	1.0	Pass
P _{lt}	0.072	0.65	Pass
d(t) (%)	0	3.3	Pass
d _{max} (%)	0	4	Pass
dc (%)	0	3.3	Pass

- NOTE:**
- (1) P_{st} means short-term flicker indicator.
 - (2) P_{lt} means long-term flicker indicator.
 - (3) d(t) means maximum time that not exceeds 500ms.
 - (4) d_{max} means maximum relative voltage change.
 - (5) dc means relative steady-state voltage change.

10.6 Test Results (3)

TEST MODE	Mode 19		
FUNDAMENTAL VOLTAGE/AMPERE	230.3Vrms/ 0.197Arms	POWER FREQUENCY	49.987Hz
OBSERVATION PERIOD (Tp)	10 min	POWER FACTOR	0.478
ENVIRONMENTAL CONDITIONS	21deg. C, 70% RH, 997mbar	TESTED BY: Andy Cheng	

TEST PARAMETER	MEASUREMENT VALUE	LIMIT	REMARKS
P _{st}	0.072	1.0	Pass
P _{lt}	0.072	0.65	Pass
d(t) (%)	0	3.3	Pass
d _{max} (%)	0	4	Pass
dc (%)	0	3.3	Pass

- NOTE:**
- (1) P_{st} means short-term flicker indicator.
 - (2) P_{lt} means long-term flicker indicator.
 - (3) d(t) means maximum time that not exceeds 500ms.
 - (4) d_{max} means maximum relative voltage change.
 - (5) dc means relative steady-state voltage change.

11 Immunity Test

11.1 General Immunity Requirements

EN 61000-6-1: 2007, Immunity requirements

Reference standard	Test specification	Performance Criterion
IEC 61000-4-2 ESD	Enclosure port: ±8kV Air discharge, ±4kV Contact discharge,	B
IEC 61000-4-3 RS	Enclosure port: 80-1000 MHz, 3V/m, 80% AM (1kHz), 1.4-2.0 GHz, 3V/m, 80% AM (1kHz), 2.0-2.7 GHz, 1V/m, 80% AM (1kHz)	A
IEC 61000-4-4 EFT	AC Power line: ±1kV, DC Power line: ±0.5kV Signal line: ±0.5kV	B
IEC 61000-4-5 Surge	1.2/50 us Open Circuit Voltage, 8 /20 us Short Circuit Current AC Power Line: line to line 1 kV, line to earth 2kV DC Power Line: line to earth 0.5kV	B
IEC 61000-4-6 CS	0.15-80 MHz, 3 Vr.m.s, 80% AM, 1kHz	A
IEC 61000-4-8 PFMF	50 Hz, 3A/m, 60 Hz, 3 A/m,	A
IEC 61000-4-11 Dips & Interruptions	Voltage Dips: 0% residual– 0.5, 1 period, 70% residual – 25, 30 period	B C
	Voltage Interruptions: 0% residual – 250, 300 period	C

EN 55024:2010, Immunity requirements

Clause	Reference standard	Table	Test specification	Performance Criterion
4.2.1	IEC 61000-4-2 ESD	1.3	Enclosure port: ±8kV Air discharge, ±4kV Contact discharge	B
4.2.3.2	IEC 61000-4-3 RS	1.2	Enclosure port: 80-1000 MHz, 3V/m, 80% AM (1kHz)	A
4.2.2	IEC 61000-4-4 EFT	2.3	Signal ports and telecommunication ports: xDSL equipment: ±0.5kV, 5/50 (T_r/T_h) ns, 100kHz others: ±0.5kV, 5/50 (T_r/T_h) ns, 5kHz	B
		3.3	Input DC power port: ±0.5kV, 5/50 (T_r/T_h) ns, 5kHz	
		4.5	Input AC Power ports: ±1kV, 5/50 (T_r/T_h) ns, 5kHz	
4.2.5	IEC 61000-4-5 Surge	2.2	Signal and telecommunication ports (direct to outdoor cables): 10/700 (5/320) (T_r/T_h) µs w/o primary protectors: ±1kV, or with primary protectors fitted: ±4kV	C
		3.2	Input DC power port (direct to outdoor cables): 1.2/50 (8/20) (T_r/T_h) µs Line to earth: ±0.5kV	B
		4.4	Input AC Power ports: 1.2/50 (8/20) (T_r/T_h) µs, Line to line: ±1kV Line to earth: ±2kV	
4.2.3.3	IEC 61000-4-6 CS	2.1	Signal and telecommunication ports(cable length > 3m): 0.15-80 MHz, 3V, 80% AM (1kHz)	A
		3.1	Input DC power port: 0.15-80 MHz, 3V, 80% AM (1kHz)	
		4.1	Input AC Power ports: 0.15-80 MHz, 3V, 80% AM (1kHz)	
4.2.4	IEC 61000-4-8 PFMF	1.1	Enclosure port: 50 or 60 Hz, 1A/m	A
4.2.6	IEC 61000-4-11 Dips & Interruptions	4.2	Input AC Power ports: Voltage Dips: >95% reduction – 0.5 period 30% reduction – 25 periods	B C
		4.3	Input AC Power ports: Voltage Interruptions: >95% reduction – 250 periods	C

11.2 Performance Criteria

General Performance Criteria

Performance criterion A

The equipment shall continue to operate as intended without operator intervention. No degradation of performance or loss of function is allowed below a performance level specified by the manufacturer when the equipment is used as intended. The performance level may be replaced by a permissible loss of performance. If the minimum performance level or the permissible performance loss is not specified by the manufacturer, then either of these may be derived from the product description and documentation, and by what the user may reasonably expect from the equipment if used as intended.

Performance criterion B

After the test, the equipment shall continue to operate as intended without operator intervention. No degradation of performance or loss of function is allowed, after the application of the phenomena below a performance level specified by the manufacturer, when the equipment is used as intended. The performance level may be replaced by a permissible loss of performance. During the test, degradation of performance is allowed. However, no change of operating state or stored data is allowed to persist after the test. If the minimum performance level (or the permissible performance loss) is not specified by the manufacturer, then either of these may be derived from the product description and documentation, and by what the user may reasonably expect from the equipment if used as intended.

Performance criterion C

Loss of function is allowed, provided the function is self-recoverable, or can be restored by the operation of the controls by the user in accordance with the manufacturer's instructions. Functions, and/or information stored in non-volatile memory, or protected by a battery backup, shall not be lost.

Particular performance criteria

The particular performance criteria which are specified in the normative annexes of EN 55024 take precedence over the corresponding parts of the general performance criteria. Where particular performance criteria for specific functions are not given, then the general performance criteria shall apply.

12 Electrostatic Discharge Immunity Test (ESD)

12.1 Test Specification

Basic Standard:	IEC 61000-4-2
Discharge Impedance:	330 ohm / 150 pF
Discharge Voltage:	Air Discharge: ± 2 , ± 4 , ± 8 kV (Direct) Contact Discharge: ± 2 , ± 4 kV (Direct & Indirect)
Number of Discharge: <EN 61000-6-1>	Minimum 20 times at each test point
Number of Discharge: <EN 55024>	Air – Direct: 10 discharges per location (each polarity) Contact – Direct & Indirect: 25 discharges per location (each polarity) and min. 200 times in total
Discharge Mode:	Single Discharge
Discharge Period:	1-second minimum

12.2 Test Instruments

DESCRIPTION & MANUFACTURER	MODEL NO.	SERIAL NO.	CALIBRATED UNTIL
KeyTek, ESD Simulator	MZ-15/EC	9902287	Mar. 30, 2009

- NOTE:** 1. The test was performed in ESD Room No. 2.
 2. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
 3. Test date: Mar. 27 ~ Apr. 9, 2008

12.3 Test Arrangement

The discharges shall be applied in two ways: <For EN 55024>

- a. Contact discharges to the conductive surfaces and coupling planes:

The EUT shall be exposed to at least 200 discharges, 100 each at negative and positive polarity, at a minimum of four test points. One of the test points shall be subjected to at least 50 indirect discharges to the center of the front edge of the horizontal coupling plane. The remaining three test points shall each receive at least 50 direct contact discharges. If no direct contact test points are available, then at least 200 indirect discharges shall be applied in the indirect mode. Test shall be performed at a maximum repetition rate of one discharge per second.

- b. Air discharges at slots and apertures and insulating surfaces:

On those parts of the EUT where it is not possible to perform contact discharge testing, the equipment should be investigated to identify user accessible points where breakdown may occur. Such points are tested using the air discharge method. This investigation should be restricted to those area normally handled by the user. A minimum of 10 single air discharges shall be applied to the selected test point for each such area.

The basic test procedure was in accordance with IEC 61000-4-2:

- a. Electrostatic discharges were applied only to those points and surfaces of the EUT that are accessible to users during normal operation.
- b. The test was performed with at least ten single discharges on the pre-selected points in the most sensitive polarity.
- c. The time interval between two successive single discharges was at least 1 second.
- d. The ESD generator was held perpendicularly to the surface to which the discharge was applied and the return cable was at least 0.2 meters from the EUT.
- e. Contact discharges were applied to the non-insulating coating, with the pointed tip of the generator penetrating the coating and contacting the conducting substrate.
- f. Air discharges were applied with the round discharge tip of the discharge electrode approaching the EUT as fast as possible (without causing mechanical damage) to touch the EUT. After each discharge, the ESD generator was removed from the EUT and re-triggered for a new single discharge. The test was repeated until all discharges were complete.
- g. At least ten single discharges (in the most sensitive polarity) were applied to the **Horizontal Coupling Plane** at points on each side of the EUT. The ESD generator was positioned at a distance of 0.1 meters from the EUT with the discharge electrode touching the **HCP**.
- h. At least ten single discharges (in the most sensitive polarity) were applied to the center of one vertical edge of the **Vertical Coupling Plane** in sufficiently different positions that the four faces of the EUT were completely illuminated. The **VCP** (dimensions 0.5m x 0.5m) was placed vertically to and 0.1 meters from the EUT.




TABLE-TOP EQUIPMENT

The configuration consisted of a wooden table 0.8 meters high standing on the **Ground Reference Plane**. The **GRP** consisted of a sheet of aluminum at least 0.25mm thick, and 2.5 meters square connected to the protective grounding system. A **Horizontal Coupling Plane** (1.6m x 0.8m) was placed on the table and attached to the **GRP** by means of a cable with 940kΩ total impedance. The equipment under test, was installed in a representative system as described in section 7 of IEC 61000-4-2, and its cables were placed on the **HCP** and isolated by an insulating support of 0.5mm thickness. A distance of 1-meter minimum was provided between the EUT and the walls of the laboratory and any other metallic structure.

For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

12.4 Test Results (1)

Test mode	Mode 1	Input Power	230 Vac, 50 Hz
Environmental Conditions	25 °C, 50% RH 997 mbar	Tested by	Andy Cheng

Test Results of Direct Application

Discharge Level (kV)	Polarity (+/-)	Test Point	Contact Discharge	Air Discharge	Performance Criterion
2, 4	+/-	1, 2	Note	N/A	A
2, 4, 8	+/-	3	N/A	Note	A

Description of test points of direct application: Please refer to following page for representative mark only.

Test Results of Indirect Application



Discharge Level (kV)	Polarity (+/-)	Test Point	Horizontal Coupling Plane	Vertical Coupling Plane	Performance Criterion
2, 4	+/-	Four Sides	Note	Note	A

Description of test points of indirect application:

1. Front side
2. Rear side
3. Right side
4. Left side

Note: The EUT function was correct during the test.

Description of Test Points



12.5 Test Results (2)

Test mode	Mode 16, 19	Input Power	230 Vac, 50 Hz
Environmental Conditions	25 °C, 50% RH 997 mbar	Tested by	Andy Cheng

Test Results of Direct Application

Discharge Level (kV)	Polarity (+/-)	Test Point	Contact Discharge	Air Discharge	Performance Criterion
2, 4	+/-	1	Note	N/A	A
2, 4, 8	+/-	2, 3, 4	N/A	Note	A

Description of test points of direct application: Please refer to following page for representative mark only.

Test Results of Indirect Application


Discharge Level (kV)	Polarity (+/-)	Test Point	Horizontal Coupling Plane	Vertical Coupling Plane	Performance Criterion
2, 4	+/-	Four Sides	Note	Note	A

Description of test points of indirect application:


1. Front side 2. Rear side 3. Right side 4. Left side

Note: The EUT function was correct during the test.

Description of Test Points



970201A04



970201A04

13 Radiated, Radio-frequency, Electromagnetic Field Immunity Test (RS)

13.1 Test Specification

<EN 61000-6-1>

Basic Standard:	IEC 61000-4-3
Frequency Range:	80 MHz - 1000 MHz, 1400-2000MHz, 2000-2700MHz
Field Strength:	3 V/m, 1 V/m
Modulation:	1kHz Sine Wave, 80%, AM Modulation
Frequency Step:	1 % of preceding frequency value
Polarity of Antenna:	Horizontal and Vertical
Antenna Height:	1.5m
Dwell Time:	3 seconds

<EN 55024>

Basic Standard:	IEC 61000-4-3
Frequency Range:	80 MHz - 1000 MHz
Field Strength:	3 V/m
Modulation:	1kHz Sine Wave, 80%, AM Modulation
Frequency Step:	1 % of preceding frequency value
Polarity of Antenna:	Horizontal and Vertical
Antenna Height:	1.5m
Dwell Time:	3 seconds

13.2 Test Instruments

DESCRIPTION & MANUFACTURER	MODEL NO.	SERIAL NO.	CALIBRATED UNTIL
R&S Signal Generator	SML03	101074	Nov. 01, 2008
AR RF Amplifier	60S1G3	304334	NA
Electric Field Sensor	CTR1001A	06D00232SN0-02	Aug. 08, 2008
BOONTON RF Voltage Meter	4232A	10180	Jun. 07, 2008
BOONTON Power Sensor	51011-EMC	34152	Jun. 06, 2008
BOONTON Power Sensor	51011-EMC	34153	May 27, 2008
FRANKONIA Power Amplifier	FLH 100	0042	NA
Log-Periodic Antenna	AT 5080	312115	NA
HP-IB Extender	37204	3212U26684	NA
EMCO BiconiLog Antenna	3141	1001	NA
COMTEST Compact Full Anechoic Chamber (7x3x3 m)	CFAC	ADT-S01	Oct. 20, 2008
Software	ADT_RS_V7.6	NA	NA

- NOTE:**
1. The test was performed in RS Room No.1.
 2. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA
 3. Test date: Mar. 27 ~ Apr. 9, 2008

13.3 Test Arrangement

The test procedure was in accordance with IEC 61000-4-3. <EN 61000-6-1>

- a. The testing was performed in a modified semi-anechoic chamber.
- b. The frequency range is swept from 80 MHz to 1000 MHz, 1400 MHz to 2000 MHz, 2000MHz to 2700MHz, with the signal 80% amplitude modulated with a 1kHz sine wave.
- c. The dwell time of the amplitude modulated carrier was applied in 3 s at each of the frequencies during the scan. The sensitive frequencies (e.g. clock frequencies or frequencies identified by the manufacturer or obtained as outcome of the test) shall be analyzed in addition to the stepped frequencies.
- d. The field strength level was 3 V/m, 1V/m.
- e. The test was performed with the EUT exposed to both vertically and horizontally polarized fields on each of the four sides.

The test procedure was in accordance with IEC 61000-4-3. <EN 55024>

- a. The testing was performed in a modified semi-anechoic chamber.
- b. The frequency range is swept from 80 MHz to 1000 MHz, with the signal 80% amplitude modulated with a 1kHz sine wave.
- c. The field strength level was 3 V/m.
- d. The test was performed with the EUT exposed to both vertically and horizontally polarized fields on each of the four sides.




Table-top Equipment

The EUT installed in a representative system as described in section 7 of IEC 61000-4-3 was placed on a non-conductive table 0.8 meters in height. The system under test was connected to the power and signal wire according to relevant installation instructions.

For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

13.4 Test Results

Test mode	Mode 1, 16, 19	Input Power	230 Vac, 50 Hz
Environmental conditions	25 °C, 65% RH, 1000mbar	Tested by	Andy Cheng

Frequency (MHz)	Polarity	Azimuth(°)	Applied Field Strength		Observation	Performance Criterion
			(V/m)	Modulation		
80 -1000	V&H	0, 90, 180, 270	3	80% AM (1kHz)	Note	A
1400 - 2000	V&H	0, 90, 180, 270	3	80% AM (1kHz)	Note	A
2000 -2700	V&H	0, 90, 180, 270	1	80% AM (1kHz)	Note	A

Note: The EUT function was correct during the test.

14 Electrical Fast Transient/Burst Immunity Test (EFT)

14.1 Test Specification

<EN 61000-6-1 & EN 55024>

Basic Standard: IEC 61000-4-4

Test Voltage: Signal / telecommunication port: N/A

Input DC power port: N/A

Input AC power port: ±1kV

Impulse Repetition Frequency: xDSL telecommunication port: 100kHz

others: 5kHz

Impulse Wave Shape: 5/50 ns

Burst Duration: 0.75 ms for 100kHz Repetition Frequency

15 ms for 5kHz Repetition Frequency

Burst Period: 300 ms

Test Duration: 1 min.

14.2 Test Instruments


DESCRIPTION & MANUFACTURER	MODEL NO.	SERIAL NO.	CALIBRATED UNTIL
Haefely, EFT Generator	PEFT 4010	154954	Mar. 10, 2009
Haefely, Capacitive Clamp	IP4A	155173	NA

NOTE: 1. The test was performed in EMS Room No. 1.

2. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
3. Test date: Mar. 27 ~ Apr. 9, 2008

14.3 Test Arrangement

- a. Both positive and negative polarity discharges were applied.
- b. The distance between any coupling devices and the EUT should be 0.5 m for table-top equipment testing, and 1.0 m for floor standing equipment.
- c. The duration time of each test sequential was 1 minute.
- d. The transient/burst waveform was in accordance with IEC 61000-4-4, 5/50 ns.



NOTE:

- (A) location for supply line coupling
 (B) location for signal lines coupling

For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

14.4 Test Results (1)

Test mode	Mode 1	Input Power	230 Vac, 50 Hz
Environmental conditions	20 °C, 70% RH, 1001mbar	Tested by	Andy Cheng

Input AC power port

Voltage (kV)	Test Point	Polarity (+/-)	Observation	Performance Criterion
1	L1	+/-	Note	B
1	L2	+/-	Note	B
1	L1-L2	+/-	Note	B

Note: The power of DC output was flickered +0.069V or -0.046V during the test, but self-recoverable after the test.

14.5 Test Results (2)

Test mode	Mode 16	Input Power	230 Vac, 50 Hz
Environmental conditions	20 °C, 70% RH, 1001mbar	Tested by	Andy Cheng

Input AC power port

Voltage (kV)	Test Point	Polarity (+/-)	Observation	Performance Criterion
1	L1	+/-	Note	B
1	L2	+/-	Note	B
1	L1-L2	+/-	Note	B

Note: The power of DC output was flickered +0.12V or -0.03V during the test, but self-recoverable after the test.

14.6 Test Results (3)

Test mode	Mode 19	Input Power	230 Vac, 50 Hz
Environmental conditions	20 °C, 70% RH, 1001mbar	Tested by	Andy Cheng

Input AC power port

Voltage (kV)	Test Point	Polarity (+/-)	Observation	Performance Criterion
1	L1	+/-	Note	B
1	L2	+/-	Note	B
1	L1-L2	+/-	Note	B

Note: The power of DC output was flickered +0.31V during the test, but self-recoverable after the test.

15 Surge Immunity Test

15.1 Test Specification

<EN 61000-6-1 & EN 55024>

Basic Standard:

IEC 61000-4-5

Wave-Shape:

Signal / telecommunication port (direct to outdoor cables*):
 10/700 μ s Open Circuit Voltage
 5/320 μ s Short Circuit Current

Input DC power port (direct to outdoor cables*):
 1.2/50 μ s Open Circuit Voltage
 8/20 μ s Short Circuit Current

Input AC power port:
 1.2/50 μ s Open Circuit Voltage
 8/20 μ s Short Circuit Current

Test Voltage:

Signal and telecommunication ports**:
 w/o primary protectors: N/A
 with primary protectors fitted: N/A

Input DC power port:
 Line to earth or ground:N/A

Input AC power ports:
 Line to line: $\pm 0.5\text{kV}$, $\pm 1\text{kV}$
 Line to earth or ground: N/A

AC Phase Angle (degree):

0°, 90°, 180°, 270°

Pulse Repetition Rate:

1 time / 20 sec.

Number of Tests:

5 positive and 5 negative at selected points

* This test is only applicable only to ports, which according to the manufacturer's specification, may connect directly to outdoor cables.

** For ports where primary protection is intended, surges are applied at voltages up to 4 kV with the primary protectors fitted. Otherwise the 1 kV test level is applied without primary protection in place.

15.2 Test Instruments

Description & Manufacturer	Model No.	Serial No.	Cal. Date	Cal. Due
TESEQ, Surge Simulator	NSG 3060	1572	May 19, 2016	May 18, 2017
Coupling Decoupling Network	CDN-UTP8	028	Aug. 22, 2016	Aug. 21, 2017
TESEQ Coupling Decoupling Network	CDN HSS-2	41009	May 21, 2016	May 20, 2017
TESEQ Coupling Decoupling Networ	CDN 118-T8	40386	Sep. 09, 2016	Sep. 08, 2017

- Notes:
1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
 2. The test was performed in EMS Room No. 2.
 3. Tested Date: Oct. 5, 2016.

15.3 Test Arrangement

a. Input AC/DC Power ports:

The surge is to be applied to the EUT power supply terminals via the capacitive coupling network. Decoupling networks are required in order to avoid possible adverse effects on equipment not under test that may be powered by the same lines, and to provide sufficient decoupling impedance to the surge wave. The power cord between the EUT and the coupling/decoupling networks shall be 2 meters in length (or shorter).

For double-insulated products without PE or external earth connections, the test shall be done in a similar way as for grounded products but without adding any additional external grounded connections. If there are no other possible connections to earth, line-to-ground tests may be omitted.

b. Signal and telecommunication ports,

- Unshielded unsymmetrical interconnection lines:

The surge is applied to the lines via the capacitive coupling. The coupling / decoupling networks shall not influence the specified functional conditions of the EUT. The interconnection line between the EUT and the coupling/decoupling networks shall be 2 meters in length.

- Unshielded symmetrical interconnections communication lines:

The surge is applied to the lines via gas arrestors coupling. Test levels below the ignition point of the coupling arrestor cannot be specified. The interconnection line between the EUT and the coupling/decoupling networks shall be 2 meters in length.

- High speed communications lines

Prior to the test, the correct operation of the port shall be verified; the external connection shall then be removed and the surge applied directly to the port's terminals with no coupling /decoupling network. After the surge, the correct operation of the port shall again be verified.

- Shielded lines:

- Direct application,

The EUT is isolated from ground and the surge is applied to its metallic enclosure; the termination (or auxiliary equipment) at the port(s) under test is grounded. This test applies to equipment with single or multiple shielded cables.

Rules for application of the surge to shielded lines:

- a) Shields grounded at both ends

- The surge injection on the shield.


- b) Shields grounded at one end

- If in the installation the shield is connected only at the auxiliary equipment, test shall be done in that configuration but with the generator still connected to the EUT side. If cable lengths allow, the cables shall be on insulated supports 0,1 m above the ground plane or cable tray.

For products which do not have metallic enclosures, the surge is applied directly to the shielded cable.

- Alternative coupling method for testing single cables in a multi-shield configuration,

Surges are applied in close proximity to the interconnection cable under test by a wire. The length of the cable between the port(s) under test and the device attached to the other end of the cable shall be the lesser of: the maximum length permitted by the EUT's specification, or 20 m. Where the length exceeds 1 m, excess lengths of cables shall be bundled at the approximate centre of the cables with the bundles 30 cm to 40 cm in length.



For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

15.4 Test Results

Test mode	Mode 1	Input Power	230 Vac, 50 Hz
Environmental conditions	26 °C, 63% RH, 999mbar	Tested by	Ken Chen

Input AC power port

Voltage (kV)	Test Point	Polarity (+/-)	Observation	Performance Criterion
0.5, 1	L1-L2	+/-	Note	A

Note: The EUT function was correct during the test.

16 Immunity to Conducted Disturbances Induced by RF Fields (CS)

16.1 Test Specification

<EN 61000-6-1 & EN 55024>

Basic Standard:	IEC 61000-4-6
Frequency Range:	0.15 MHz - 80 MHz
Voltage Level:	3 V
Modulation:	1kHz Sine Wave, 80%, AM Modulation
Frequency Step:	1 % of preceding frequency value
Dwell Time	3 seconds


16.2 Test Instruments

DESCRIPTION & MANUFACTURER	MODEL NO.	SERIAL NO.	CALIBRATED UNTIL
ROHDE & SCHWARZ Signal Generator	SMY01	841104/033	Nov. 27, 2008
Digital Sweep Function Generator	8120	984801	NA
AR Power Amplifier	75A250AM1	306331	NA
FCC Coupling Decoupling Network	FCC-801-M3-25A	48	Jul. 22, 2008
FCC Coupling Decoupling Network	FCC-801-M3-25A	01022	Mar. 02, 2009
FCC Coupling Decoupling Network	FCC-801-M2-16A	01047	Jul. 13, 2008
FISCHER CUSTOM COMMUNICATIONS EM Injection Clamp	FCC-203I	50	NA
FCC Coupling Decoupling Network	FCC-801-T8	02038	May 28, 2008
FCC Coupling Decoupling Network	FCC-801-T2	02020	May 28, 2008
FCC Coupling Decoupling Network	FCC-801-T4	02031	Jun. 14, 2008
R&S Power Sensor	NRV-Z5	837878/038	Oct. 25, 2008
R&S Power Sensor	NRV-Z5	837878/039	Oct. 25, 2008
R&S Power Meter	NRVD	837794/040	Oct. 25, 2008
Software	ADT_CS_V7.3.8	NA	NA

- NOTE:** 1. The test was performed in CS Room No. 1.
 2. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
 3. Test date: Mar. 27 ~ Apr. 9, 2008

16.3 Test Arrangement

- The EUT shall be tested within its intended operating and climatic conditions.
- An artificial hand was placed on the hand-held accessory and connected to the ground reference plane.
- One of the CDNs not used for injection was terminated with 50 ohm, providing only one return path. All other CDNs were coupled as decoupling networks.
- The frequency range is swept from 150 kHz to 80 MHz, using the signal level established during the setting process and with a disturbance signal of 80 % amplitude. The signal is modulated with a 1 kHz sine wave, pausing to adjust the RF signal level or the switch coupling devices as necessary. Where the frequency is swept incrementally, the step size shall not exceed 1 % of the preceding frequency value.
- Attempts should be made to fully exercise the EUT during testing, and to fully interrogate all exercise modes selected for susceptibility.



Note:

1. The EUT clearance from any metallic obstacles shall be at least 0,5 m.
2. Interconnecting cables ($\leq 1 \text{ m}$) belonging to the EUT shall remain on the insulating support.
3. The equipment to be tested is placed on an insulating support of 0,1 meters height above a ground reference plane. All relevant cables shall be provided with the appropriate coupling and decoupling devices at a distance between 0,1 meters and 0,3 meters from the projected geometry of the EUT on the ground reference plane.

For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

16.4 Test Results

Test mode	Mode 1, 16, 19	Input Power	230 Vac, 50 Hz
Environmental conditions	26 °C, 65% RH, 1001mbar	Tested by	Andy Cheng

Frequency (MHz)	Level (Vrms)	Tested Line	Injection Method	Return Path	Observation	Performance Criterion
0.15 – 80	3	AC Power	CDN-M2	N/A	Note	A

Note: The EUT function was correct during the test.

17 Power Frequency Magnetic Field Immunity Test

17.1 Test Specification

<EN 61000-6-1>

Basic Standard:	IEC 61000-4-8
Frequency Range:	50Hz, 60Hz
Field Strength:	3A/m
Observation Time:	1 minute
Inductance Coil:	Rectangular type, 1 m x 1 m

<EN 55024>

Basic Standard:	IEC 61000-4-8
Frequency Range:	50Hz
Field Strength:	1 A/m
Observation Time:	1 minute
Inductance Coil:	Rectangular type, 1 m x 1 m

17.2 Test Instruments


DESCRIPTION & MANUFACTURER	MODEL NO.	SERIAL NO.	CALIBRATED UNTIL
HAEFELY Magnetic Field Tester	MAG 100.1	083794-06	NA
COMBINOVA Magnetic Field Meter	MFM10	224	Aug. 23, 2008

NOTE: 1. The test was performed in EMS Room No. 1.

2. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
3. Test date: Mar. 27 ~ Apr. 9, 2008

17.3 Test Arrangement

- a. The equipment is configured and connected to satisfy its functional requirements.
- b. The power supply, input and output circuits shall be connected to the sources of power supply, control and signal.
- c. The cables supplied or recommended by the equipment manufacturer shall be used. 1 meter of all cables used shall be exposed to the magnetic field.



TABLETOP EQUIPMENT

The equipment shall be subjected to the test magnetic field by using the induction coil of standard dimension (1 m x 1 m). The induction coil shall then be rotated by 90 degrees in order to expose the EUT to the test field with different orientations.

For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

17.4 Test Results

Test mode	Mode 1, 16, 19	Input Power	230 Vac, 50 Hz/ 60 Hz
Environmental conditions	22 °C, 70% RH, 999mbar	Tested by	Andy Cheng

Application	Frequency (Hz)	Field Strength (A/m)	Observation	Performance Criterion
X - Axis	50, 60	3	Note	A
Y - Axis	50, 60	3	Note	A
Z - Axis	50, 60	3	Note	A

Note: The EUT function was correct during the test.

18 Voltage Dips and Interruptions

18.1 Test Specification

<EN 61000-6-1>

Basic Standard:	IEC 61000-4-11
Test levels:	Voltage Dips: 0% residual – 0.5, 1 period 70% residual – 25, 30 period
Interval between Event:	Voltage Interruptions: 0% residual – 250, 300 period
Sync Angle (degrees):	Minimum ten seconds
Test Cycle:	0° / 180°
	3 times

<EN 55024>

Basic Standard:	IEC 61000-4-11
Test levels:	Voltage Dips: >95% reduction – 0.5 period 30% reduction – 25 periods
Interval between Event:	Voltage Interruptions: >95% reduction – 250 periods
Sync Angle (degrees):	Minimum ten seconds
Test Cycle:	0° / 180°
	3 times


18.2 Test Instruments

DESCRIPTION & MANUFACTURER	MODEL NO.	SERIAL NO.	CALIBRATED UNTIL
HAEFELY Mains Interference Simulator	PLINE1610	083690-17	May 08, 2008

- NOTE:**
1. The test was performed in EMS Room No. 1.
 2. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
 3. Test date: Mar. 27 ~ Apr. 9, 2008

18.3 Test Arrangement

The EUT shall be tested for each selected combination of test levels and duration with a sequence of 3 dips/interruptions with intervals of 10 s minimum (between each test event). Each representative mode of operation shall be tested. Abrupt changes in supply voltage shall occur at 0 degree crossover point of the voltage waveform.



For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

18.4 Test Results

Test mode	Mode 1, 16, 19	Input Power	230Vac, 50Hz, 220Vac, 60Hz, 110Vac, 60Hz, 100Vac, 50Hz
Environmental conditions	26 °C, 63% RH, 999mbar	Tested by	Andy Cheng

Input Power for testing: 230 Vac, 50 Hz					
Voltage Residual (%)	Duration (period)	Interval (sec)	Times	Observation	Performance Criterion
0	0.5, 1	10	3	Note 1	A
70	25	10	3	Note 1	A
0	250	10	3	Note 2	B
Input Power for testing: 220 Vac, 60 Hz					
Voltage Residual (%)	Duration (period)	Interval (sec)	Times	Observation	Performance Criterion
0	0.5, 1	10	3	Note 1	A
70	30	10	3	Note 1	A
0	300	10	3	Note 2	B
Input Power for testing: 100 Vac, 50 Hz					
Voltage Residual (%)	Duration (period)	Interval (sec)	Times	Observation	Performance Criterion
0	0.5, 1	10	3	Note 1	A
70	25	10	3	Note 1	A
0	250	10	3	Note 2	B
Input Power for testing: 110 Vac, 60 Hz					
Voltage Residual (%)	Duration (period)	Interval (sec)	Times	Observation	Performance Criterion
0	0.5, 1	10	3	Note 1	A
70	30	10	3	Note 1	A
0	300	10	3	Note 2	B

Note: 1. The EUT function was correct during the test.
 2. The EUT reset during the test.

19 Pictures of Test Arrangements

19.1 Conducted Emission from the AC Mains Power Port - EN 61000-6-3



19.2 Conducted Emission from the AC Mains Power Port - EN 55032



19.3 Radiated Emission at Frequencies up to 1GHz - EN 61000-6-3



19.4 Radiated Emission at Frequencies up to 1GHz - EN 55032



19.5 Harmonics Current, Voltage Fluctuations and Flicker Measurement

For Mode 1



For Mode 16



For Mode 19



19.6 Electrostatic Discharge Immunity Test (ESD)

For Mode 1



For Mode 16




For Mode 19




19.7 Radio-frequency, Electromagnetic Field Immunity Test (RS)


For Mode 1



For Mode 16




For Mode 19




19.8 Electrical Fast Transient/Burst Immunity Test (EFT)


Mains ports – For Mode 1



Mains ports – For Mode 16



Mains ports – For Mode 19



19.9 Surge Immunity Test

Mains ports



19.10 Conducted Disturbances Induced by RF Fields (CS)


Mains ports – For Mode 1



Mains ports – For Mode 16



Mains ports – For Mode 19



19.11 Power Frequency Magnetic Field Immunity Test (PFMF)

For Mode 1



For Mode 16



For Mode 19



19.12 Voltage Dips and Interruptions

For Mode 1



For Mode 16



For Mode 19



Appendix – Information on the Testing Laboratories

We, Bureau Veritas Consumer Products Services (H.K.) Ltd., Taoyuan Branch, were founded in 1988 to provide our best service in EMC, Radio, Telecom and Safety consultation. Our laboratories are accredited and approved according to ISO/IEC 17025.

If you have any comments, please feel free to contact us at the following:

Linko EMC/RF Lab

Tel: 886-2-26052180

Fax: 886-2-26051924

Hsin Chu EMC/RF/Telecom Lab

Tel: 886-3-6668565

Fax: 886-3-6668323

Hwa Ya EMC/RF/Safety Lab

Tel: 886-3-3183232

Fax: 886-3-3270892

Email: service.adt@tw.bureauveritas.com

Web Site: www.bureauveritas-adt.com

The address and road map of all our labs can be found in our web site also.

--- END ---