

TEST REPORT

FOR

AC/DC Power Supply

BRAND : 

MODEL : TPP 15-105A-J

SERIES MODEL : Refer to item 5.1 for more details

REPORT NUMBER : 4790771479A-EN-E0-V0

ISSUE DATE : Mar. 22, 2023

Prepared for

TRACO ELECTRONIC AG

Sihlbruggstrasse 111 CH-6340 Baar Switzerland

Prepared by

Underwriters Laboratories Taiwan Co., Ltd.,

**Building B and Building E, No. 372-7, Sec. 4, Zhongxing Rd., Zhudong Township,
Hsinchu County, Taiwan**

Tel: +886.2.2896.7790

Fax: +886.3.583.7948

Website: www.ul.com



The results reported herein have been performed in accordance with the laboratory's terms of accreditation. This report shall not be reproduced except in full without the written approval of the Laboratory. The results in this report are responsible of the test sample(s) provided by the client only and are not to be used to indicate applicability to other similar products.

Revision History

<u>Rev.</u>	<u>Issue Date</u>	<u>Revisions</u>	<u>Revised By</u>
--	Mar. 22, 2023	Initial Issue	Sally Lu

Summary of Test Results				
EMISSION				
Standard	Test Item	Limit	Result	Remark
EN 55032:2015 / A11: 2020	Conducted disturbance at mains terminals ports	Class B	PASS	N/A
	Conducted common mode (asymmetric mode) disturbance telecommunication ports	Class B	N/A	(Note 1)
	Radiated disturbance below 1GHz	Class B	PASS	N/A
	Radiated disturbance above 1 GHz	Class B	N/A	(Note 2)
EN IEC 61000-3-2: 2019/A1: 2021	Harmonic current disturbance	Class A	PASS	N/A
EN 61000-3-3: 2013/A2: 2021	Voltage Fluctuations & Flicker	Refer to 6.5.1	PASS	N/A

Note 1: Since the EUT does not contain asymmetric port, the test is unnecessary.

Note 2: Since the highest frequency of EUT is less than 108 MHz, the measurement above 1 GHz is unnecessary.

Summary of Test Results				
IMMUNITY				
Basic Standard	Test Item	Class / Severity	Require Performance Criteria	Result
EN 61000-4-2: 2009	Electrostatic discharge immunity	Contact ±4 kV Air ±8 kV	B	PASS (Note 5)
EN IEC 61000-4-3: 2020	Continuous RF electromagnetic field disturbances, swept test	80-1000MHz 3V/m 80%, 1kHz, AM	A	PASS
	Continuous RF electromagnetic field disturbances, spot test	1800 ;2600 ;3500 5000 MHz (±1%) 3V/m 80%, 1kHz, AM (Note 2)	A	PASS
	immunity levels to common wireless communication devices	See Table I.1	A	PASS
EN 61000-4-4: 2012	Electrical fast transient/burst immunity	1kV(AC Mains) 5/50ns, 5kHz	B	PASS
		0.5kV(DC Ports) 5/50ns, 5kHz	B	N/A (Note 3)
		0.5kV(Signal Lines) 5/50ns, 5kHz	B	N/A (Note 4)
EN 61000-4-5: 2014 / A1: 2017	Surge immunity	AC Mains 2.0kV(Common) 1.0kV(Differential) 1.2/50us	B	PASS
		DC Ports 0.5kV Line to Ground	B	N/A (Note 3)
		Signal port 1.0kV (w/o primary protector) 4.0kV (w primary protector) 1.2/50us or 10/700us (Note 1)	C	N/A (Note 4)
		0.5kV Coaxial or shielded to ground 1.2/50 (8/20) us	B	N/A (Note 4)

Summary of Test Results				
IMMUNITY				
Basic Standard	Test Item	Class / Severity	Require Performance Criteria	Result
EN 61000-4-6: 2014 / AC:2015	Continuous induced RF disturbances	AC Mains 0.15~10MHz, 3V 10~30MHz, 3~1V 30~80MHz, 1V with 1kHz 80% AM (Note 2)	A	PASS
		DC Ports 0.15~10MHz, 3V 10~30MHz, 3~1V 30~80MHz, 1V with 1kHz 80% AM (Note 2)	A	N/A (Note 3)
		Signal Line 0.15~10MHz, 3V 10~30MHz, 3~1V 30~80MHz, 1V with 1kHz 80% AM (Note 2)	A	N/A (Note 4)
EN 61000-4-8: 2010	Power frequency magnetic field immunity (Continuous)	50 Hz, 1 A/m(r.m.s)	A	PASS
EN IEC 61000-4-11: 2020	Voltage dips, short interruptions and voltage variations immunity	Voltage dips, <5% residual with 0.5cycles	B	PASS
		Voltage dips, 70% residual with 25 cycles	C	
		Voltage interruptions, <5% residual with 250 cycles	C	

Note 1: Where the coupling network for the 10/700 μs waveform affects the functioning of high speed data ports, the test shall be carried out using a 1,2/50 (8/20) μs waveform and appropriate coupling network.

Note 2: The frequency range is scanned as specified. However, when specified in EN 55035 , an additional EUT contains telephony functional test shall be carried out at a limited number of frequencies. The selected frequencies for conducted immunity tests are: 0,2; 1; 7,1; 13,56; 21; 27,12 and 40,68 MHz (±1 %) and radiated immunity tests are 80; 120; 160; 230; 434; 460; 600; 863 and 900MHz (±1 %).

Note 3: Since the EUT does not contain DC power port, the test is unnecessary.

Note 4: Since the EUT does not contain signal port, the test is unnecessary.

Note 5: Customers add countermeasure components to the fixture board. For the corresponding components, please refer to the appendix III.”

Table I.1 – Guidance on the selection of immunity levels to common wireless communication devices

Table clause	Approximate protection distance (m)	Calculated RF field strength in V/m for frequencies and protection distances simulating different radio transmission types, assuming a given ERP						
		LTE/UMTS (0,2 W) 800 MHz	GSM		WiMAX/3 G (1,26 W) 2,6 GHz	WiMAX (1,26 W) 3,5 GHz	Wi-Fi (1 W) 5 GHz	Maximum RF field strength at any frequency
			900 MHz	1,8 GHz				
I.1.1	3,0	0,6	1,8	1,3	1,5	1,5	1,3	3
I.1.2	1,5	1,2	3,7	2,6	2,9	2,9	2,6	4
I.1.3	1,0	1,7	5,5	3,9	4,4	4,4	3,9	6
I.1.4	0,5	3,3	10,5	10,5	11,8	11,8	10,5	12
I.1.5	0,2	8,3	26,4	26,4	29,6	29,6	26,4	30

The protection distance is not the test distance as defined in IEC 61000-4-3:2006/AMD1:2007/AMD2:2010, but the shortest expected operating distance between the EUT and the interfering wireless communication device at which the immunity performance criteria will be satisfied.

TABLE OF CONTENTS

1. ATTESTATION OF TEST RESULTS	9
2. TEST METHODOLOGY	10
3. FACILITIES AND ACCREDITATION	10
4. CALIBRATION AND UNCERTAINTY	11
4.1. Measuring Instrument Calibration	11
4.2. Measurement Uncertainty	11
5. EQUIPMENT UNDER TEST	13
5.1. Description of EUT	13
5.2. Test Mode	15
5.3. EUT Operation Test Setup	15
5.4. Monitoring of EUT for All Immunity Test	15
5.5. Accessory.....	16
5.6. Block diagram showing the configuration of system tested.....	16
5.7. Description of support units	18
5.8. Measuring Instrument List	19
6. EMISSION TEST	23
6.1. Conducted Disturbance Measurement	23
6.1.1. Limits of conducted disturbance voltage and common mode disturbance.	23
6.1.2. Test Procedure	24
6.1.3. Test Setup	24
6.1.4. Test Result	25
6.2. Radiated Disturbance Measurement(below 1GHz).....	27
6.2.1. Limits of radiated disturbance measurement.....	27
6.2.2. Test Procedure	28
6.2.3. Test Setup	28
6.2.4. Test Result	30
6.3. Harmonic Current Disturbance Measurement.....	32
6.3.1. Limits of Harmonic Current	32
6.3.2. Test Procedure	33
6.3.3. Test Setup	33
6.3.4. Test Condition.....	33
6.3.5. Test Result	34
6.4. Voltage Fluctuation and Flicker Measurement.....	37
6.4.1. Limits of Voltage Fluctuation and Flicker.....	37
6.4.2. Test Procedure	38
6.4.3. Test Setup	38
6.4.4. Test Condition.....	38
6.4.5. Test Result	39

7. IMMUNITY TEST	40
7.1. Performance Criteria	40
7.2. Electrostatic Discharge Immunity Test.....	41
7.2.1. Test Specification	41
7.2.2. Test Procedure	41
7.2.3. Test Setup	42
7.2.4. Test Result	44
7.3. Radio Frequency Electromagnetic Field Immunity Test.....	48
7.3.1. Test Specification	48
7.3.2. Test Procedure	48
7.3.3. Test Setup	49
7.3.4. Test Result	50
7.4. Electrical Fast Transient/Burst Immunity Test.....	52
7.4.1. Test Specification	52
7.4.2. Test Procedure	52
7.4.3. Test Setup	53
7.4.4. Test Result	54
7.5. Surge Immunity Test	55
7.5.1. Test Specification	55
7.5.2. Test Procedure	55
7.5.3. Test Result	56
7.6. Immunity to Conducted Disturbances Induced by RF Fields.....	57
7.6.1. Test Specification	57
7.6.2. Test Procedure	57
7.6.3. Test Setup	58
7.6.4. Test Result	59
7.7. Power frequency magnetic field immunity Test.....	60
7.7.1. Test Specification	60
7.7.2. Test Procedure	60
7.7.3. Test Setup	61
7.7.4. Test Results.....	62
7.8. Voltage Dips and Short Interruptions Immunity Test.....	63
7.8.1. Test Specification	63
7.8.2. Test Procedure	63
7.8.3. Test Setup	63
7.8.4. Test Result	64
Appendix I: Photographs of EMC Test Configuration.....	65
Appendix II: Photographs of the EUT.....	73
Appendix III: Countermeasure file for ESD	74
Annex : Additional test request by client	75

1. ATTESTATION OF TEST RESULTS

COMPANY NAME: TRACO ELECTRONIC AG
Sihlbruggstrasse 111 CH-6340 Baar Switzerland

MANUFACTURER: TRACO ELECTRONIC AG
Sihlbruggstrasse 111 CH-6340 Baar Switzerland

EUT DESCRIPTION: AC/DC Power Supply

BRAND: 

MODEL: TPP 15-105A-J

SERIES MODEL : Refer to item 5.1 for more details

DATE of TESTED: Dec. 6, 2022 ~ Dec. 19, 2022

APPLICABLE STANDARDS	
STANDARDS	TEST RESULTS
EN 55032 :2015 / A11: 2020 EN 55035: 2017 / A11: 2020 EN IEC 61000-3-2: 2019/A1: 2021 EN 61000-3-3: 2013/A2: 2021	PASS

Underwriters Laboratories Taiwan Co., Ltd. Tested the above equipment in accordance with the requirements set forth in the above standards. All indications of Pass/Fail in this report are opinions expressed by Underwriters Laboratories Taiwan Co., Ltd. Based on interpretations and/or observations of test results. The test results show that the equipment tested is capable of demonstrating compliance with the requirements as documented in this report.

Note: The results documented in this report apply only to the tested sample, under the conditions and modes of operation as described herein. This document may not be altered or revised in any way unless done so by Underwriters Laboratories Taiwan Co., Ltd. And all revisions are duly noted in the revisions section. Any alteration of this document not carried out by Underwriters Laboratories Taiwan Co., Ltd. Will constitute fraud and shall nullify the document. This report must not be used by the client to claim product certification, approval, or endorsement by NVLAP, NIST, any agency of the Federal Government, or any agency of any government.

Prepared By:



Sally Lu Date : Mar. 22, 2023
Project Handler

Approve and Authorized By:



Hank Yang Date : Mar. 22, 2023
Laboratory Engineer Associate

2. TEST METHODOLOGY

All tests were performed in accordance with the correspond to each test item's procedure of this report and refer to each standard.

3. FACILITIES AND ACCREDITATION

Test Location	Underwriters Laboratories Taiwan Co., Ltd.,
Address	Building B and Building E, No. 372-7, Sec. 4, Zhongxing Rd., Zhudong Township, Hsinchu County, Taiwan
Description	All measurement facilities use to collect the measurement data are located at Building B and Building E, No. 372-7, Sec. 4, Zhongxing Rd., Zhudong Township, Hsinchu County, Taiwan

4. CALIBRATION AND UNCERTAINTY

4.1. Measuring Instrument Calibration

The measuring equipment utilized to perform the tests documented in this report has been calibrated in accordance with the manufacturer's recommendations, and is traceable to recognized national standards.

4.2. Measurement Uncertainty

The decision rule refer to CISPR 16-4-2 clause 4.2 accordingly. If U_{lab} is less than U_{cispr} , then:

- compliance is deemed to occur if no measured disturbance level exceeds the disturbance limit ;
- non-compliance is deemed to occur if any measured disturbance level exceeds the disturbance limit.

Where relevant, the following measurement uncertainty levels have been estimated for tests performed on the apparatus:

The following uncertainties have been calculated to provide a confidence level of 95 % using a coverage factor $k=2$.

Electromagnetic interference:

Test Item	Measurement Frequency Range	K	U(dB)
Conducted disturbance at mains terminals ports	0.15MHz ~ 30MHz	2	3.2
966-1 Test Site			
Radiated disturbance below 1 GHz	30MHz ~ 1000MHz	2	5.9

Test Item	K	Voltage(%)	Current(%)
Harmonic&Flicker	2	0.17	0.38

Electromagnetic sensitivity:

Test Item	Measurement Frequency Range	K	U(dB)
Radiated, radio frequency electromagnetic field immunity	80MHz ~ 6000MHz	2	2.1
Immunity to conducted disturbances, induced by radio-frequency fields (CDN)	0.15MHz ~ 80MHz	2	2.4

Test Item	K	Voltage(%)	Rise Time(%)	First Peak Current (%)	Current @ 30ns (%)	Current @ 60ns (%)
Electrostatic discharge immunity	2	2.8	7.2	3.4	3.1	3.7

Test Item	K	Peak Voltage(%)	Rise Time(%)	Pulse width(%)	Burst Period (%)	Burst duration (%)	Repetition rate (%)
Electrical fast transient/burst immunity	2	3.6	3.7	1.7	0.94	0.47	0.29

Test Item	K	Phase Shifting (%)	Voltage (%)	Current (%)	Front Time (For waveform of the surge voltage)(%)	Duration (For waveform of the surge voltage)(%)	Front Time (For waveform of the surge current)(%)	Duration (For waveform of the surge current)(%)
Surge immunity	2	1.1	3.6	2.7	1.2	0.43	5.9	0.79

Test Item	K	Magnetic field Strength(%)
Power Frequency Magnetic Field Immunity Test	2	4.9%

Test Item	K	Voltage(%)	Time (%)	Phase Angle (%)
Voltage dips, short interruptions and voltage variations immunity	2	2.3	3.1	1.1

5. EQUIPMENT UNDER TEST

5.1. Description of EUT

EUT Name:	AC/DC Power Supply
Brand:	
Model:	TPP 15-105A-J
Series Model:	TPP 15-103abc(x), TPP 15-105abc(x), TPP 15-107abc(x), TPP 15-109abc(x), TPP 15-112abc(x), TPP 15-115abc(x), TPP 15-118abc(x), TPP 15-124abc(x), TPP 15-128abc(x), TPP 15-136abc(x), TPP 15-148abc(x), TPP 15-153abc(x)
Power Rating:	From AC power
Highest Frequency within EUT:	Less than 108MHz
Condition of EUT:	Mass-Production Test sample
Sample ID:	5574627
Date Of Receipt Of Sample:	Nov. 28, 2022

Note :

1. The models difference table as below:

Model Number	Input Range (Vac)	Output Voltage (Vdc)
TPP 15-103abc(x)	85 ~ 264	3.3
TPP 15-105abc(x)	85 ~ 264	5
TPP 15-107abc(x)	85 ~ 264	7.5
TPP 15-109abc(x)	85 ~ 264	9
TPP 15-112abc(x)	85 ~ 264	12
TPP 15-115abc(x)	85 ~ 264	15
TPP 15-118abc(x)	85 ~ 264	18
TPP 15-124abc(x)	85 ~ 264	24
TPP 15-128abc(x)	85 ~ 264	28
TPP 15-136abc(x)	85 ~ 264	36
TPP 15-148abc(x)	85 ~ 264	48
TPP 15-153abc(x)	85 ~ 264	53

a can be B or blank
b can be A, A2, or blank
c can be -J, -M, -D or blank
(x) can be six variables, each variable may be A through Z, 0 through 9, dash, any punctuation marks or blank.
※ All the model's rated voltage is 100 ~ 240 Vac; input range is 85 ~ 264 Vac.

2. This supplemental report was issued based on the original report with report number 4790423395A-EN-E0-V0, the differences were as below:

- Change model, series model, applicant, manufacturer and brand.
- Remove EMI data from Mode 2.

3. According to above conditions, there is no addition test has to be performed. All test data are copied from the original test report (Report No.: 4790423395A-EN-E0-V0), and all data are verified to meet the requirements.

5.2. Test Mode

The Pre-test modes:

Mode	Description	Conducted Emission	Radiated Emission
Mode 1	Full Load (TPP 15-105A-J)	v	v

After pre-testing, the final test mode was displayed as below table.

Test Items		Test Mode
Emission	Conducted Emission	Mode 1
	Radiated Emission	Mode 1
	Harmonic & Flicker	Mode 1
Immunity	Electrostatic Discharge	Mode 1
	Radio Frequency Electromagnetic Field	Mode 1
	Electrical Fast Transient	Mode 1
	Surge Immunity	Mode 1
	Immunity to conducted disturbances, induced by radio-frequency fields	Mode 1
	Power frequency magnetic field immunity	Mode 1
	Voltage Dips and Interruptions	Mode 1

Note:

1. The customer only provided TPP 15-105A-J for the EMC test.

5.3. EUT Operation Test Setup

Mode 1 & 2: (For Emission)

- a. The EUT was linked to resistance load with full load during the testing.
- b. Power on the EUT and run test.

Mode 1: (For Immunity)

- a. The EUT was linked to resistance load with full load and the resistance load was connected with a meter during the testing.
- b. Power on the EUT and run test.

5.4. Monitoring of EUT for All Immunity Test


Audio	N/A
Visual	Monitor the output voltage through the meter.

5.5. Accessory


N/A

5.6. Block diagram showing the configuration of system tested


Mode 1 & 2: (For Emission test)



Mode 1: (For Immunity – RS, EFT, Surge, CS, PFMF, DIP test)



Mode 1: (For Immunity – ESD test)



5.7. Description of support units

The EUT has been tested as an independent unit together with other necessary accessories or support units. The following support units or accessories were used to form a representative test configuration during the tests.

Item	Equipment	Mfr/Brand	Model/Type No.	Series No.	FCC ID	Note
A	Voltage Meter	N/A	SD-670	N/A	N/A	N/A
B	Resistance Load	N/A	N/A	N/A	N/A	Provided by customer
C	Test board	N/A	N/A	N/A	N/A	Provided by customer

Item	Connection	Shielded Type	Note
1	AC power cable	Non-shielded	Provided by customer
2	DC Power Wire	Non-shielded	Provided by customer
3	DC Power wire	Non-shielded	N/A

5.8. Measuring Instrument List

Instrument					
Equipment	Manufacturer	Model No.	Serial No.	Last Cal.	Expired date
Conducted Disturbance					
EMI Test Receiver	Rohde & Schwarz	ESR7	101753	2022/11/10	2023/11/9
Two-Line V-Network	Rohde & Schwarz	ENV216	102136	2022/8/29	2023/8/28
Two-Path V-LISN	SCHWARZBECK	NSLK 8127	8127-946	2022/11/10	2023/11/9
RF Current Probe	FCC	F-52	171502	2022/1/25	2023/1/24
Coupling and Decoupling Network	TESEQ	ISN ST08	45105	2022/2/9	2023/2/8
Impedance Stabilization Network	TESEQ	ISN T800	42830	2022/3/23	2023/3/22
Impedance Stabilization Network	TESEQ	ISN T8-Cat6	39923	2022/2/14	2023/2/13
Capacitive Voltage Probe	TESEQ	CVP 2200A	44922	2022/2/16	2023/2/15
Impuls-Begrenzer Pulse Limiter	Rohde & Schwarz	ESH3-Z2	102219-Qt	2022/8/30	2023/8/29
Cable	TITAN	CFD200	T0732ACFD20020A300-2	2022/4/9	2023/4/8
Measurement Software	Farad	EZ-EMC Ver: UL-3A1.2	N/A	N/A	N/A
Radiated Disturbance					
966-1					
EMI Test Receiver	Rohde & Schwarz	ESR7	101755	2022/12/7	2023/12/6
Trilog-Broadband Antena with 5dB Attenuator	SCHWARZBECK	VULB 9168 & N-6-05	774 & AT-N0538	2022/2/8	2023/2/7
Preamplifier	EMC Instrument	EMC330E	980404	2022/5/13	2023/5/12
Preamplifier	EMC Instrument	EMC051835BE	980407	2022/1/14	2023/1/13
Cables	UltraPhase&EMC Instrument	A1K50-UP0358-A1K50-1500&EMC106-NM-SM-2500/8000	170111-3&170104/170223	2022/1/18	2023/1/17
Measurement Software	Farad	EZ-EMC Ver: UL-3A1	N/A	N/A	N/A
Voltage Harmonic & Flicker					
single phase coupling unit	TESEQ	CCN1000-1	1652A01270	2022/3/21	2023/3/20
Programmable AC and DC Power Sources	TESEQ	NSG1007	1652A00760	2022/3/21	2023/3/20
Measurement Software	TESEQ	WIN2100(4.28.0)	N/A	N/A	N/A

Instrument					
Equipment	Manufacturer	Model No.	Serial No.	Last Cal.	Expired date
Electrostatic discharge					
ESD Generator	TESEQ	NSG 437	1125	2022/11/23	2023/11/22
Barometer	TFA	DIVA PLUS	35.1078.10.IT	2022/6/7	2023/6/6
Radio frequency electromagnetic field immunity					
RF and Microwave Signal Generator	Rohde & Schwarz	SMB100A	113793	2022/2/20	2023/2/19
Power amplifier	Milmega	80RF1000-300	1077558	N/A	N/A
Power amplifier	Milmega	AS0860B	1077559	N/A	N/A
Directional coupler	Werlatone	C10117-10	111786	N/A	N/A
Directional coupler	Werlatone	C8719-20	111759	N/A	N/A
Antenna	AR	ATR80M6G	346008	N/A	N/A
Antenna	SCHWARZBECK	STLP 9149	00441	N/A	N/A
RF switch	OSP	OSP	N/A	N/A	N/A
Power Meter	Rohde & Schwarz	NRP2	105524	2022/9/13	2023/9/12
Power Sensor	Rohde & Schwarz	NRP-Z91	103732	2022/9/13	2023/9/12
Power Sensor	Rohde & Schwarz	NRP-Z91	103733	2022/9/13	2023/9/12
Audio Analyzer	Rohde & Schwarz	UPV	104227	2022/11/28	2023/11/27
Pressure-field 1/2" Microphone	Bruel&Kjaer	Type 4192	3069928	2022/8/26	2023/8/25
GPS signal generator	Keysight Technologies	N5172B	MY56200315	2022/1/14	2023/1/13
Radio Communication Analyzer	Rohde & Schwarz	CMW500	161254	2022/12/10	2023/12/9
Microphone Adaptation Amplifier	Bruel&Kjaer	Type 5935	3070463	2022/8/1	2023/7/31
Measurement Software	Rohde & Schwarz	EMC32, VER.10.60.20	N/A	N/A	N/A
Electrical fast transient					
Ultra Compact Simulator	EM TEST	UCS 500N7	P1623180275	2022/11/24	2023/11/23
Capacitive Coupling Clamp	EM TEST	HFK	P1642185790	2022/11/25	2023/11/24
Measurement Software	TESEQ	IEC.control, VER.7.1.5	N/A	N/A	N/A

Instrument					
Equipment	Manufacturer	Model No.	Serial No.	Last Cal.	Expired date
Surge					
Ultra Compact Simulator	EM TEST	UCS 500N7	P1623180275	2022/11/24	2023/11/23
Telecom Surge Generator	EM TEST	TSurge7	P1620180015	2022/11/23	2023/11/22
Coupling and Decoupling Network	EM TEST	CNV 508T5	P1637184038	2022/11/23	2023/11/22
Coupling and Decoupling Network	TESEQ	CDN HSS-2	45091	2022/11/23	2023/11/22
Measurement Software	TESEQ	IEC.control, VER.7.1.5	N/A	N/A	N/A
Immunity to conducted disturbances, induced by radio-frequency fields					
Signal Generator	Rohde & Schwarz	SMC100A	105811	2022/9/26	2023/9/25
Power amplifier	Rohde & Schwarz	BBA150-A125B125	102340	N/A	N/A
Coupling and Decoupling Network	TESEQ	CDN M016	45073	2022/3/18	2023/3/17
Coupling and Decoupling Network	TESEQ	CDN T2-10	45003	2022/3/18	2023/3/17
Coupling and Decoupling Network	TESEQ	CDN T4-10	44939	2022/3/18	2023/3/17
Coupling and Decoupling Network	TESEQ	CDN T8-10	49203	2022/12/12	2023/12/11
Coupling and Decoupling Network	TESEQ	CDN ST08A	57417	2022/6/27	2023/6/26
EM Injection Clamp	TESEQ	CAL 801A & KEMZ 801A	75454.1, 75454.2 & 45181	2022/4/13	2023/4/12
Power - Sensor	Rohde & Schwarz	NRP-Z91	103730	2022/12/9	2023/12/8
Power - Sensor	Rohde & Schwarz	NRP-Z91	103731	2022/12/9	2023/12/8
Pressure-field 1/2" Microphone	Bruel&Kjaer	Type 4192	3069928	2022/8/26	2023/8/25
Audio Analyzer	Rohde & Schwarz	UPV	104227	2022/11/28	2023/11/27
Microphone Adaptation Amplifier	Bruel&Kjaer	Type 5935	3070463	2022/8/1	2023/7/31
Measurement Software	Rohde & Schwarz	EMC32, VER.10.20.01	N/A	N/A	N/A
Power frequency magnetic field immunity					
Ultra Compact Simulator	EM TEST	UCS 500N7	P1623180275	2022/11/24	2023/11/23
Current Transformer	EM TEST	MC 2630	P1644186773	2022/8/22	2023/8/21
Magnetic Field Test Antena	EM TEST	MS 100N	P1627181324	2022/8/22	2023/8/21
Current Transformer	EM TEST	MFT100	P2025241594	2022/8/22	2023/8/21
Motorized Variac	EM TEST	MV 2616 (varic NX1-260-16)	P1643186426	2022/11/25	2023/11/24

Instrument					
Equipment	Manufacturer	Model No.	Serial No.	Last Cal.	Expired date
Voltage dips and interruptions					
Ultra Compact Simulator	EM TEST	UCS 500N7	P1623180275	2022/11/24	2023/11/23
Motorized Variac	EM TEST	MV 2616 (varic NX1-260-16)	P1643186426	2022/11/25	2023/11/24
Measurement Software	TESEQ	IEC.control, VER.7.1.5	N/A	N/A	N/A

6. EMISSION TEST

6.1. Conducted Disturbance Measurement

6.1.1. Limits of conducted disturbance voltage and common mode disturbance.

AC mains port:

FREQUENCY (MHz)	<input type="checkbox"/> Class A (dB μ V)		<input checked="" type="checkbox"/> Class B (dB μ V)	
	Quasi-peak	Average	Quasi-peak	Average
0.15 -0.5	79.00	66.00	66 - 56 *	56 - 46*
0.50 -5.0	73.00	60.00	56.00	46.00
5.0 -30.0	73.00	60.00	60.00	50.00

Telecommunications/network port:

FREQUENCY (MHz)	<input type="checkbox"/> Class A			
	Voltage limit (dB μ V)		Current limit(dB μ A)	
	Quasi-peak	Average	Quasi-peak	Average
0.15 -0.5	97 - 87 *	84 - 74*	53 - 43 *	40 - 30*
0.50 -30.0	87.00	74.00	43.00	30.00
FREQUENCY (MHz)	<input type="checkbox"/> Class B			
	Voltage limit (dB μ V)		Current limit(dB μ A)	
	Quasi-peak	Average	Quasi-peak	Average
0.15 -0.5	84 - 74 *	74 - 64*	40 - 30 *	30 - 20*
0.50 -30.0	74.00	64.00	30.00	20.00

Note:

- (1) The tighter limit applies at the band edges.
- (2) The limit of " * " marked band means the limitation decreases linearly with the logarithm of the frequency in the range.
- (3) The test result calculated as following:
 Measurement Value = Reading Level + Correct Factor
 Correct Factor = Insertion Loss + Cable Loss + Attenuator Factor(if use)
 Margin Level = Measurement Value - Limit Value


The following table is the setting of the receiver

Receiver Parameters	Setting
Attenuation	10 dB
Start Frequency	0.15 MHz
Stop Frequency	30 MHz
IF Bandwidth	9 kHz

6.1.2. Test Procedure

- The EUT was placed 0.8 meters from the horizontal ground plane with EUT being connected to the power mains through a line impedance stabilization network (LISN). All other support equipments powered from additional LISN(s). The LISN provide 50 Ohm/ 50uH of coupling impedance for the measuring instrument.
- Interconnecting cables that hang closer than 40 cm to the ground plane shall be folded back and forth in the center forming a bundle 30 to 40 cm long.
- I/O cables that are not connected to a peripheral shall be bundled in the center. The end of the cable may be terminated, if required, using the correct terminating impedance. The overall length shall at least 1 m.
- LISN at least 80 cm from nearest part of EUT chassis.
- For the actual test configuration, please refer to the related Item:EUT Test Photos.

6.1.3. Test Setup




The 0.8 m distance specified between EUT/AE/PSU and AMN/AAN, is applicable only to the EUT being measured. If the device is AE then it shall be ≥ 0.8 m.

For the actual test configuration, please refer to Appendix I: Photographs of the Test Configuration.

6.1.4. Test Result

Mode 1 ; LISN (150k-30MHz)


Test Mode:	Mode 1	Temperature:	24°C
Test Voltage:	AC230V/50Hz	Humidity:	62%RH
Tested By:	Rupert Huang	Test Date:	Dec. 16, 2022



No.	Frequency (MHz)	Reading (dBuV)	Correct (dB)	Result (dBuV)	Limit (dBuV)	Margin (dB)	Remark
1	0.5047	25.75	19.54	45.29	56.00	-10.71	QP
2	0.5047	13.68	19.54	33.22	46.00	-12.78	AVG
3	1.0128	27.64	19.56	47.20	56.00	-8.80	QP
4	1.0128	11.46	19.56	31.02	46.00	-14.98	AVG
5	1.7628	25.97	19.58	45.55	56.00	-10.45	QP
6	1.7628	7.95	19.58	27.53	46.00	-18.47	AVG
7	2.3617	24.59	19.59	44.18	56.00	-11.82	QP
8	2.3617	7.21	19.59	26.80	46.00	-19.20	AVG
9	4.0782	24.78	19.63	44.41	56.00	-11.59	QP
10	4.0782	7.14	19.63	26.77	46.00	-19.23	AVG
11	4.6741	25.98	19.64	45.62	56.00	-10.38	QP
12	4.6741	7.57	19.64	27.21	46.00	-18.79	AVG

Remark:
 Result = Reading +Correct.
 Correct = Insertion Loss + Cable Loss + Attenuator Factor.
 Margin = Result - Limit.

Test Mode:	Mode 1	Temperature:	24°C
Test Voltage:	AC230V/50Hz	Humidity:	62%RH
Tested By:	Rupert Huang	Test Date:	Dec. 16, 2022



No.	Frequency (MHz)	Reading (dBuV)	Correct (dB)	Result (dBuV)	Limit (dBuV)	Margin (dB)	Remark
1	0.8443	28.97	19.56	48.53	56.00	-7.47	QP
2	0.8443	16.70	19.56	36.26	46.00	-9.74	AVG
3	0.9300	28.88	19.56	48.44	56.00	-7.56	QP
4	0.9300	15.80	19.56	35.36	46.00	-10.64	AVG
5	1.0117	29.14	19.56	48.70	56.00	-7.30	QP
6	1.0117	15.96	19.56	35.52	46.00	-10.48	AVG
7	1.0967	28.30	19.56	47.86	56.00	-8.14	QP
8	1.0967	15.34	19.56	34.90	46.00	-11.10	AVG
9	1.6825	28.08	19.58	47.66	56.00	-8.34	QP
10	1.6825	12.46	19.58	32.04	46.00	-13.96	AVG
11	2.3704	26.65	19.59	46.24	56.00	-9.76	QP
12	2.3704	10.54	19.59	30.13	46.00	-15.87	AVG

Remark:

Result = Reading + Correct.

Correct = Insertion Loss + Cable Loss + Attenuator Factor.

Margin = Result - Limit.

6.2. Radiated Disturbance Measurement(below 1GHz)

6.2.1. Limits of radiated disturbance measurement

FREQUENCY (MHz)	<input type="checkbox"/> Class A		<input checked="" type="checkbox"/> Class B	
	<input type="checkbox"/> At 10m	<input type="checkbox"/> At 3m	<input type="checkbox"/> At 10m	<input checked="" type="checkbox"/> At 3m
	dB μ V/m	dB μ V/m	dB μ V/m	dB μ V/m
30 – 230	40	50	30	40
230 – 1000	47	57	37	47


NOTE:

- (1) The limit for radiated test was performed according to EN55032, CISPR 32.
- (2) The tighter limit applies at the band edges.
- (3) The test result calculated as following:
 Measurement Value = Reading Level + Correct Factor,
 Correct Factor = Antenna Factor + Cable Loss - Amplifier Gain(if use),
 Margin Level = Measurement Value - Limit Value.


6.2.2. Test Procedure

- a. The measuring distance of at 3m shall be used for measurements at frequency from 30 to 1000MHz.
- b. The EUT was placed on the top of a rotating table 0.8 meters above the ground at a 3 meter chamber. The table was rotated 360 degrees to determine the position of the highest radiation.
- c. The height of the equipment shall be set at 0.8 m; the height of the test antenna shall vary between 1 m to 4 m. Both horizontal and vertical polarizations of the antenna are set to make the measurement.
- d. The initial step in collecting radiated emission data is a spectrum analyzer peak detector mode pre-scanning the measurement frequency range. Significant peaks are then marked and then Quasi Peak detector mode re-measured.
- e. If the Peak Mode measured value compliance with and lower than Quasi Peak Mode Limit, the EUT shall be deemed to meet QP Limits and then no additional QP Mode measurement performed.
- f. For the actual test configuration, please refer to the related Item:EUT Test Photos.

6.2.3. Test Setup




For the actual test configuration, please refer to Appendix I: Photographs of the Test Configuration.



6.2.4. Test Result

Mode 1 ; 30M-1GHz

Test Mode:	Mode 1	Temperature:	21°C
Test Voltage:	AC 230V/50Hz	Humidity:	64%RH
Tested By:	Duncan Wang	Test Date:	Dec. 16, 2022



No.	Frequency (MHz)	Reading (dBuV/m)	Correct (dB/m)	Result (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Remark
1	34.5590	37.18	-13.58	23.60	40.00	-16.40	PK
2	41.9310	37.07	-12.70	24.37	40.00	-15.63	PK
3	67.4097	36.42	-14.04	22.38	40.00	-17.62	PK
4	166.9963	35.24	-12.37	22.87	40.00	-17.13	PK
5	192.3133	45.53	-14.74	30.79	40.00	-9.21	PK
6	521.0787	35.11	-5.49	29.62	47.00	-17.38	PK


Remark:

Result = Reading + Correct.

Correct Factor = Antenna Factor + Cable Loss - Amplifier Gain.

Margin = Result - Limit.

Test Mode:	Mode 1	Temperature:	21°C
Test Voltage:	AC 230V/50Hz	Humidity:	64%RH
Tested By:	Duncan Wang	Test Date:	Dec. 16, 2022



No.	Frequency (MHz)	Reading (dBuV/m)	Correct (dB/m)	Result (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Remark
1	35.2703	42.14	-13.54	28.60	40.00	-11.40	PK
2	47.1690	48.25	-12.27	35.98	40.00	-4.02	PK
3	54.1853	43.13	-12.21	30.92	40.00	-9.08	PK
4	67.4097	43.08	-14.04	29.04	40.00	-10.96	PK
5	110.2837	46.20	-15.64	30.56	40.00	-9.44	PK
6	192.4427	45.23	-14.75	30.48	40.00	-9.52	PK

Remark:

Result = Reading +Correct.

Correct Factor = Antenna Factor + Cable Loss - Amplifier Gain.

Margin = Result - Limit.

6.3. Harmonic Current Disturbance Measurement


6.3.1. Limits of Harmonic Current

EN IEC 61000-3-2						
Equipment Category	Harmonic Order n	Max. Permissible Harmonic Current A	Equipment Category	Harmonic Order n	Max. Permissible Harmonic Current A mA/w	
Class A	Odd Harmonics		Class D	Odd Harmonics only		
	3	2.30		3	2.30	3.4
	5	1.14		5	1.14	1.9
	7	0.77		7	0.77	1.0
	9	0.40		9	0.40	0.5
	11	0.33		11	0.33	0.35
	13	0.21		13	0.21	0.296
	15 ≤ n ≤ 39	0.15 x 15/n		15 ≤ n ≤ 39	0.15 x 15/n	3.85/n
	Even Harmonics					
	2	1.08				
	4	0.43				
	6	0.30				
	8 ≤ n ≤ 40	0.23 x 8/n				

6.3.2. Test Procedure

- a. The EUT was placed on the top of a wooden table 0.8 meters above the ground and operated to produce under normal conditions
- b. Tests was performed according to the Test the measured values of the harmonics components of the input current in Clause 7 of EN IEC 61000-3-2 depend on which standard adopted for compliance measurement.

6.3.3. Test Setup




For the actual test configuration, please refer to Appendix I: Photographs of the Test Configuration.

6.3.4. Test Condition

Test Mode:	Mode 1	Temperature:	21 °C
Test Voltage:	230V/50Hz	Humidity:	64 %RH
Tested By:	Duncan Wang	Test Date:	Dec. 9, 2022

6.3.5. Test Result

Harmonics – Class-A per Ed. 5.0 (Run time) incl. inter-harmonics



Test result: Pass Worst harmonics H15-8.7% of 150% limit, H15-12.9% of 100% limit

Test Result: Pass Source qualification: Normal

THC(A):0.115	I-THD(%):190.6	POHC(A):0.024	POHC Limit(A):0.251
--------------	----------------	---------------	---------------------

Highest parameter values during test:			
V_RMS (Volts):	229.89	Frequency(Hz):	50.00
I_Peak (Amps):	0.589	I_RMS (Amps):	0.130
I_Fund (Amps):	0.060	Crest Factor:	4.534
Power (Watts):	13.6	Power Factor:	0.457

Harm#	Harms(avg)	100%Limit	%of Limit	Harms(max)	150%Limit	%of Limit	Status
2	0.001	1.080	N/A	0.001	1.620	N/A	Pass
3	0.058	2.300	2.5	0.058	3.450	1.7	Pass
4	0.001	0.430	N/A	0.001	0.645	N/A	Pass
5	0.054	1.140	4.7	0.054	1.710	3.1	Pass
6	0.000	0.300	N/A	0.000	0.450	N/A	Pass
7	0.048	0.770	6.2	0.048	1.155	4.1	Pass
8	0.000	0.230	N/A	0.000	0.345	N/A	Pass
9	0.041	0.400	10.2	0.041	0.600	6.8	Pass
10	0.000	0.184	N/A	0.000	0.276	N/A	Pass
11	0.033	0.330	10.1	0.033	0.495	6.8	Pass
12	0.000	0.153	N/A	0.000	0.230	N/A	Pass
13	0.026	0.210	12.3	0.026	0.315	8.3	Pass
14	0.000	0.131	N/A	0.000	0.197	N/A	Pass
15	0.019	0.150	12.9	0.020	0.225	8.7	Pass
16	0.000	0.115	N/A	0.000	0.173	N/A	Pass
17	0.014	0.132	10.8	0.014	0.198	7.3	Pass
18	0.000	0.102	N/A	0.000	0.153	N/A	Pass
19	0.011	0.118	9.5	0.011	0.178	6.4	Pass
20	0.000	0.092	N/A	0.000	0.138	N/A	Pass
21	0.010	0.107	9.6	0.010	0.161	6.4	Pass
22	0.000	0.084	N/A	0.000	0.125	N/A	Pass
23	0.010	0.098	10.4	0.010	0.147	7.0	Pass
24	0.000	0.077	N/A	0.000	0.115	N/A	Pass
25	0.010	0.090	11.0	0.010	0.135	7.4	Pass
26	0.000	0.071	N/A	0.000	0.107	N/A	Pass
27	0.009	0.083	11.1	0.009	0.125	7.5	Pass
28	0.000	0.066	N/A	0.000	0.099	N/A	Pass
29	0.008	0.078	10.5	0.008	0.116	7.1	Pass
30	0.000	0.061	N/A	0.000	0.092	N/A	Pass
31	0.007	0.073	9.3	0.007	0.109	6.3	Pass
32	0.000	0.058	N/A	0.000	0.086	N/A	Pass
33	0.006	0.068	8.1	0.006	0.102	5.5	Pass
34	0.000	0.054	N/A	0.000	0.081	N/A	Pass
35	0.005	0.064	N/A	0.005	0.096	N/A	Pass
36	0.000	0.051	N/A	0.000	0.077	N/A	Pass
37	0.004	0.061	N/A	0.004	0.091	N/A	Pass
38	0.000	0.048	N/A	0.000	0.073	N/A	Pass
39	0.004	0.058	N/A	0.004	0.087	N/A	Pass
40	0.000	0.046	N/A	0.000	0.069	N/A	Pass

Test Result: Pass Source qualification: Normal

THC(A):0.115	I-THD(%):190.6	POHC(A):0.024	POHC Limit(A):0.251
--------------	----------------	---------------	---------------------

Highest parameter values during test:			
V_RMS (Volts):	229.89	Frequency(Hz):	50.00
I_Peak (Amps):	0.589	I_RMS (Amps):	0.130
I_Fund (Amps):	0.060	Crest Factor:	4.534
Power (Watts):	13.6	Power Factor:	0.457

Harm#	Harms(avg)	100%Limit	%of Limit	Harms(max)	150%Limit	%of Limit	Status
2	0.001	1.080	N/A	0.001	1.620	N/A	Pass
3	0.058	2.300	2.5	0.058	3.450	1.7	Pass
4	0.001	0.430	N/A	0.001	0.645	N/A	Pass
5	0.054	1.140	4.7	0.054	1.710	3.1	Pass
6	0.000	0.300	N/A	0.000	0.450	N/A	Pass
7	0.048	0.770	6.2	0.048	1.155	4.1	Pass
8	0.000	0.230	N/A	0.000	0.345	N/A	Pass
9	0.041	0.400	10.2	0.041	0.600	6.8	Pass
10	0.000	0.184	N/A	0.000	0.276	N/A	Pass
11	0.033	0.330	10.1	0.033	0.495	6.8	Pass
12	0.000	0.153	N/A	0.000	0.230	N/A	Pass
13	0.026	0.210	12.3	0.026	0.315	8.3	Pass
14	0.000	0.131	N/A	0.000	0.197	N/A	Pass
15	0.019	0.150	12.9	0.020	0.225	8.7	Pass
16	0.000	0.115	N/A	0.000	0.173	N/A	Pass
17	0.014	0.132	10.8	0.014	0.198	7.3	Pass
18	0.000	0.102	N/A	0.000	0.153	N/A	Pass
19	0.011	0.118	9.5	0.011	0.178	6.4	Pass
20	0.000	0.092	N/A	0.000	0.138	N/A	Pass
21	0.010	0.107	9.6	0.010	0.161	6.4	Pass
22	0.000	0.084	N/A	0.000	0.125	N/A	Pass
23	0.010	0.098	10.4	0.010	0.147	7.0	Pass
24	0.000	0.077	N/A	0.000	0.115	N/A	Pass
25	0.010	0.090	11.0	0.010	0.135	7.4	Pass
26	0.000	0.071	N/A	0.000	0.107	N/A	Pass
27	0.009	0.083	11.1	0.009	0.125	7.5	Pass
28	0.000	0.066	N/A	0.000	0.099	N/A	Pass
29	0.008	0.078	10.5	0.008	0.116	7.1	Pass
30	0.000	0.061	N/A	0.000	0.092	N/A	Pass
31	0.007	0.073	9.3	0.007	0.109	6.3	Pass
32	0.000	0.058	N/A	0.000	0.086	N/A	Pass
33	0.006	0.068	8.1	0.006	0.102	5.5	Pass
34	0.000	0.054	N/A	0.000	0.081	N/A	Pass
35	0.005	0.064	N/A	0.005	0.096	N/A	Pass
36	0.000	0.051	N/A	0.000	0.077	N/A	Pass
37	0.004	0.061	N/A	0.004	0.091	N/A	Pass
38	0.000	0.048	N/A	0.000	0.073	N/A	Pass
39	0.004	0.058	N/A	0.004	0.087	N/A	Pass
40	0.000	0.046	N/A	0.000	0.069	N/A	Pass

6.4. Voltage Fluctuation and Flicker Measurement

6.4.1. Limits of Voltage Fluctuation and Flicker

Test items	Limits	Descriptions
P_{st}	$\leq 1.0, T_p=10\text{min}$	short-term flicker indicator
P_{lt}	$\leq 0.65, T_p=2\text{h}$	long-term flicker indicator
d_c	$\leq 3.3\%$	relative steady-state voltage change
d_{max}	$\leq 4\%$ (or 6% ^{Note(1)} , 7% ^{Note(2)})	maximum relative voltage change:
$d_{(t)}$	$\leq 3.3\%$, more than 500ms	relative voltage change characteristic

Note:

(1)6 % for equipment which is:

- a. switched manually, or
- b. switched automatically more frequently than twice per day, and also has either a delayed restart (the delay being not less than a few tens of seconds), or manual restart, after a power supply interruption.


(2)7 % for equipment which is

- a. attended whilst in use (for example: hair dryers, vacuum cleaners, kitchen equipment such as mixers, garden equipment such as lawn mowers, portable tools such as electric drills), or
- b. switched on automatically, or is intended to be switched on manually, no more than twice per day, and also has either a delayed restart (the delay being not less than a few tens of seconds) or manual restart, after a power supply interruption.

6.4.2. Test Procedure

- a. The EUT was placed on the top of a wooden table 0.8 meters above the ground and operated to produce the most unfavorable sequence of voltage changes under normal conditions
- b. During the flicker measurement, the measure time shall include that part of whole operation changes according to EN 61000-3-3 Annex A for each product type has different requirement.
- c. Tests was performed according to the Test Conditions/Assessment of Voltage Fluctuations specified in Clause 6.0/4.0 of EN 61000-3-3 depend on which standard adopted for compliance measurement.
- d. All types of harmonic current and/or voltage fluctuation in this report are assessed by direct measurement using flicker-meter.

6.4.3. Test Setup



For the actual test configuration, please refer to Appendix I: Photographs of the Test Configuration.

6.4.4. Test Condition

Test Mode:	Mode 1	Temperature:	21 °C
Test Voltage:	230V/50Hz	Humidity:	64 %RH
Tested By:	Duncan Wang	Test Date:	Dec. 9, 2022


6.4.5. Test Result

Test Result: Pass


Status: Test Completed

Pst and limit line

European Limits



Plt and limit line



Parameter values recorded during the test:

Vrms at the end of test (Volt):	229.85		
Highest dt (%):		Test limit (%):	
T-max (mS):	0	Test limit (mS):	500.0 Pass
Highest dc (%):	0.00	Test limit (%):	3.30 Pass
Highest dmax (%):	0.00	Test limit (%):	4.00 Pass
Highest Pst (10 min. period):	0.064	Test limit:	1.000 Pass
Highest Plt (2 hr. period):	0.028	Test limit:	0.650 Pass

7. IMMUNITY TEST

7.1. Performance Criteria

According to EN 55035 standard, the general performance criteria as following:

Criteria A	The equipment shall continue to operate as intended without operator intervention. No degradation of performance, loss of function or change of operating state is allowed below a performance level specified by the manufacturer when the equipment is used as intended. The performance level may be replaced by a permissible loss of performance. If the minimum performance level or the permissible performance loss is not specified by the manufacturer, then either of these may be derived from the product description and documentation, and by what the user may reasonably expect from the equipment if used as intended.
Criteria B	During the application of the disturbance, degradation of performance is allowed. However, no unintended change of actual operating state or stored data is allowed to persist after the test. After the test, the equipment shall continue to operate as intended without operator intervention; no degradation of performance or loss of function is allowed, below a performance level specified by the manufacturer, when the equipment is used as intended. The performance level may be replaced by a permissible loss of performance. If the minimum performance level (or the permissible performance loss), or recovery time, is not specified by the manufacturer, then either of these may be derived from the product description and documentation, and by what the user may reasonably expect from the equipment if used as intended.
Criteria C	Loss of function is allowed, provided the function is self-recoverable, or can be restored by the operation of the controls by the user in accordance with the manufacturer's instructions. A reboot or re-start operation is allowed. Information stored in non-volatile memory, or protected by a battery backup, shall not be lost.

7.2. Electrostatic Discharge Immunity Test

7.2.1. Test Specification

Standard:	EN 55035 (refer to IEC/EN 61000-4-2)
Discharge Impedance:	330(1±10%)Ω / 150(1±10%)pF
Discharge Voltage:	Air Discharge: ±2kV/±4kV/±8kV (Direct)
Polarity:	Contact Discharge: ±2kV/±4kV (Direct/Indirect) Positive and Negative
Discharge Mode of Operation:	Single discharges
Discharge Period:	1 second minimum

7.2.2. Test Procedure

The test generator necessary to perform direct and indirect application of discharges to the EUT in the following manner:

- a. Contact discharge was applied to conductive surfaces and coupling planes of the EUT. During the test, it was performed with single discharges. For the single discharge time between successive single discharges was at least 1 second. On each pre-selected point at least 10 single discharges (at each polarity) shall be applied. Test shall be performed at a maximum repetition rate of one discharge per second.

Vertical Coupling Plane (VCP):

The coupling plane, of dimensions 0.5m x 0.5m, is placed parallel to, and positioned at a distance 0.1m from, the EUT, with the Discharge Electrode touching the coupling plane. The four faces of the EUT will be performed with electrostatic discharge.

Horizontal Coupling Plane (HCP):

The coupling plane is placed under to the EUT. The generator shall be positioned vertically at a distance of 0.1m from the EUT, with the Discharge Electrode touching the coupling plane. The four faces of the EUT will be performed with electrostatic discharge.


- b. Air discharges at insulation surfaces of the EUT.

It was at least 10 single discharges with positive and negative at the same selected point.

- c. For the actual test configuration, please refer to the related Item :EUT Test Photos.

7.2.3. Test Setup


(Table Top)



A distance of 0,8 m minimum shall be provided between the EUT and the walls of the laboratory and any other metallic structure.

For the actual test configuration, please refer to Appendix I: Photographs of the Test Configuration.

(Floor Standing)



7.2.4. Test Result

Test Mode:	Mode 1	Temperature:	22°C
Test Voltage:	AC 230V/50Hz	Humidity:	45%RH
Discharge of times:	Air: 10 times Contact: 10 times	ATM pressure	1020 hpa
Tested By:	Duncan Wang	Test Date:	Dec. 12, 2022



Mode	Air Discharge								Contact Discharge							
	2kV		4kV		8kV		-kV		2kV		4kV		-kV		-kV	
Location	+	-	+	-	+	-	+	-	+	-	+	-	+	-	+	-
1~6	-	-	-	-	-	-	-	-	A	A	A	A	-	-	-	-
7~12	A	A	A	A	A	A	-	-	-	-	-	-	-	-	-	-
Criterion	B								B							
Results	A								A							
Judgment	PASS															
Note	There was no abnormal situation during the test compared with initial operation.															



Mode	HCP Discharge								VCP Discharge							
	2kV		4kV		-kV		-kV		2kV		4kV		-kV		-kV	
Location	+	-	+	-	+	-	+	-	+	-	+	-	+	-	+	-
front	A	A	A	A	-	-	-	-	A	A	A	A	-	-	-	-
rear	A	A	A	A	-	-	-	-	A	A	A	A	-	-	-	-
left	A	A	A	A	-	-	-	-	A	A	A	A	-	-	-	-
right	A	A	A	A	-	-	-	-	A	A	A	A	-	-	-	-
Criterion	B				-				B				-			
Results	A				-				A				-			
Judgment	PASS															
Note	There was no abnormal situation during the test compared with initial operation.															

Customer request:

Mode	Air Discharge								Contact Discharge							
	2kV		4kV		8kV		15kV		2kV		4kV		8kV		-kV	
Location	+	-	+	-	+	-	+	-	+	-	+	-	+	-	+	-
1~6	-	-	-	-	-	-	-	-	-	-	-	-	A	A	-	-
7~12	-	-	-	-	-	-	A	A	-	-	-	-	-	-	-	-
Criterion	A								A							
Results	A								A							
Judgment	PASS															
Note	There was no abnormal situation during the test compared with initial operation.															

Mode	HCP Discharge								VCP Discharge							
	2kV		4kV		8kV		-kV		2kV		4kV		8kV		-kV	
Location	+	-	+	-	+	-	+	-	+	-	+	-	+	-	+	-
front	-	-	-	-	A	A	-	-	-	-	-	-	A	A	-	-
rear	-	-	-	-	A	A	-	-	-	-	-	-	A	A	-	-
left	-	-	-	-	A	A	-	-	-	-	-	-	A	A	-	-
right	-	-	-	-	A	A	-	-	-	-	-	-	A	A	-	-
Criterion	-				A				-				A			
Results	-				A				-				A			
Judgment	PASS															
Note	There was no abnormal situation during the test compared with initial operation.															





7.3. Radio Frequency Electromagnetic Field Immunity Test

7.3.1. Test Specification


Standard:	EN 55035 (refer to IEC/EN IEC 61000-4-3)
Frequency Range:	80 MHz to 1000MHz
Spot Frequency:	1800, 2600, 3500, 5000 ($\pm 1\%$)
Field Strength:	3V/m (unmodulated)
Immunity level to common wireless communication:	See Table I.1 for test frequency and level
Modulation:	80%, AM(1kHz)
Frequency Step:	1%
Polarity of Antenna	Vertical and Horizontal
Test Distance:	3 meters
Antenna Height:	1.55 meters
Dwell Time:	3 s

7.3.2. Test Procedure

The test procedure was in accordance with IEC/EN IEC 61000-4-3.

- a. The testing was performed in a fully anechoic chamber. The transmit antenna was located at a distance of 3 meters from the EUT.
- b. The frequency range is swept from 80 MHz to 1000MHz with the signal 80% amplitude modulated with a 1kHz sine wave. The rate of sweep did not exceed 1.5×10^{-3} decade/s. Where the frequency range is swept incrementally, the step size was 1% of fundamental.
- c. The dwell time at each frequency shall be not less than the time necessary for the EUT to be able to respond.
- d. The field strength level from 80 MHz to 1000MHz was 3V/m.
- e. A special spot frequency test point are 1800, 2600, 3500 and 5000MHz ($\pm 1\%$)
- f. Immunity level to common wireless communication test distance is base on client requirement.
- g. The test was performed with the EUT exposed to both vertically and horizontally polarized fields on each of the four sides.

7.3.3. Test Setup



For the actual test configuration, please refer to Appendix I: Photographs of the Test Configuration.

7.3.4. Test Result

Test Mode:	Mode 1	Temperature:	22°C
Test Voltage:	AC 230V/ 50Hz	Humidity:	68%RH
Tested By:	Duncan Wang	Test Date:	Dec. 12, 2022

Freq. Range (MHz)	Position (Face)	Polarity (H or V)	Field Strength (V/m)	Criterion	Results	Judgement
80-1000	Front / Left / Right / Rear	H / V	3V/m	A	A	PASS
1800(±1%)	Front / Left / Right / Rear	H / V	3V/m	A	A	PASS
2600(±1%)	Front / Left / Right / Rear	H / V	3V/m	A	A	PASS
3500(±1%)	Front / Left / Right / Rear	H / V	3V/m	A	A	PASS
5000(±1%)	Front / Left / Right / Rear	H / V	3V/m	A	A	PASS
Note	There was no abnormal situation during the test compared with initial operation.					

Immunity Level to common wireless communication						
Freq. Range (MHz)	Position (Face)	Polarity (H or V)	Field Strength (V/m)	Criterion	Results	Judgement
800(±1%)	Front / Left / Right / Rear	H / V	3V/m	A	A	PASS
900(±1%)	Front / Left / Right / Rear	H / V	3V/m	A	A	PASS
1800(±1%)	Front / Left / Right / Rear	H / V	3V/m	A	A	PASS
2600(±1%)	Front / Left / Right / Rear	H / V	3V/m	A	A	PASS
3500(±1%)	Front / Left / Right / Rear	H / V	3V/m	A	A	PASS
5000(±1%)	Front / Left / Right / Rear	H / V	3V/m	A	A	PASS
Note	There was no abnormal situation during the test compared with initial operation.					

Customer request:

Freq. Range (MHz)	Position (Face)	Polarity (H or V)	Field Strength (V/m)	Criterion	Results	Judgement
80-1000	Front / Left / Right / Rear	H / V	10V/m	A	A	PASS
1800(±1%)	Front / Left / Right / Rear	H / V	10V/m	A	A	PASS
2600(±1%)	Front / Left / Right / Rear	H / V	10V/m	A	A	PASS
3500(±1%)	Front / Left / Right / Rear	H / V	10V/m	A	A	PASS
5000(±1%)	Front / Left / Right / Rear	H / V	10V/m	A	A	PASS
Note	There was no abnormal situation during the test compared with initial operation.					

Immunity Level to common wireless communication						
Freq. Range (MHz)	Position (Face)	Polarity (H or V)	Field Strength (V/m)	Criterion	Results	Judgement
800(±1%)	Front / Left / Right / Rear	H / V	10V/m	A	A	PASS
900(±1%)	Front / Left / Right / Rear	H / V	10V/m	A	A	PASS
1800(±1%)	Front / Left / Right / Rear	H / V	10V/m	A	A	PASS
2600(±1%)	Front / Left / Right / Rear	H / V	10V/m	A	A	PASS
3500(±1%)	Front / Left / Right / Rear	H / V	10V/m	A	A	PASS
5000(±1%)	Front / Left / Right / Rear	H / V	10V/m	A	A	PASS
Note	There was no abnormal situation during the test compared with initial operation.					

7.4. Electrical Fast Transient/Burst Immunity Test


7.4.1. Test Specification

Standard:	EN 55035 (refer to IEC/EN 61000-4-4)
Test Voltage:	0.5,1 kV(Peak)
Polarity:	Positive and Negative
Impulse Frequency:	5 kHz
Impulse wave shape:	5/50 Tr/Th ns
Burst Duration:	15ms
Burst Period:	300ms
Test Duration:	1 Minute

7.4.2. Test Procedure

- a. The EUT was tested with 1000 volt discharges to the AC power input leads, 500 volt discharges to the signal/control ports.
- b. Both positive and negative polarity discharges were applied.
- c. Table-top equipment and equipment normally mounted on ceilings or walls as well as built-in equipment shall be tested with the EUT located ($0,1 \pm 0,01$) m above the ground reference plane.
- d. The EUT and the auxiliary equipment were placed on a table of 0.8 m heights above a metal ground reference plane. The size of ground plane is greater than 0.8m×1m and project beyond the EUT by at least 0.1m on all sides. The ground plane is connected to the protective earth. The minimum distance between the EUT and all other conductive structures (including the generator, AE and the walls of a shielded room), except the ground reference plane, shall be more than 0,5 m.
- e. The duration time of each test sequential was 1 minute.
- f. The transient/burst waveform was in accordance with IEC/EN 61000-4-4, 5/50ns.

7.4.3. Test Setup



- (A) location for supply line coupling
- (B) location for signal lines coupling

For the actual test configuration, please refer to Appendix I: Photographs of the Test Configuration.

7.4.4. Test Result

Test Mode:	Mode 1	Temperature:	22°C
Test Voltage:	AC 230V/ 50Hz	Humidity:	65%RH
Tested By:	Duncan Wang	Test Date:	Dec. 09, 2022

Repetition Frequency		5kHz						Criterion	Results	Judgment
Test Port		Test Levels (kV)								
		+0.5	-0.5	+1.0	-1.0	-	-			
AC Power Port	L	-	-	A	A	-	-	B	A	PASS
	N	-	-	A	A	-	-			
	L + N	-	-	A	A	-	-			
Note		There was no abnormal situation during the test compared with initial operation.								

Customer request:

Repetition Frequency		5kHz						Criterion	Results	Judgment
Test Port		Test Levels (kV)								
		+0.5	-0.5	+1.0	-1.0	+2.0	-2.0			
AC Power Port	L	-	-	-	-	A	A	B	A	PASS
	N	-	-	-	-	A	A			
	L + N	-	-	-	-	A	A			
Note		There was no abnormal situation during the test compared with initial operation.								

7.5. Surge Immunity Test

7.5.1. Test Specification

Standard:	EN 55035 (refer to IEC/EN 61000-4-5)
Waveform:	1.2/50 (8/20) Tr/Th μ s , 10/700 Tr/Th μ s
Test Voltage:	0.5,1 kV(Line to Line) 0.5,1,2 kV(Line to Earth)
Polarity:	Positive and Negative
Phase Angle:	90°/270°
Repetition Rate:	1 per minute
Times:	5 times each polarity

7.5.2. Test Procedure

- a. The EUT and the auxiliary equipment were placed on a table of 0.8m heights above a metal ground reference plane. The size of ground plane is greater than 1m \times 1m and project beyond the EUT by at least 0.1m on all sides. The ground plane is connected to the protective earth. The length of power cord between the coupling device and the EUT shall not exceed 2 meters (provided by the manufacturer).
- b. The EUT was connected to the power mains through a coupling device that directly couples the surge interference signal. The surge noise was applied synchronized to the voltage phase at the zero crossing and the peak value of the AC voltage wave (positive and negative).
- c. The surges were applied line to line and line(s) to earth. When testing line to earth the test voltage was applied successively between each of the lines and earth. Steps up to the test level specified increased the test voltage. All lower levels including the selected test level were tested. The polarity of each surge level included positive and negative test pulses.
- d. If EUT was included telecom port and connected to outdoor directly, test shall be applied to line to earth test using 10/700 surge wave form. If the wave form affects the functioning of high speed data port, the test shall be carried out using 1.2/50 wave form do the test.

7.5.3. Test Result

Test Mode:	Mode 1	Temperature:	22°C
Test Voltage:	AC 230V/ 50Hz	Humidity:	65%RH
Tested By:	Duncan Wang	Test Date:	Dec. 09, 2022

Wave Form EUT Ports Tested	1.2/50(8/20)Ti/Th us						Criterion	Results	Judgement
	Polarity	Phase	Voltage						
			0.5kV	1kV	2kV	4kV			
L - N	+	90°	A	A	-	-	B	A	PASS
	-	270°	A	A	-	-			
Note	There was no abnormal situation during the test compared with initial operation.								

7.6. Immunity to Conducted Disturbances Induced by RF Fields


7.6.1. Test Specification

Standard:	EN 55035 (refer to IEC/EN 61000-4-6)
Frequency Range:	0.15-10; 10-30; 30-80MHz
Field Strength:	3V; 3 to 1V; 1V (unmodulated, r.m.s.)
Modulation:	80% AM (1 kHz)
Frequency Step:	1%
Dwell Time:	3s

7.6.2. Test Procedure

- a. The EUT shall be tested within its intended operating and climatic conditions.
- b. The test shall be performed with the test generator connected to each of the coupling and decoupling devices in turn, while the other non-excited RF input ports of the coupling devices are terminated by a 50-ohm load resistor.
- c. The frequency range is swept from 150 kHz to 80 MHz, using the signal level established during the setting process and with a disturbance signal of 80% amplitude. The signal is modulated with a 1 kHz sine wave, pausing to adjust the RF signal level or the switch coupling devices as necessary. The step size shall not exceed 1% of the start and thereafter 1% of the preceding frequency value where the frequency is swept incrementally.
- d. The dwell time at each frequency shall not be less than the time necessary for the EUT to be exercised, and able to respond. Sensitive frequencies such as clock frequencies and harmonics or frequencies of dominant interest, shall be analyzed separately.
- e. Attempts should be made to fully exercise the EUT during test, and to fully interrogate all exercise modes selected for susceptibility.

7.6.3. Test Setup



- a) The EUT clearance from any metallic objects other than test equipment shall be at least 0,5 m.
- b) Only one of the CDNs not used for injection shall be terminated with 50 Ω, providing only a return path. All other CDNs shall be configured as decoupling networks.

For the actual test configuration, please refer to Appendix I: Photographs of the Test Configuration.

7.6.4. Test Result

Test Mode:	Mode 1	Temperature:	22°C
Test Voltage:	AC 230V/ 50Hz	Humidity:	65%RH
Tested By:	Duncan Wang	Test Date:	Dec. 09, 2022

Test Ports (Mode)	Freq. Range (MHz)	Field Strength	CDN	Criterion	Results	Judgement
AC Power Port	0.15 --- 10	3V	M016(M2)	A	A	PASS
	10 --- 30	3 to 1V		A	A	PASS
	30 --- 80	1V		A	A	PASS
Note	There was no abnormal situation during the test compared with initial operation.					

Customer Request:

Test Ports (Mode)	Freq. Range (MHz)	Field Strength	CDN	Criterion	Results	Judgement
AC Power Port	0.15 --- 80	10V	M016(M2)	A	A	PASS
Note	There was no abnormal situation during the test compared with initial operation.					

7.7. Power frequency magnetic field immunity Test


7.7.1. Test Specification

Standard:	EN 55035 (refer to IEC/EN 61000-4-8)
Frequency Range:	50 Hz
Field Strength:	1 A/m
Observation Time:	1 minute
Inductance Coil:	Rectangular type, 1m x 1m

7.7.2. Test Procedure

- a. The EUT and support equipment, are placed on a table that is 0.8 meter above a metal ground plane measured 1m*1m min. and 0.65mm thick min.
- b. The equipment cabinets shall be connected to the safety earth directly on the GRP via the earth terminal of the EUT.
- c. The cables supplied or recommended by the equipment manufacturer shall be used 1 meter of all cables used shall be exposed to the magnetic field.
- d. The EUT with coil shall be leave all magnetic material and wall 1m away in any axis during the test.
- e. The cable length from generator to coil shall be less than 2m
- f. The background noise shall be 20dB less than test field strength.
- g. Test shall be applied to three axis X, Y, Z and disturbance over 1 minute.
- h. All cables shall be exposed to the magnetic field for 1m of their length.

7.7.3. Test Setup



Note:

TABLE-TOP EQUIPMENT

The equipment shall be subjected to the test magnetic field by using the induction coil of standard dimension (1 m x 1 m). The induction coil shall then be rotated by 90 degrees in order to expose the EUT to the test field with different orientations.

FLOOR-STANDING EQUIPMENT

The equipment shall be subjected to the test magnetic field by using induction coils of suitable dimensions. The test shall be repeated by moving and shifting the induction coils, in order to test the whole volume of the EUT for each orthogonal direction. The test shall be repeated with the coil shifted to different positions along the side of the EUT, in steps corresponding to 50% of the shortest side of the coil. The induction coil shall then be rotated by 90 degrees in order to expose the EUT to the test field with different orientations.

For the actual test configuration, please refer to Appendix I: Photographs of the Test Configuration.

7.7.4. Test Results

Test Mode:	Mode 1	Temperature:	22°C
Test Voltage:	AC 230V/ 50Hz	Humidity:	65%RH
Tested By:	Duncan Wang	Test Date:	Dec. 09, 2022

Level	Magnetic Field Strength (A/m)	Criterion	Results			Judgement
			X	Y	Z	
1	1	A	A	A	A	PASS
2	3	/	/	/	/	
3	10	/	/	/	/	
4	30	/	/	/	/	
5	100	/	/	/	/	
X	Special	/	/	/	/	
Note	There was no abnormal situation during the test compared with initial operation.					

Customer Request:

Level	Magnetic Field Strength (A/m)	Criterion	Results			Judgement
			X	Y	Z	
1	1	/	/	/	/	PASS
2	3	/	/	/	/	
3	10	/	/	/	/	
4	30	A	A	A	A	
5	100	/	/	/	/	
X	Special	/	/	/	/	
Note	There was no abnormal situation during the test compared with initial operation.					

7.8. Voltage Dips and Short Interruptions Immunity Test


7.8.1. Test Specification

Standard:	EN 55035 (refer to IEC/EN IEC 61000-4-11)
Voltage Dips:	<5% residual ; 70% residual
Voltage Interruptions:	<5% residual
Voltage Phase Angle:	0°/45°/90°/135°/180°/225°/270°/315°

7.8.2. Test Procedure

- The power cord was used as supplied by the manufacturer. The EUT was connected to the line output of the Voltage Dips and Interruption Generator.
- For voltage dips, changes in supply voltage shall occur at zero crossings of the voltage, and at additional angles considered critical by product committees or individual product specifications preferably selected from 45°, 90°, 135°, 180°, 225°, 270° and 315° on each phase.
- For short interruptions, the angle shall be defined by the product committee as the worst case. In the absence of definition, it is recommended to use 0° for one of the phases.

7.8.3. Test Setup



For the actual test configuration, please refer to Appendix I: Photographs of the Test Configuration.



7.8.4. Test Result

Test Mode:	Mode 1	Temperature:	20°C
Test Voltage:	AC 100-240V/ 50/ 60Hz	Humidity:	57%RH
Tested By:	Rupert Huang	Test Date:	Dec. 19, 2022


100V/60Hz					
Interruption & Dips	Duration (cycle)	Residual voltage	Performance Criteria	Results	Judgment
Voltage dips	0.5	<5%	B	A	PASS
	30	70%	C	A	
Voltage interruptions	300	<5%	C	B	
Note	Results A : The equipment continues to operate as intended without operator intervention. Results B : The output voltage was lost during the test, but it will automatically return to normal conditions after the test.				

240V/50Hz					
Interruption & Dips	Duration (cycle)	Residual voltage	Performance Criteria	Results	Judgment
Voltage dips	0.5	<5%	B	A	PASS
	25	70%	C	A	
Voltage interruptions	250	<5%	C	B	
Note	Results A : The equipment continues to operate as intended without operator intervention. Results B : The output voltage was lost during the test, but it will automatically return to normal conditions after the test.				


Radiated Disturbance: Mode 1, 30M-1GHz





Harmonic and Flicker: Mode 1




Electrostatic Discharge Immunity: Mode 01




Radio Frequency Field Immunity: Mode 01




Electrical Fast Transient Immunity: Mode 01



Surge Immunity: Mode 01




Immunity to conducted disturbance induced by RF fields: Mode 01



Power Frequency Magnetic Immunity: Mode 01



Voltages Dips and Short Interruption Immunity: Mode 01




Appendix II: Photographs of the EUT

Please see the photographs of EUT in the test report no.: 4790423395-EP.

END OF REPORT

Appendix III: Countermeasure file for ESD



Annex : Additional test request by client.

RS TEST RESULT FORM

Project No.: 4790771479

Applicant	TRACO	Product Name	AC/DC Power Supply
Model Name	TPP 15-105A-J	Standard	EN 55035

Test Mode:	Mode 1	Temperature:	22°C
Test Voltage:	AC 230V/ 50Hz	Humidity:	68%RH
Tested By:	Duncan Wang	Test Date:	Dec. 12, 2022

Customer request: H: Horizontal V: Vertical

Freq. Range (MHz)	Position (Face)	Polarity (H or V)	Field Strength (V/m)	Criterion	Results	Judgment
80-1000	Front	H / V	20	A	A	Pass
	Left	H / V	20	A	A	
	Right	H / V	20	A	A	
	Rear	H / V	20	A	A	
1800(±1%)	Front / Left / Right / Rear	H / V	20	A	A	Pass
2600(±1%)	Front / Left / Right / Rear	H / V	20	A	A	Pass
3500(±1%)	Front / Left / Right / Rear	H / V	20	A	A	Pass
5000(±1%)	Front / Left / Right / Rear	H / V	20	A	A	Pass
Note	There was no abnormal situation during the test compared with initial operation.					

Immunity Level to common wireless communication						
Freq. Range (MHz)	Position (Face)	Polarity (H or V)	Field Strength (V/m)	Criterion	Results	Judgment
800	Front / Left / Right / Rear	H / V	20	A	A	Pass
900	Front / Left / Right / Rear	H / V	20	A	A	Pass
1800(±1%)	Front / Left / Right / Rear	H / V	20	A	A	Pass
2600(±1%)	Front / Left / Right / Rear	H / V	20	A	A	Pass
3500(±1%)	Front / Left / Right / Rear	H / V	20	A	A	Pass
5000(±1%)	Front / Left / Right / Rear	H / V	20	A	A	Pass
Note	There was no abnormal situation during the test compared with initial operation.					

CS TEST RESULT FORM

Project No.: 4790771479

Applicant	TRACO	Product Name	AC/DC Power Supply
Model Name	TPP 15-105A-J	Standard	EN 55035

Test Mode:	Mode 1	Temperature:	22°C
Test Voltage:	AC 230V/ 50Hz	Humidity:	65%RH
Tested By:	Duncan Wang	Test Date:	Dec. 09, 2022

Customer request:

Test Ports (Mode)	Freq. Range (MHz)	Field Strength	CDN	Criteria	Results	Judgment
AC Power	0.15 --- 80	20V	M016(M2)	A	A	Pass
Note	There was no abnormal situation during the test compared with initial operation.					