

CE EMC Test Report

Report No.: CE190514C15A

Test Model: TMDC 20-7211H, TMDC 20-7218H, TMDC 20-7222H, TMDC 20-7225H

Series Model: TMDC 20-Series - *Multiple listing see item 3.1*

Received Date: Mar. 22, 2019

Test Date: Mar. 26 to Apr. 25, 2019

Issued Date: Oct. 3, 2019

Applicant: TRACO ELECTRONIC AG

Address: SIHLBRUGGSTRASSE 111 CH-6340 BAAR, SWITZERLAND

Issued By: Bureau Veritas Consumer Products Services (H.K.) Ltd., Taoyuan Branch
Lin Kou Laboratories

Lab Address: No. 47-2, 14th Ling, Chia Pau Vil., Lin Kou Dist., New Taipei City, Taiwan

Test Location (1): No. 47-2, 14th Ling, Chia Pau Vil., Lin Kou Dist., New Taipei City, Taiwan

Test Location (2): No. 49, Lane 206, Wende Rd., Chiung Lin Township, Hsinchu County, Taiwan



This report is for your exclusive use. Any copying or replication of this report to or for any other person or entity, or use of our name or trademark, is permitted only with our prior written permission. This report sets forth our findings solely with respect to the test samples identified herein. The results set forth in this report are not indicative or representative of the quality or characteristics of the lot from which a test sample was taken or any similar or identical product unless specifically and expressly noted. Our report includes all of the tests requested by you and the results thereof based upon the information that you provided to us. You have 60 days from date of issuance of this report to notify us of any material error or omission caused by our negligence, provided, however, that such notice shall be in writing and shall specifically address the issue you wish to raise. A failure to raise such issue within the prescribed time shall constitute your unqualified acceptance of the completeness of this report, the tests conducted and the correctness of the report contents. Unless specific mention, the uncertainty of measurement has been explicitly taken into account to declare the compliance or non-compliance to the specification. The report must not be used by the client to claim product certification, approval, or endorsement by TAF or any government agencies.

Table of Contents

Release Control Record	4
1 Certificate of Conformity	5
2 Summary of Test Results	6
2.1 Measurement Uncertainty	7
2.2 Modification Record	7
3 General Information	8
3.1 Description of EUT	8
3.2 Features of EUT	8
3.3 Operating Modes of EUT and Determination of Worst Case Operating Mode	9
3.4 Test Program Used and Operation Descriptions	9
3.5 Primary Clock Frequencies of Internal Source	9
3.6 Package Specifications by Manufacturer	10
4 Configuration and Connections with EUT	11
4.1 Connection Diagram of EUT and Peripheral Devices	11
4.2 Configuration of Peripheral Devices and Cable Connections	12
5 Conducted Emission from the Mains Power Port	13
5.1 Limits	13
5.2 Test Instruments	13
5.3 Test Arrangement	14
5.4 Test Results	15
6 Radiated Emission at Frequencies up to 1GHz	23
6.1 Limits	23
6.2 Test Instruments	24
6.3 Test Arrangement	25
6.4 Test Results	26
7 General Immunity Requirements	34
7.1 Specific Immunity Requirements by Manufacturer	36
7.2 Performance Criteria	36
8 Electrostatic Discharge Immunity Test (ESD)	37
8.1 Test Specification	37
8.2 Test Instruments	37
8.3 Test Arrangement	38
8.4 Supplementary Information	39
8.5 Test Results	39
9 Radiated, Radio-frequency, Electromagnetic Field Immunity Test (RS)	41
9.1 Test Specification	41
9.2 Test Instruments	41
9.3 Test Arrangement	42
9.4 Supplementary Information	42
9.5 Test Results	43
10 Electrical Fast Transient/Burst Immunity Test (EFT)	44
10.1 Test Specification	44
10.2 Test Instruments	44
10.3 Test Arrangement	45
10.4 Supplementary Information	45
10.5 Test Results	46

11	Surge Immunity Test.....	47
11.1	Test Specification.....	47
11.2	Test Instruments	47
11.3	Test Arrangement	48
11.4	Supplementary Information	49
11.5	Test Results	49
12	Immunity to Conducted Disturbances Induced by RF Fields (CS).....	50
12.1	Test Specification.....	50
12.2	Test Instruments	50
12.3	Test Arrangement	51
12.4	Supplementary Information	52
12.5	Test Results	52
13	Power Frequency Magnetic Field Immunity Test.....	53
13.1	Test Specification.....	53
13.2	Test Instruments	53
13.3	Test Arrangement	54
13.4	Supplementary Information	54
13.5	Test Results	55
14	Pictures of Test Arrangements	56
14.1	Conducted Emission from the Mains Power Port	56
14.2	Radiated Emission at Frequencies up to 1GHz	57
14.3	Electrostatic Discharge Immunity Test (ESD)	58
14.4	Radio-frequency, Electromagnetic Field Immunity Test (RS).....	59
14.5	Electrical Fast Transient/Burst Immunity Test (EFT).....	60
14.6	Surge Immunity Test.....	60
14.7	Conducted Disturbances Induced by RF Fields (CS)	61
14.8	Power Frequency Magnetic Field Immunity Test (PFMF)	62
	Appendix – Information of the Testing Laboratories	63

Release Control Record

Issue No.	Description	Date Issued
CE190514C15A	Original release.	Oct. 3, 2019

1 Certificate of Conformity

Product: DC to DC Converter

Brand:



Test Model: TMDC 20-7211H , TMDC 20-7218H, TMDC 20-7222H, TMDC 20-7225H

Series Model: TMDC 20-Series - *Multiple listing see item 3.1*

Sample Status: Engineering sample

Applicant: TRACO ELECTRONIC AG

Test Date: Mar. 26 to Apr. 25, 2019

Standards: **EN 55032:2015 +AC:2016, Class A**

EN 61000-3-2:2014 (Not applicable)

EN 61000-3-3:2013 (Not applicable)

EN 55035:2017

EN 61000-4-2:2009 / IEC 61000-4-2:2008 ED. 2.0

EN 61000-4-3:2006 +A1:2008 +A2:2010 / IEC 61000-4-3:2010 ED. 3.2

EN 61000-4-4:2012 / IEC 61000-4-4:2012 ED. 3.0

EN 61000-4-5:2014 +A1:2017 / IEC 61000-4-5:2014 +A1:2017 ED. 3.0

EN 61000-4-6:2014 +AC:2015 / IEC 61000-4-6:2013 ED. 4.0

EN 61000-4-8:2010 / IEC 61000-4-8:2009 ED. 2.0

EN 61000-4-11:2004 +A1:2017 / IEC 61000-4-11:2004 +A1:2017 ED. 2.0 (Not applicable)

Broadband impulse noise disturbances (Not applicable)

EN 55024:2010 / EN 55024:2010 +A1:2015

EN 61000-4-2:2009 / IEC 61000-4-2:2008 ED. 2.0

EN 61000-4-3:2006 +A1:2008 +A2:2010 / IEC 61000-4-3:2010 ED. 3.2

EN 61000-4-4:2012 / IEC 61000-4-4:2012 ED. 3.0

EN 61000-4-5:2014 +A1:2017 / IEC 61000-4-5:2014 +A1:2017 ED. 3.0

EN 61000-4-6:2014 +AC:2015 / IEC 61000-4-6:2013 ED. 4.0

EN 61000-4-8:2010 / IEC 61000-4-8:2009 ED. 2.0

EN 61000-4-11:2004 +A1:2017 / IEC 61000-4-11:2004 +A1:2017 ED. 2.0 (Not applicable)

The above equipment has been tested by **Bureau Veritas Consumer Products Services (H.K.) Ltd., Taoyuan Branch**, and found compliance with the requirement of the above standards. The test record, data evaluation & Equipment Under Test (EUT) configurations represented herein are true and accurate accounts of the measurements of the sample's EMC characteristics under the conditions specified in this report.


Prepared by :



Celia Chen / Supervisor

Date: Oct. 3, 2019

Approved by :



Kenny Meng / Assistant Manager

Date: Oct. 3, 2019

2 Summary of Test Results

Emission			
Standard	Test Item	Result/Remarks	Verdict
EN 55032:2015 +AC:2016	Conducted emission from the mains power port	Minimum passing Class A margin is -6.62 dB at 0.22168 MHz	Pass
	Asymmetric mode conducted emission at telecommunication ports and tuner ports	Without telecom port of the EUT	N/A
	Radiated emission 30-1000 MHz	Minimum passing Class A margin is -3.01 dB at 60.09 MHz	Pass
	Radiated emission above 1GHz	EUT's highest frequency is below 108MHz	N/A
	Conducted differential voltage emissions	Without tuner function of the EUT.	N/A
EN 61000-3-2:2014	Harmonic current emissions	Test not applicable because port does not exist.	N/A
EN 61000-3-3:2013	Voltage fluctuations and flicker	Test not applicable because port does not exist.	N/A

EN 55035, Immunity				
EN 55035 Clause	Basic standard	Test Item	Result/Remarks	Verdict
4.2.1	EN 61000-4-2:2009 / IEC 61000-4-2:2008 ED. 2.0	Electrostatic discharges (ESD)	Performance Criterion A	Pass
4.2.2.2	EN 61000-4-3:2006 +A1:2008 +A2:2010 / IEC 61000-4-3:2010 ED. 3.2	Continuous radiated disturbances (RS)	Performance Criterion A	Pass
4.2.4	EN 61000-4-4:2012 / IEC 61000-4-4:2012 ED. 3.0	Electrical fast transients (EFT)	Performance Criterion A	Pass
4.2.5	EN 61000-4-5:2014 +A1:2017 / IEC 61000-4-5:2014 +A1:2017 ED. 3.0	Surges	Performance Criterion A	Pass
4.2.2.3	EN 61000-4-6:2014 +AC:2015 / IEC 61000-4-6:2013 ED. 4.0	Continuous conducted disturbances (CS)	Performance Criterion A	Pass
4.2.3	EN 61000-4-8:2010 / IEC 61000-4-8:2009 ED. 2.0	Power-frequency magnetic fields (PFMF)	Performance Criterion A	Pass
4.2.6	EN 61000-4-11:2004 +A1:2017 / IEC 61000-4-11:2004 +A1:2017 ED. 2.0	Voltage dips and interruptions	Test not applicable because AC power port does not exist.	N/A
4.2.7	-	Broadband impulse noise disturbances, Repetitive (Applicable only to xDSL ports.)	Without CPE xDSL port of the EUT.	N/A

EN 55035, Immunity				
EN 55035 Clause	Basic standard	Test Item	Result/Remarks	Verdict
4.2.7	-	Broadband impulse noise disturbances, Isolated (Applicable only to xDSL ports.)	Without CPE xDSL port of the EUT.	N/A

EN 55024, Immunity				
EN 55024 Clause	Basic standard	Test Item	Result/Remarks	Verdict
4.2.1	EN 61000-4-2:2009 / IEC 61000-4-2:2008 ED. 2.0	Electrostatic discharges (ESD)	Performance Criterion A	Pass
4.2.3.2	EN 61000-4-3:2006 +A1:2008 +A2:2010 / IEC 61000-4-3:2010 ED. 3.2	Continuous radiated disturbances (RS)	Performance Criterion A	Pass
4.2.2	EN 61000-4-4:2012 / IEC 61000-4-4:2012 ED. 3.0	Electrical fast transients (EFT)	Performance Criterion A	Pass
4.2.5	EN 61000-4-5:2014 +A1:2017 / IEC 61000-4-5:2014 +A1:2017 ED. 3.0	Surges	Performance Criterion A	Pass
4.2.3.3	EN 61000-4-6:2014 +AC:2015 / IEC 61000-4-6:2013 ED. 4.0	Continuous conducted disturbances (CS)	Performance Criterion A	Pass
4.2.4	EN 61000-4-8:2010 / IEC 61000-4-8:2009 ED. 2.0	Power-frequency magnetic fields (PFMF)	Performance Criterion A	Pass
4.2.6	EN 61000-4-11:2004 +A1:2017 / IEC 61000-4-11:2004 +A1:2017 ED. 2.0	Voltage dips and interruptions	Test not applicable because AC power port does not exist.	N/A

Note:

1. There is no deviation to the applied test methods and requirements covered by the scope of this report.
2. The above EN/IEC basic standards are applied with latest version if customer has no special requirement.
3. Determining compliance based on the results of the compliance measurement, not taking into account measurement instrumentation uncertainty.
4. N/A: Not Applicable.

2.1 Measurement Uncertainty

Where relevant, the following measurement uncertainty levels have been estimated for tests performed on the EUT as specified in CISPR 16-4-2:


Measurement	Expanded Uncertainty (k=2) (\pm)	Maximum allowable uncertainty (\pm)
Conducted emission from AC mains power port using AMN, 150kHz ~ 30MHz	2.79 dB	3.4 dB (U_{cispr})
Radiated emission, 30MHz ~ 1GHz	3.67 dB	6.3 dB (U_{cispr})

2.2 Modification Record

There were no modifications required for compliance.

3 General Information

3.1 Description of EUT

Product	DC to DC Converter
Brand	
Test Model	TMDC 20-7211H , TMDC 20-7218H, TMDC 20-7222H, TMDC 20-7225H
Series Model	TMDC 20-Series - Multiple listing see as below note
Model Difference	Refer to note as below
Sample Status	Engineering sample
Operating Software	N/A
Power Supply Rating	Refer to note as below
Accessory Device	N/A
Data Cable Supplied	N/A

Note:

1. This report is issued as a supplementary report of BV CPS report no.: CE190514C15. The difference compared with original report are changing exterior color and thus revised the test photo and adding standard list of EN 55024; therefore all test data was copied from the original test report and all data was verified to meet the standard version.
2. The EUT is a DC to DC Converter, the specifications of standard models were listed as below:

Model Number	Input Voltage (Range)	Output Voltage
Standard	VDC	VDC
TMDC 20-7211H-B1	110 (80 ~ 160)	5
TMDC 20-7211H		5.1
TMDC 20-7212H		12
TMDC 20-7213H		15
TMDC 20-7215H		24
TMDC 20-7218H		48
TMDC 20-7222H		±12
TMDC 20-7223H		±15
TMDC 20-7225H		±24

During the test, the **Model No.: TMDC 20-7211H , TMDC 20-7218H, TMDC 20-7222H, TMDC 20-7225H** were selected as the representative models for the test and therefore only their test data were recorded in this report.

3.2 Features of EUT

The tests reported herein were performed according to the method specified by TRACO ELECTRONIC AG, for detailed feature description, please refer to the manufacturer's specifications or user's manual.

3.3 Operating Modes of EUT and Determination of Worst Case Operating Mode

1. The EUT was pre-tested under operating and standby condition and the worst emission level was found under **operating condition**.

2. As client's requirement, test modes are presented in the report as below.

Mode	Model No.	Test Condition	Input power
Conducted emission test & Radiated emission test			
1	TMDC 20-7211H	Full Load	110Vdc
2	TMDC 20-7218H		
3	TMDC 20-7222H		
4	TMDC 20-7225H		
EFT, Surge tests			
1	TMDC 20-7211H	Full Load	110Vdc
2	TMDC 20-7218H		
3	TMDC 20-7222H		
4	TMDC 20-7225H		
ESD, RS, CS, PFMF tests			
1	TMDC 20-7211H	Full Load	110Vdc

3.4 Test Program Used and Operation Descriptions

◆ For Conducted & Radiated tests:

Set the EUT full load.

◆ For Immunity tests:

Connected a resistor load to DC output port of EUT to make EUT have maximum power consumption and a multimeter was used to monitor voltage of output.

3.5 Primary Clock Frequencies of Internal Source


The highest frequency generated or used within the EUT or on which the EUT operates or tunes is below 108MHz, provided by TRACO ELECTRONIC AG, for detailed internal source, please refer to the manufacturer's specifications.

3.6 Package Specifications by Manufacturer

Package Specifications :

Package Specifications Chassis Mounting

Mechanical Dimensions



Connections

Pin	Single Output	Dual Output
1	Remote On/Off	Remote On/Off
2	-Vin	-Vin
3	+Vin	+Vin
4	NC	NC
5	-Vout	-Vout
6	NC	Common
7	+Vout	+Vout
8	NC	NC

NC: No Connection

- ▶ All dimensions in mm (inches)
- ▶ Tolerance: ± 0.5 (± 0.02)


Physical Characteristics

Case Size	: 96.0x54.0x23.3mm (3.78x2.13x0.92 inches)
Case Material	: Plastic resin (flammability to UL 94V-0 rated)
Weight	: 107g


4 Configuration and Connections with EUT

4.1 Connection Diagram of EUT and Peripheral Devices

Emission tests:



Immunity tests:



4.2 Configuration of Peripheral Devices and Cable Connections

Emission tests:

ID	Product	Brand	Model No.	Serial No.	FCC ID	Remarks
A.	Load	N/A	N/A	N/A	N/A	Supplied by client
B.	DC Power Supply	CHROMA	62150H-600S	62150EC00479	N/A	Provided by Lab

ID	Cable Descriptions	Qty.	Length (m)	Shielding (Yes/No)	Cores (Qty.)	Remarks
1.	DC power cable	2	0.05	N	0	Supplied by client
2.	DC power cable	1	1.0	N	0	Provided by Lab
3.	DC power cable	1	10	N	0	Provided by Lab

Note: The core(s) is(are) originally attached to the cable(s).

Immunity tests:

ID	Product	Brand	Model No.	Serial No.	FCC ID	Remarks
A.	Load	N/A	N/A	N/A	N/A	Supplied by client
B.	Multimeter	YFE	YF-370A	N/A	N/A	Provided by Lab
C.	DC Power Supply	CHROMA	62150H-600S	62150EC00479	N/A	Provided by Lab

Note: All power cords of the above support units are non-shielded (1.8m).

ID	Cable Descriptions	Qty.	Length (m)	Shielding (Yes/No)	Cores (Qty.)	Remarks
1.	DC power cable	2	0.05	N	0	Supplied by client
2.	Data cable	1	1.2	N	0	Provided by Lab
3.	DC power cable	1	1.8	N	0	Provided by Lab
4.	DC power cable	1	2.0	N	0	Provided by Lab

Note: The core(s) is(are) originally attached to the cable(s).

5 Conducted Emission from the Mains Power Port

5.1 Limits

Frequency range (MHz)	Coupling device	Detector type / bandwidth	Class A limits (dBuV)
0.15 - 0.5	AMN	Quasi-peak / 9kHz	79
0.5 - 30.0			73
0.15 - 0.5		Average / 9kHz	66
0.5 - 30.0			60

Frequency range (MHz)	Coupling device	Detector type / bandwidth	Class B limits (dBuV)
0.15 - 0.5	AMN	Quasi-peak / 9kHz	66 - 56
0.5 - 5			56
5 - 30.0			60
0.15 - 0.5		Average / 9kHz	56 - 46
0.5 - 5			46
5 - 30.0			50

5.2 Test Instruments


Description & Manufacturer	Model No.	Serial No.	Cal. Date	Cal. Due
ROHDE & SCHWARZ TEST RECEIVER	ESR3	102414	Jan. 17, 2019	Jan. 16, 2020
ROHDE & SCHWARZ Artificial Mains Network (for EUT)	ENV216	101197	May 23, 2018	May 22, 2019
LISN With Adapter (for EUT)	AD10	C10Ada-002	May 23, 2018	May 22, 2019
ROHDE & SCHWARZ Artificial Mains Network (for peripherals)	ESH3-Z5	100218	Nov. 30, 2018	Nov. 29, 2019
SCHWARZBECK Artificial Mains Network (For EUT)	NNLK8129	8129229	May 3, 2018	May 2, 2019
SCHWARZBECK Artificial Mains Network (For EUT)	NNLK 8121	8121-808	Mar. 15, 2019	Mar. 14, 2020
Software	Cond_V7.3.7.4	NA	NA	NA
RF cable (JYEBAO) With 10dB PAD	5D-FB	Cable-C10.01	Feb. 13, 2019	Feb. 12, 2020
SUHNTER Terminator (For ROHDE & SCHWARZ LISN)	65BNC-5001	E1-011484	May 8, 2018	May 7, 2019
ROHDE & SCHWARZ Artificial Mains Network (For TV EUT)	ESH3-Z5	100220	Nov. 21, 2018	Nov. 20, 2019
LISN With Adapter (for TV EUT)	100220	NA	Nov. 21, 2018	Nov. 20, 2019

- Note: 1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
2. The test was performed in Shielded Room No. 10.
3. The VCCI Site Registration No. C-11852.
4. Tested Date: Mar. 26, 2019.

5.3 Test Arrangement

- The EUT was placed 0.4 meters from the conducting wall of the shielded room with EUT being connected to the power mains through an Artificial Mains Network (AMN). Other support units were connected to the power mains through another AMN. The two AMNs provide 50 Ohm/ 50uH of coupling impedance for the measuring instrument.
- Both lines of the power mains connected to the EUT were checked for maximum conducted interference.
- The test results of conducted emissions at mains ports are recorded of six worst margins for quasi-peak (mandatory) [and average (if necessary)] values against the limits at frequencies of interest unless the margin is 20 dB or greater.

Note: The resolution bandwidth and video bandwidth of test receiver is 9kHz for quasi-peak detection (QP) and average detection (AV) at frequency 0.15MHz-30MHz.



- Note:**
1. Support units were connected to second AMN.
 2. The distance specified between EUT/AE and other metallic objects is ≥ 0.8 m in the measurement arrangement for table-top EUT.
 3. Cable on the RGP must to be insulated.

For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.


5.4 Test Results

Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	110Vdc	Environmental Conditions	25°C, 75%RH, 1010mbar
Tested by	Hermes Lin		
Test Mode	Mode 1		

Phase Of Power : Positive (+)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.22168	9.99	49.41	49.39	59.40	59.38	79.00	66.00	-19.60	-6.62
2	0.44325	10.02	40.71	40.69	50.73	50.71	79.00	66.00	-28.27	-15.29
3	1.10837	10.07	37.07	37.06	47.14	47.13	73.00	60.00	-25.86	-12.87
4	3.98844	10.12	40.19	40.17	50.31	50.29	73.00	60.00	-22.69	-9.71
5	4.65242	10.14	38.73	38.52	48.87	48.66	73.00	60.00	-24.13	-11.34
6	23.49039	10.57	39.91	36.98	50.48	47.55	73.00	60.00	-22.52	-12.45

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	110Vdc	Environmental Conditions	25°C, 75%RH, 1010mbar
Tested by	Hermes Lin		
Test Mode	Mode 1		

Phase Of Power : Negative (-)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.22154	9.98	46.03	46.02	56.01	56.00	79.00	66.00	-22.99	-10.00
2	0.44325	10.02	36.19	36.15	46.21	46.17	79.00	66.00	-32.79	-19.83
3	1.10866	10.07	35.94	35.92	46.01	45.99	73.00	60.00	-26.99	-14.01
4	9.97743	10.32	37.33	37.15	47.65	47.47	73.00	60.00	-25.35	-12.53
5	14.19169	10.43	38.28	37.99	48.71	48.42	73.00	60.00	-24.29	-11.58
6	23.50212	10.67	41.15	39.99	51.82	50.66	73.00	60.00	-21.18	-9.34

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	110Vdc	Environmental Conditions	25°C, 75%RH, 1010mbar
Tested by	Hermes Lin		
Test Mode	Mode 2		

Phase Of Power : Positive (+)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.28288	10.00	41.10	41.08	51.10	51.08	79.00	66.00	-27.90	-14.92
2	0.56647	10.03	36.44	36.43	46.47	46.46	73.00	60.00	-26.53	-13.54
3	9.05076	10.27	40.63	40.58	50.90	50.85	73.00	60.00	-22.10	-9.15
4	10.18075	10.30	40.69	40.61	50.99	50.91	73.00	60.00	-22.01	-9.09
5	11.02922	10.32	40.47	40.34	50.79	50.66	73.00	60.00	-22.21	-9.34
6	15.83852	10.41	38.83	38.15	49.24	48.56	73.00	60.00	-23.76	-11.44

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	110Vdc	Environmental Conditions	25°C, 75%RH, 1010mbar
Tested by	Hermes Lin		
Test Mode	Mode 2		

Phase Of Power : Negative (-)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.28294	10.00	29.20	29.19	39.20	39.19	79.00	66.00	-39.80	-26.81
2	0.56647	10.03	34.78	34.75	44.81	44.78	73.00	60.00	-28.19	-15.22
3	9.04685	10.29	39.40	38.87	49.69	49.16	73.00	60.00	-23.31	-10.84
4	9.89532	10.32	38.49	38.07	48.81	48.39	73.00	60.00	-24.19	-11.61
5	11.02531	10.35	38.36	36.69	48.71	47.04	73.00	60.00	-24.29	-12.96
6	25.44539	10.71	34.81	31.90	45.52	42.61	73.00	60.00	-27.48	-17.39

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	110Vdc	Environmental Conditions	25°C, 75%RH, 1010mbar
Tested by	Hermes Lin		
Test Mode	Mode 3		

Phase Of Power : Positive (+)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.28815	10.00	42.08	42.07	52.08	52.07	79.00	66.00	-26.92	-13.93
2	0.57641	10.03	38.49	38.47	48.52	48.50	73.00	60.00	-24.48	-11.50
3	1.15297	10.07	38.82	38.80	48.89	48.87	73.00	60.00	-24.11	-11.13
4	7.49458	10.22	41.01	40.89	51.23	51.11	73.00	60.00	-21.77	-8.89
5	9.51214	10.29	40.41	40.07	50.70	50.36	73.00	60.00	-22.30	-9.64
6	13.84051	10.37	40.21	38.97	50.58	49.34	73.00	60.00	-22.42	-10.66

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	110Vdc	Environmental Conditions	25°C, 75%RH, 1010mbar
Tested by	Hermes Lin		
Test Mode	Mode 3		

Phase Of Power : Negative (-)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.28772	10.00	33.38	33.37	43.38	43.37	79.00	66.00	-35.62	-22.63
2	0.57670	10.03	37.63	37.61	47.66	47.64	73.00	60.00	-25.34	-12.36
3	1.15297	10.07	38.88	38.87	48.95	48.94	73.00	60.00	-24.05	-11.06
4	8.64803	10.27	40.23	40.14	50.50	50.41	73.00	60.00	-22.50	-9.59
5	12.97249	10.40	40.24	40.14	50.64	50.54	73.00	60.00	-22.36	-9.46
6	13.84051	10.42	39.00	37.49	49.42	47.91	73.00	60.00	-23.58	-12.09

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	110Vdc	Environmental Conditions	25°C, 75%RH, 1010mbar
Tested by	Hermes Lin		
Test Mode	Mode 4		

Phase Of Power : Positive (+)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.28100	10.00	41.31	41.30	51.31	51.30	79.00	66.00	-27.69	-14.70
2	0.56256	10.03	35.89	35.88	45.92	45.91	73.00	60.00	-27.08	-14.09
3	1.12560	10.07	36.54	36.53	46.61	46.60	73.00	60.00	-26.39	-13.40
4	9.56688	10.29	40.62	40.61	50.91	50.90	73.00	60.00	-22.09	-9.10
5	13.78577	10.37	40.44	40.25	50.81	50.62	73.00	60.00	-22.19	-9.38
6	14.63033	10.39	40.26	40.13	50.65	50.52	73.00	60.00	-22.35	-9.48

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	110Vdc	Environmental Conditions	25°C, 75%RH, 1010mbar
Tested by	Hermes Lin		
Test Mode	Mode 4		

Phase Of Power : Negative (-)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.56256	10.03	33.70	33.69	43.73	43.72	73.00	60.00	-29.27	-16.28
2	1.12560	10.07	35.65	35.64	45.72	45.71	73.00	60.00	-27.28	-14.29
3	10.41144	10.33	41.29	41.08	51.62	51.41	73.00	60.00	-21.38	-8.59
4	11.25600	10.35	41.38	40.98	51.73	51.33	73.00	60.00	-21.27	-8.67
5	12.10056	10.38	41.12	40.67	51.50	51.05	73.00	60.00	-21.50	-8.95
6	13.78577	10.42	41.16	40.93	51.58	51.35	73.00	60.00	-21.42	-8.65

Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value



6 Radiated Emission at Frequencies up to 1GHz

6.1 Limits

For Class A Equipment

Frequency range (MHz)	Distance (m)	Limits (dBuV/m)
30 - 230	10	40
230 - 1000		47
30 - 230	3	50
230 - 1000		57

For Class B Equipment

Frequency range (MHz)	Distance (m)	Limits (dBuV/m)
30 - 230	10	30
230 - 1000		37
30 - 230	3	40
230 - 1000		47

For FM Receivers

Frequency range (MHz)	Measurement		Class B limits (dBuV/m)	
	Distance (m)	Detector type/ bandwidth	Fundamental	Harmonics
30 - 230	10	Quasi peak/ 120 kHz	50	42
230 - 300				42
300 - 1000				46
30 - 230	3		60	52
230 - 300				52
300 - 1000				56

These relaxed limits apply only to emissions at the fundamental and harmonic frequencies of the local oscillator. Signals at all other frequencies shall be compliant with the limits given in Table A4.1 & A4.2 of EN 55032.

6.2 Test Instruments

Description & Manufacturer	Model No.	Serial No.	Cal. Date	Cal. Due
EMCI Preamplifier	EMC9135	980326	Feb. 20, 2019	Feb. 19, 2020
EMCI Preamplifier	EMC9135	980327	Feb. 20, 2019	Feb. 19, 2020
Agilent Test Receiver	N9038A	MY50010158	Jun. 27, 2018	Jun. 26, 2019
Agilent Test Receiver	N9038A	MY51210114	Jul. 2, 2018	Jul. 1, 2019
Schwarzbeck Antenna	VULB9168	9168-316	Nov. 27, 2018	Nov. 26, 2019
Schwarzbeck Antenna	VULB9168	9168-317	Nov. 27, 2018	Nov. 26, 2019
Max Full. Turn Table & Tower	MF7802	MF7802121	NA	NA
Max Full. Tower	MF7802	MF780208105	NA	NA
Software	Radiated_V8.7.08	NA	NA	NA
JYEBAO RF cable With 5dB PAD	LMR-600	CABLE-CH8-01.V	Sep. 28, 2018	Sep. 27, 2019
JYEBAO RF cable With 5dB PAD	LMR-600	CABLE-CH8-02.H	Sep. 28, 2018	Sep. 27, 2019
WOKEN RF cable With 5dB PAD	8D	CABLE-CH8-03.3M	Sep. 28, 2018	Sep. 27, 2019


Note: 1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
 2. The test was performed in Chamber No. 8.
 3. The Industry Canada Reference No. IC 7450E-8.
 4. The VCCI Site Registration No. R-12946.
 5. Tested Date: Mar. 29, 2019.

6.3 Test Arrangement

- The EUT was placed on the top of a rotating table 0.8 meters above the ground at an accredited test facility. The table was rotated 360 degrees to determine the position of the highest radiation.
- The EUT was set 10 meters away from the interference-receiving antenna, which was mounted on the top of a variable-height antenna tower.
- The antenna is a broadband antenna, and its height is varied from one meter to four meters above the ground to determine the maximum value of the field strength. Both horizontal and vertical polarizations of the antenna are set to make the measurement.
- For each suspected emission, the EUT was arranged to its worst case and then the antenna was tuned to heights from 1 meter to 4 meters and the rotatable table was turned from 0 degrees to 360 degrees to find the maximum reading.
- The test-receiver system was set to quasi-peak detect function and specified bandwidth with maximum hold mode when the test frequency is up to 1 GHz.

Note:

- The resolution bandwidth and video bandwidth of test receiver/spectrum analyzer is 120kHz for quasi-peak detection (QP) at frequency up to 1GHz.
- The measurement distance is the shortest horizontal distance between an imaginary circular periphery just encompassing this arrangement and the calibration point of the antenna.



Note: Cable on the RGP must be insulated.

For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.


6.4 Test Results

Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Input Power	110Vdc	Environmental Conditions	24°C, 73%RH, 1002mbar
Tested by	Paul Chen		
Test Mode	Mode 1		

Antenna Polarity & Test Distance : Horizontal at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	60.09	19.79 QP	40.00	-20.21	4.00 H	77	38.07	-18.28
2	190.80	19.16 QP	40.00	-20.84	4.00 H	339	38.42	-19.26
3	279.77	30.52 QP	47.00	-16.48	3.85 H	186	47.29	-16.77
4	300.22	33.07 QP	47.00	-13.93	3.56 H	17	49.31	-16.24
5	329.83	27.10 QP	47.00	-19.90	3.43 H	216	42.62	-15.52
6	411.91	24.90 QP	47.00	-22.10	2.77 H	144	38.61	-13.71

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Input Power	110Vdc	Environmental Conditions	24°C, 73%RH, 1002mbar
Tested by	Paul Chen		
Test Mode	Mode 1		

Antenna Polarity & Test Distance : Vertical at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	54.98	35.29 QP	40.00	-4.71	2.15 V	332	53.39	-18.10
2	60.09	34.68 QP	40.00	-5.32	1.87 V	312	53.15	-18.47
3	75.52	29.37 QP	40.00	-10.63	1.00 V	333	50.57	-21.20
4	192.89	32.96 QP	40.00	-7.04	1.00 V	264	52.07	-19.11
5	282.35	34.83 QP	47.00	-12.17	1.00 V	235	51.10	-16.27
6	299.83	36.76 QP	47.00	-10.24	1.00 V	299	52.48	-15.72
7	340.84	31.70 QP	47.00	-15.30	1.00 V	332	46.33	-14.63

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Input Power	110Vdc	Environmental Conditions	24°C, 73%RH, 1002mbar
Tested by	Paul Chen		
Test Mode	Mode 2		

Antenna Polarity & Test Distance : Horizontal at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	55.44	20.98 QP	40.00	-19.02	4.00 H	38	39.01	-18.03
2	67.85	21.31 QP	40.00	-18.69	4.00 H	74	40.79	-19.48
3	109.10	19.83 QP	40.00	-20.17	4.00 H	121	40.23	-20.40
4	184.55	18.65 QP	40.00	-21.35	4.00 H	357	37.45	-18.80
5	288.70	27.56 QP	47.00	-19.44	3.88 H	351	44.10	-16.54
6	434.15	24.27 QP	47.00	-22.73	2.97 H	132	37.01	-12.74

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Input Power	110Vdc	Environmental Conditions	24°C, 73%RH, 1002mbar
Tested by	Paul Chen		
Test Mode	Mode 2		

Antenna Polarity & Test Distance : Vertical at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	56.02	36.57 QP	40.00	-3.43	1.87 V	139	54.78	-18.21
2	60.53	36.64 QP	40.00	-3.36	2.05 V	312	55.33	-18.69
3	73.53	32.86 QP	40.00	-7.14	1.36 V	305	53.66	-20.80
4	159.35	26.91 QP	40.00	-13.09	1.00 V	73	43.55	-16.64
5	186.29	33.93 QP	40.00	-6.07	1.00 V	56	52.61	-18.68
6	287.32	33.38 QP	47.00	-13.62	1.00 V	282	49.53	-16.15

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Input Power	110Vdc	Environmental Conditions	24°C, 73%RH, 1002mbar
Tested by	Paul Chen		
Test Mode	Mode 3		

Antenna Polarity & Test Distance : Horizontal at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	55.41	18.31 QP	40.00	-21.69	4.00 H	139	36.34	-18.03
2	69.24	19.86 QP	40.00	-20.14	4.00 H	74	39.82	-19.96
3	109.10	20.58 QP	40.00	-19.42	4.00 H	332	40.98	-20.40
4	156.66	19.66 QP	40.00	-20.34	4.00 H	316	36.69	-17.03
5	279.12	26.09 QP	47.00	-20.91	3.88 H	187	42.88	-16.79
6	325.58	22.24 QP	47.00	-24.76	3.25 H	183	37.86	-15.62

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Input Power	110Vdc	Environmental Conditions	24°C, 73%RH, 1002mbar
Tested by	Paul Chen		
Test Mode	Mode 3		

Antenna Polarity & Test Distance : Vertical at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	54.88	32.61 QP	40.00	-7.39	1.78 V	326	50.73	-18.12
2	60.51	30.78 QP	40.00	-9.22	1.56 V	312	49.46	-18.68
3	73.19	30.07 QP	40.00	-9.93	2.07 V	297	50.81	-20.74
4	156.61	31.36 QP	40.00	-8.64	1.00 V	263	48.10	-16.74
5	177.46	30.89 QP	40.00	-9.11	1.00 V	51	48.58	-17.69
6	266.12	29.75 QP	47.00	-17.25	1.00 V	270	46.69	-16.94

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Input Power	110Vdc	Environmental Conditions	24°C, 73%RH, 1002mbar
Tested by	Paul Chen		
Test Mode	Mode 4		

Antenna Polarity & Test Distance : Horizontal at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	60.39	22.32 QP	40.00	-17.68	4.00 H	115	40.74	-18.42
2	67.90	19.63 QP	40.00	-20.37	4.00 H	74	39.13	-19.50
3	108.84	20.13 QP	40.00	-19.87	4.00 H	71	40.54	-20.41
4	187.87	16.66 QP	40.00	-23.34	4.00 H	347	35.72	-19.06
5	280.53	25.89 QP	47.00	-21.11	3.96 H	166	42.64	-16.75
6	327.69	25.83 QP	47.00	-21.17	3.52 H	343	41.40	-15.57

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Input Power	110Vdc	Environmental Conditions	24°C, 73%RH, 1002mbar
Tested by	Paul Chen		
Test Mode	Mode 4		

Antenna Polarity & Test Distance : Vertical at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	55.85	36.33 QP	40.00	-3.67	1.29 V	39	54.52	-18.19
2	60.09	36.99 QP	40.00	-3.01	1.07 V	280	55.46	-18.47
3	72.66	31.08 QP	40.00	-8.92	2.21 V	330	51.71	-20.63
4	175.96	28.76 QP	40.00	-11.24	1.00 V	43	46.26	-17.50
5	280.50	28.84 QP	47.00	-18.16	1.00 V	229	45.17	-16.33
6	337.78	27.51 QP	47.00	-19.49	1.00 V	344	42.17	-14.66

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value



7 General Immunity Requirements

EN 55035:2017, Immunity requirements

Reference standard	Test specification	Performance Criterion
EN/IEC 61000-4-2 ESD	Enclosure port: $\pm 8\text{kV}$ Air discharge, $\pm 4\text{kV}$ Contact discharge	B
EN/IEC 61000-4-3 RS	Enclosure port: Swept freq. test : 80-1000 MHz, 3V/m, 80% AM (1kHz), Spot freq. test : 1800, 2600, 3500, 5000 MHz ($\pm 1\%$), 3V/m, 80% AM (1kHz)	A
EN/IEC 61000-4-4 EFT	Analogue/digital data ports (cable length > 3m): xDSL equipment: $\pm 0.5\text{kV}$, 5/50 (T_r/T_h) ns, 100kHz others: $\pm 0.5\text{kV}$, 5/50 (T_r/T_h) ns, 5kHz	B
	DC network power port (cable length > 3m): $\pm 0.5\text{kV}$, 5/50 (T_r/T_h) ns, 5kHz	
	AC mains power ports: $\pm 1.0\text{kV}$, 5/50 (T_r/T_h) ns, 5kHz	
EN/IEC 61000-4-5 Surge	Analogue/digital data ports (direct to outdoor cables): Port type: unshielded symmetrical 10/700(5/320) (T_r/T_h) μs , w/o primary protectors (line to ground): $\pm 1.0\text{kV}$, or with primary protectors (line to ground): $\pm 1.0\text{kV}$, $\pm 4.0\text{kV}$ Port type: coaxial or shielded 1.2/50 (8/20) (T_r/T_h) μs , shield to ground: $\pm 0.5\text{kV}$	C
	DC network power port (direct to outdoor cables): 1.2/50(8/20) (T_r/T_h) μs , Line to ground: $\pm 0.5\text{kV}$	B
	AC mains power ports: 1.2/50(8/20) (T_r/T_h) μs , Line to line: $\pm 1\text{kV}$, Line to ground: $\pm 2\text{kV}$	B
EN/IEC 61000-4-6 CS	Analogue/digital data ports (cable length > 3m) ; DC network power ports (cable length > 3m) ; AC mains power ports 0.15-10 MHz, 3V, 80% AM (1kHz), 10-30 MHz, 3V-1V, 80% AM (1kHz), 30-80 MHz, 1V, 80% AM (1kHz)	A
EN/IEC 61000-4-8 PFMF	Enclosure port: 50 or 60 Hz, 1A/m	A

EN 55024:2010 / EN 55024:2010 +A1:2015, Immunity requirements

Clause	Reference standard	Table	Test specification	Performance Criterion
4.2.1	EN/IEC 61000-4-2 ESD	1.3	Enclosure port: ±8kV Air discharge, ±4kV Contact discharge	B
4.2.3.2	EN/IEC 61000-4-3 RS	1.2	Enclosure port: 80-1000 MHz, 3V/m, 80% AM (1kHz)	A
4.2.2	EN/IEC 61000-4-4 EFT	2.3	Signal ports and telecommunication ports: xDSL equipment: ±0.5kV, 5/50 (T _r /T _h) ns, 100kHz others: ±0.5kV, 5/50 (T _r /T _h) ns, 5kHz	B
		3.3	Input DC power port: ±0.5kV, 5/50 (T _r /T _h) ns, 5kHz	
		4.5	Input AC Power ports: ±1kV, 5/50 (T _r /T _h) ns, 5kHz	
4.2.5	EN/IEC 61000-4-5 Surge	2.2	Signal and telecommunication ports (direct to outdoor cables): 10/700 (5/320) (T _r /T _h) µs w/o primary protectors: ±1kV, or with primary protectors fitted: ±4kV	C
		3.2	Input DC power port (direct to outdoor cables): 1.2/50 (8/20) (T _r /T _h) µs Line to earth: ±0.5kV	B
		4.4	Input AC Power ports: 1.2/50 (8/20) (T _r /T _h) µs, Line to line: ±1kV Line to earth: ±2kV	
4.2.3.3	EN/IEC 61000-4-6 CS	2.1	Signal and telecommunication ports(cable length > 3m): 0.15-80 MHz, 3V, 80% AM (1kHz)	A
		3.1	Input DC power port: 0.15-80 MHz, 3V, 80% AM (1kHz)	
		4.1	Input AC Power ports: 0.15-80 MHz, 3V, 80% AM (1kHz)	
4.2.4	EN/IEC 61000-4-8 PFMF	1.1	Enclosure port: 50 or 60 Hz, 1A/m	A

7.1 Specific Immunity Requirements by Manufacturer

Additional Test		
Reference standard	Test specification	Performance Criterion
EN/IEC 61000-4-2 ESD	Enclosure port: ±6kV Contact discharge	A
EN/IEC 61000-4-3 RS	Enclosure port: Swept freq. test : 80-1000 MHz, 10V/m, 80% AM (1kHz), Spot freq. test : 1800, 2600, 3500, 5000 MHz (±1 %), 10V/m, 80% AM (1kHz)	A
EN/IEC 61000-4-4 EFT	DC network power port (cable length > 3m): ±2kV, 5/50 (T _r /T _n) ns, 5kHz	A
EN/IEC 61000-4-5 Surge	DC network power port (direct to outdoor cables): 1.2/50(8/20) (T _r /T _n) μs, Line to line: ±2kV	A
EN/IEC 61000-4-6 CS	Input DC Power ports: 0.15-80 MHz, 10V, 80% AM (1kHz)	A
EN/IEC 61000-4-8 PFMF	Enclosure port: 50 Hz, 100A/m (1 min.) 50 Hz, 1000A/m (1 sec.)	A

7.2 Performance Criteria

General Performance Criteria

Performance criterion A

The equipment shall continue to operate as intended without operator intervention. No degradation of performance or loss of function is allowed below a performance level specified by the manufacturer when the equipment is used as intended. The performance level may be replaced by a permissible loss of performance. If the minimum performance level or the permissible performance loss is not specified by the manufacturer, then either of these may be derived from the product description and documentation, and by what the user may reasonably expect from the equipment if used as intended.

Performance criterion B

After the test, the equipment shall continue to operate as intended without operator intervention. No degradation of performance or loss of function is allowed, after the application of the phenomena below a performance level specified by the manufacturer, when the equipment is used as intended. The performance level may be replaced by a permissible loss of performance. During the test, degradation of performance is allowed. However, no change of operating state or stored data is allowed to persist after the test. If the minimum performance level (or the permissible performance loss) is not specified by the manufacturer, then either of these may be derived from the product description and documentation, and by what the user may reasonably expect from the equipment if used as intended.

Performance criterion C

Loss of function is allowed, provided the function is self-recoverable, or can be restored by the operation of the controls by the user in accordance with the manufacturer's instructions. Functions, and/or information stored in non-volatile memory, or protected by a battery backup, shall not be lost.

Product Specific Performance Criteria

The particular performance criteria which are specified in the normative annexes of EN 55035 / EN 55024 take precedence over the corresponding parts of the general performance criteria. Where particular performance criteria for specific functions are not given, then the general performance criteria shall apply.

8 Electrostatic Discharge Immunity Test (ESD)

8.1 Test Specification

Basic Standard:	EN/IEC 61000-4-2
Discharge Impedance:	330 ohm / 150 pF
Discharge Voltage:	Air Discharge: $\pm 2\text{kV}$, $\pm 4\text{kV}$, $\pm 8\text{kV}$ (Direct) Contact Discharge: $\pm 2\text{kV}$, $\pm 4\text{kV}$, $\pm 6\text{kV}$ (Indirect/ Direct)
Number of Discharge:	Air – Direct: 10 discharges per location (each polarity) Contact – Direct & Indirect: 10 discharges per location (each polarity)
Discharge Mode:	Single Discharge
Discharge Period:	1-second minimum

8.2 Test Instruments

Description & Manufacturer	Model No.	Serial No.	Cal. Date	Cal. Due
EM Test ESD Simulator	Dito	V0707102251	Apr. 08, 2019	Apr. 07, 2020

- Note:
1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
 2. The test was performed in ESD Room No. 3.
 3. Tested Date: Apr. 10, 2019.

8.3 Test Arrangement

The basic test procedure was in accordance with EN/IEC 61000-4-2:

- Electrostatic discharges were applied only to those points and surfaces of the EUT that are accessible to users during normal operation.
- The test was performed with at least ten single discharges on the pre-selected points in the most sensitive polarity.
- The time interval between two successive single discharges was at least 1 second.
- The ESD generator was held perpendicularly to the surface to which the discharge was applied and the return cable was at least 0.2 meters from the EUT.
- Contact discharges were applied to the non-insulating coating, with the pointed tip of the generator penetrating the coating and contacting the conducting substrate.
- Air discharges were applied with the round discharge tip of the discharge electrode approaching the EUT as fast as possible (without causing mechanical damage) to touch the EUT. After each discharge, the ESD generator was removed from the EUT and re-triggered for a new single discharge. The test was repeated until all discharges were complete.
- At least ten single discharges (in the most sensitive polarity) were applied to the **Horizontal Coupling Plane** at points on each side of the EUT. The ESD generator was positioned at a distance of 0.1 meters from the EUT with the discharge electrode touching the **HCP**.
- At least ten single discharges (in the most sensitive polarity) were applied to the center of one vertical edge of the **Vertical Coupling Plane** in sufficiently different positions that the four faces of the EUT were completely illuminated. The **VCP** (dimensions 0.5m x 0.5m) was placed vertically to and 0.1 meters from the EUT.




TABLE-TOP EQUIPMENT

The configuration consisted of a wooden table 0.8 meters high standing on the **Ground Reference Plane**. The **GRP** consisted of a sheet of aluminum at least 0.25mm thick, and 2.5 meters square connected to the protective grounding system. A **Horizontal Coupling Plane** (1.6m x 0.8m) was placed on the table and attached to the **GRP** by means of a cable with $940k\Omega$ total impedance. The equipment under test, was installed in a representative system as described in section 7 of EN/IEC 61000-4-2, and its cables were placed on the **HCP** and isolated by an insulating support of 0.5mm thickness. A distance of 1-meter minimum was provided between the EUT and the walls of the laboratory and any other metallic structure.

For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

8.4 Supplementary Information

The requirement followed by the client's specification. (Refer to item 7.1)

8.5 Test Results

Input Power	110Vdc	Tested by	Thomas Cheng
Environmental Conditions	23 °C, 41% RH 1003 mbar	Test mode	Mode 1

Test Results of Direct Application					
Discharge Level (kV)	Polarity (+/-)	Test Point	Contact Discharge	Air Discharge	Performance Criterion
2, 4, 8	+/-	1, 2	NA	Note	A
2, 4, 6	+/-	3	Note	NA	A

Description of test points of direct application: Please refer to following page for representative mark only.



Test Results of Indirect Application					
Discharge Level (kV)	Polarity (+/-)	Test Point	Horizontal Coupling Plane	Vertical Coupling Plane	Performance Criterion
2, 4, 6	+/-	Four Sides	Note	Note	A

Description of test points of indirect application:

1. Front side
2. Rear side
3. Right side
4. Left side

Note: The EUT function was correct during the test.

Description of Test Points



9 Radiated, Radio-frequency, Electromagnetic Field Immunity Test (RS)

9.1 Test Specification

Basic Standard:	EN/IEC 61000-4-3
Swept Frequency Range:	80 MHz - 1000 MHz
Spot Frequencies:	1800, 2600, 3500, 5000 MHz (± 1 %)
Field Strength:	3 V/m, 10 V/m
Modulation:	1kHz Sine Wave, 80%, AM Modulation
Frequency Step:	1 % of preceding frequency value
Polarity of Antenna:	Horizontal and Vertical
Antenna Height:	1.5m
Dwell Time:	3 seconds

9.2 Test Instruments

Description & Manufacturer	Model No.	Serial No.	Cal. Date	Cal. Due
BOONTON Power Meter	4232A	94901	Jun. 5, 2018	Jun. 4, 2019
BOONTON Power Sensor	51011-EMC	32807	Sep. 10, 2018	Sep. 9, 2019
BOONTON Power Sensor	51011-EMC	32832	Jun. 4, 2018	Jun. 3, 2019
TESEQ RF Generator	ITS 6006	37543	May 9, 2018	May 8, 2019
ETS Electric Field Sensor	HI-6105	00086973	Dec. 4, 2018	Dec. 3, 2019
TESEQ RF Amplifier	CBA1G-150	T44220	NA	NA
TESTQ Amplifier	CBA 3G-050	T44345	NA	NA
TESTQ Amplifier	AS1860-50	S-5944/1	NA	NA
Schwarzbeck RS Antenna	STLP 9129	9129068	NA	NA
CHANCE MOST Compact Full Anechoic Chamber (7x3x3 m)	NA	NA	Mar. 27, 2019	Mar. 26, 2020
Software	RS_V7.6	NA	NA	NA

- Note:
1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
 2. The test was performed in RS Room No.1.
 3. The transmit antenna was located at a distance of 2 meters from the EUT.
 4. Tested Date: Apr. 10, 2019.

9.3 Test Arrangement

The test procedure was in accordance with EN/IEC 61000-4-3.

- The testing was performed in a fully anechoic chamber.
- The swept frequency range is from 80 MHz to 1000 MHz and the spot frequencies are 1800, 2600, 3500, 5000 MHz ($\pm 1\%$), with the signal 80% amplitude modulated with a 1kHz sine wave.
- The dwell time of the amplitude modulated carrier was applied in 3 s at each of the frequencies during the scan. The sensitive frequencies (e.g. clock frequencies or frequencies identified by the manufacturer or obtained as outcome of the test) shall be analyzed in addition to the stepped frequencies.
- The field strength level was 3 V/m, 10 V/m.
- The test was performed with the EUT exposed to both vertically and horizontally polarized fields on each of the four sides.




Table-top Equipment

The EUT installed in a representative system as described in section 7 of EN/IEC 61000-4-3 was placed on a non-conductive table 0.8 meters in height. The system under test was connected to the power and signal wire according to relevant installation instructions.

For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

9.4 Supplementary Information

The requirement followed by the client's specification. (Refer to item 7.1)

9.5 Test Results

Input Power	110Vdc	Tested by	Thomas Cheng
Environmental Conditions	24 °C, 62% RH	Test mode	Mode 1

Frequency (MHz)	Polarity	Azimuth(°)	Applied Field Strength		Observation	Performance Criterion
			(V/m)	Modulation		
80 - 1000	V&H	0	3, 10	80% AM (1kHz)	Note	A
		90	3, 10	80% AM (1kHz)	Note	A
		180	3, 10	80% AM (1kHz)	Note	A
		270	3, 10	80% AM (1kHz)	Note	A
1800, 2600, 3500, 5000 MHz (±1 %)	V&H	0	3, 10	80% AM (1kHz)	Note	A
		90	3, 10	80% AM (1kHz)	Note	A
		180	3, 10	80% AM (1kHz)	Note	A
		270	3, 10	80% AM (1kHz)	Note	A

Note: The EUT function was correct during the test.

10 Electrical Fast Transient/Burst Immunity Test (EFT)

10.1 Test Specification

Basic Standard:	EN/IEC 61000-4-4
Test Voltage:	Analogue/digital data port (cable length > 3m): N/A DC network power port (cable length > 3m): $\pm 0.5\text{kV}$, $\pm 1\text{kV}$, $\pm 2\text{kV}$ AC mains power port: N/A
Impulse Repetition Frequency:	100kHz : applicable only to xDSL port 5kHz : others
Impulse Wave Shape :	5/50 ns
Burst Duration:	0.75 ms for 100kHz Repetition Frequency 15 ms for 5kHz Repetition Frequency,
Burst Period:	300 ms
Test Duration:	1 min.

10.2 Test Instruments


Description & Manufacturer	Model No.	Serial No.	Cal. Date	Cal. Due
TESEQ, EFT Simulator	NSG 3060	1572	May 28, 2018	May 27, 2019
TESEQ, CDN	CDN 3083-B100	303	May 28, 2018	May 27, 2019
Haefely, Capacitive Clamp	IP4A	155173	Apr. 25, 2018	Apr. 24, 2019

Note:

1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
2. The test was performed in EMS Room No. 2.
3. Tested Date: Apr. 12, 2019.

10.3 Test Arrangement

- Both positive and negative polarity discharges were applied.
- The distance between any coupling devices and the EUT should be $(0.5 - 0/+0.1)$ m for table-top equipment testing, and (1.0 ± 0.1) m for floor standing equipment.
- The duration time of each test sequential was 1 minute.
- The transient/burst waveform was in accordance with EN/IEC 61000-4-4, 5/50 ns.



NOTE:

- location for supply line coupling
- location for signal lines coupling

For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

10.4 Supplementary Information

The requirement followed by the client's specification. (Refer to item 7.1)

10.5 Test Results

Input Power	110Vdc	Tested by	Josh Lin
Environmental Conditions	22 °C, 76% RH	Test mode	Mode 1~ 4

Input DC power port

Voltage (kV)	Test Point	Polarity (+/-)	Observation	Performance Criterion
0.5, 1, 2	(+)	+/-	Note	A
0.5, 1, 2	(-)	+/-	Note	A
0.5, 1, 2	(+)-(-)	+/-	Note	A

Note: The EUT function was correct during the test.

11 Surge Immunity Test

11.1 Test Specification

Basic Standard:	EN/IEC 61000-4-5
Wave-Shape:	Analogue/digital data ports (direct to outdoor cables*): Port type: unshielded symmetrical 10/700 μ s Open Circuit Voltage 5/320 μ s Short Circuit Current Port type: coaxial or shielded 1.2/50 μ s Open Circuit Voltage 8/20 μ s Short Circuit Current DC network power port (direct to outdoor cables*): 1.2/50 μ s Open Circuit Voltage 8/20 μ s Short Circuit Current AC mains power port: 1.2/50 μ s Open Circuit Voltage 8/20 μ s Short Circuit Current
Test Voltage:	Analogue/digital data ports: Port type: unshielded symmetrical** w/o primary protectors (line to ground): NA with primary protectors (line to ground): NA Port type: coaxial or shielded shield to ground: NA DC network power port: ± 0.5 kV, ± 1 kV, ± 2 kV AC mains power ports: Line to line : NA Line to ground : NA
AC Phase Angle (degree):	90° / 270°
Pulse Repetition Rate:	1 time / 20 sec.
Number of Tests:	5 positive and 5 negative at selected points

* This test is only applicable only to ports, which according to the manufacturer's specification, may connect directly to outdoor cables.

** For ports where primary protection is intended, surges are applied at voltages up to 4 kV with the primary protectors. Otherwise the 1 kV test level is applied without primary protection in place.

11.2 Test Instruments

Description & Manufacturer	Model No.	Serial No.	Cal. Date	Cal. Due
TESEQ, Surge Simulator	NSG 3060	1572	May 28, 2018	May 27, 2019
TESEQ, CDN	CDN 3083-100	1215	May 28, 2018	May 27, 2019
Coupling Decoupling Network	CDN-UTP8	045	Aug. 27, 2018	Aug. 26, 2019
TESEQ Coupling Decoupling Network	CDN HSS-2	41009	May 23, 2018	May 22, 2019
TESEQ Coupling Decoupling Network	CDN 118-T8	40386	Sep. 20, 2018	Sep. 19, 2019
TESEQ CDN for Unshielded Unsymmetrical Signal & Data Lines	CDN117	40144	Sep. 20, 2018	Sep. 19, 2019

Note: 1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
2. The test was performed in EMS Room No. 2.
3. Tested Date: Apr. 12, 2019.

11.3 Test Arrangement

a. AC mains /DC network power ports:

The surge is to be applied to the EUT power supply terminals via the capacitive coupling network. Decoupling networks are required in order to avoid possible adverse effects on equipment not under test that may be powered by the same lines, and to provide sufficient decoupling impedance to the surge wave. The power cord between the EUT and the coupling/decoupling networks shall be 2 meters in length (or shorter).

For double-insulated products without PE or external earth connections, the test shall be done in a similar way as for grounded products but without adding any additional external grounded connections. If there are no other possible connections to earth, line-to-ground tests may be omitted.

b. Analogue/digital data ports,

- Port type: unshielded symmetrical (line to ground)

The surge is applied to the lines via the capacitive coupling. The coupling / decoupling networks shall not influence the specified functional conditions of the EUT. The interconnection line between the EUT and the coupling/decoupling networks shall be 2 meters in length.

- Port type: coaxial or shielded (shield to ground)

The surge is applied to the lines via gas arrestors coupling. Test levels below the ignition point of the coupling arrestor cannot be specified. The interconnection line between the EUT and the coupling/decoupling networks shall be 2 meters in length.

- High speed communications lines

Prior to the test, the correct operation of the port shall be verified; the external connection shall then be removed and the surge applied directly to the port's terminals with no coupling /decoupling network. After the surge, the correct operation of the port shall again be verified.

- Shielded lines:

- Direct application,

The EUT is isolated from ground and the surge is applied to its metallic enclosure; the termination (or auxiliary equipment) at the port(s) under test is grounded. This test applies to equipment with single or multiple shielded cables.

Rules for application of the surge to shielded lines:

a) Shields grounded at both ends

- The surge injection on the shield.


b) Shields grounded at one end

- If in the installation the shield is connected only at the auxiliary equipment, test shall be done in that configuration but with the generator still connected to the EUT side. If cable lengths allow, the cables shall be on insulated supports 0,1 m above the ground plane or cable tray.

For products which do not have metallic enclosures, the surge is applied directly to the shielded cable.

- Alternative coupling method for testing single cables in a multi-shield configuration,

Surges are applied in close proximity to the interconnection cable under test by a wire. The length of the cable between the port(s) under test and the device attached to the other end of the cable shall be the lesser of: the maximum length permitted by the EUT's specification, or 20 m. Where the length exceeds 1 m, excess lengths of cables shall be bundled at the approximate centre of the cables with the bundles 30 cm to 40 cm in length.



For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

11.4 Supplementary Information

The requirement followed by the client's specification. (Refer to item 7.1)

11.5 Test Results

Input Power	110Vdc	Tested by	Josh Lin
Environmental Conditions	22 °C, 76% RH	Test mode	Mode 1 ~ 4

Input DC power port

Voltage (kV)	Test Point	Polarity (+/-)	Observation	Performance Criterion
0.5, 1, 2	(+)-(-)	+/-	Note	A

Note: The EUT function was correct during the test.

12 Immunity to Conducted Disturbances Induced by RF Fields (CS)

12.1 Test Specification

Basic Standard:	EN/IEC 61000-4-6
Frequency Range:	0.15 MHz - 80 MHz
Voltage Level:	0.15 MHz - 80 MHz: 10V 0.15 MHz - 10 MHz: 3V 10 MHz - 30 MHz: 3-1 V 30 MHz - 80 MHz: 1V
Modulation:	1kHz Sine Wave, 80%, AM Modulation
Frequency Step:	1 % of preceding frequency value
Dwell Time	3 seconds

12.2 Test Instruments

Description & Manufacturer	Model No.	Serial No.	Cal. Date	Cal. Due
ROHDE & SCHWARZ Signal Generator	SML03	101801	Jan. 14, 2019	Jan. 13, 2020
Digital Sweep Function Generator	8120	984801	NA	NA
AR Power Amplifier	75A250AM1	306331	NA	NA
FCC Coupling Decoupling Network	FCC-801-M2-16A	01047	Jun. 20, 2018	Jun. 19, 2019
FISCHER CUSTOM COMMUNICATIONS EM Injection Clamp	F-203I-23mm	455	NA	NA
FISCHER CUSTOM COMMUNICATIONS Current Injection Clamp	F-120-9A	361	Jul. 24, 2018	Jul. 23, 2019
B&K Ear Simulator	4185	2553594	NA	NA
EM TEST Coupling Decoupling Network	CDN M1/32A	306508	Jun. 20, 2018	Jun. 19, 2019
TESEQ Coupling Decoupling Network	CDN T800	34428	Jun. 20, 2018	Jun. 19, 2019
TESEQ Coupling Decoupling Network	CDN T800	29459	Jun. 20, 2018	Jun. 19, 2019
FCC Coupling Decoupling Network	FCC-801-T4	02031	Jun. 20, 2018	Jun. 19, 2019
EM TEST Coupling Decoupling Network	CDN T2	306509	Jun. 20, 2018	Jun. 19, 2019
R&S Power Sensor	NRV-Z5	837878/039	Nov. 10, 2018	Nov. 9, 2019
R&S Power Meter	NRVD	837794/040	Nov. 10, 2018	Nov. 9, 2019
TESEQ Coupling Decoupling Network	CDN M232	37702	Jun. 20, 2018	Jun. 19, 2019
TESEQ Coupling Decoupling Network	CDN M332	41258	Jun. 20, 2018	Jun. 19, 2019
TESEQ Coupling Decoupling Network	CDN M332	41256	Jun. 20, 2018	Jun. 19, 2019
TESEQ Coupling Decoupling Network	CDN T400A	28569	Jun. 20, 2018	Jun. 19, 2019
TESEQ Coupling Decoupling Network	CDN T8-10	40376	Jun. 20, 2018	Jun. 19, 2019
TESEQ Coupling Decoupling Network	ISN ST08	41212	Jun. 20, 2018	Jun. 19, 2019
FCC Coupling Decoupling Network	FCC-801-M5-50A	100018	Jan. 21, 2019	Jan. 20, 2020
Software	CS_V7.4.2	NA	NA	NA

Note: 1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
2. The test was performed in CS Room No. 1.
3. Tested Date: Apr. 10, 2019.

12.4 Supplementary Information

The requirement followed by the client's specification. (Refer to item 7.1)

12.5 Test Results

Input Power	110Vdc	Tested by	Thomas Cheng
Environmental Conditions	23 °C, 66% RH	Test mode	Mode 1

Frequency (MHz)	Level (Vrms)	Tested Line	Injection Method	Return Path	Observation	Performance Criterion
0.15 – 80	10	DC power	CDN-M2	N/A	Note	A
0.15 – 10	3	DC power	CDN-M2	N/A	Note	A
10 – 30	3 – 1	DC power	CDN-M2	N/A	Note	A
30 – 80	1	DC power	CDN-M2	N/A	Note	A

Note: The EUT function was correct during the test.

13 Power Frequency Magnetic Field Immunity Test

13.1 Test Specification

Basic Standard:	EN/IEC 61000-4-8
Frequency Range:	50Hz
Field Strength:	1A/m, 100A/m, 1000A/m
Observation Time:	1 minute for Field Strength 1A/m, 100A/m 1 second for Field Strength 1000A/m
Inductance Coil:	Rectangular type, 1 m x 1 m

13.2 Test Instruments

For Field Strength: 1A/m

Description & Manufacturer	Model No.	Serial No.	Cal. Date	Cal. Due
HAEFELY Magnetic Field Tester	MAG 100	083794-06	NA	NA
COMBINOVA Magnetic Field Meter	MFM10	224	Apr. 24, 2018	Apr. 23, 2019

- Note:
1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
 2. The test was performed in EMS Room No. 1
 3. Tested Date: Apr. 10, 2019.


For Field Strength: 100A/m, 1000A/m

Description & Manufacturer	Model no.	Serial No.	Calibrated DATE	Calibrated Until
Triaxial Elf Magnetic Field Meter BELL	4090	NA	Apr. 10, 2019	Apr. 09, 2020
Power frequency magnetic filed coil 3ctest	TCX30	EC1281401	Apr. 25, 2019	Apr. 24, 2020
Power frequency magnetic filed generator 3ctest	PFMF-1200G	EC0111401	Apr. 25, 2019	Apr. 24, 2020

- Notes:
1. The calibration interval of the above test instruments are 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
 2. The test was performed in EMS-1 room. (TAF No.: 2022)
 3. Tested Date: Apr. 25, 2019.

13.3 Test Arrangement

- The equipment is configured and connected to satisfy its functional requirements.
- The power supply, input and output circuits shall be connected to the sources of power supply, control and signal.
- The cables supplied or recommended by the equipment manufacturer shall be used. 1 meter of all cables used shall be exposed to the magnetic field.



TABLETOP EQUIPMENT

The equipment shall be subjected to the test magnetic field by using the induction coil of standard dimension (1 m x 1 m). The induction coil shall then be rotated by 90 degrees in order to expose the EUT to the test field with different orientations.

For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

13.4 Supplementary Information

The requirement followed by the client's specification. (Refer to item 7.1)

13.5 Test Results

Input Power	110Vdc	Tested by	Josh Lin
Environmental Conditions	23 °C, 78% RH	Test mode	Mode 1

Application	Frequency (Hz)	Test Duration	Field Strength (A/m)	Observation	Performance Criterion
X - Axis	50	1 min.	1	Note	A
Y - Axis	50	1 min.	1	Note	A
Z - Axis	50	1 min.	1	Note	A

Note: The EUT function was correct during the test.

Input Power	110Vdc	Tested by	Yuhan Lin
Environmental Conditions	24 °C, 60% RH	Test mode	Mode 1

Application	Frequency (Hz)	Test Duration	Field Strength (A/m)	Observation	Performance Criterion
X - Axis	50	1 min.	100	Note	A
Y - Axis	50	1 min.	100	Note	A
Z - Axis	50	1 min.	100	Note	A
X - Axis	50	1 sec.	1000	Note	A
Y - Axis	50	1 sec.	1000	Note	A
Z - Axis	50	1 sec.	1000	Note	A

Note: The EUT function was correct during the test.

* The test, calibration and test results are compliance with the TAF No.: 2022.

14 Pictures of Test Arrangements


14.1 Conducted Emission from the Mains Power Port




14.2 Radiated Emission at Frequencies up to 1GHz



14.3 Electrostatic Discharge Immunity Test (ESD)



14.4 Radio-frequency, Electromagnetic Field Immunity Test (RS)



14.5 Electrical Fast Transient/Burst Immunity Test (EFT)



14.6 Surge Immunity Test



14.7 Conducted Disturbances Induced by RF Fields (CS)



14.8 Power Frequency Magnetic Field Immunity Test (PFMF)

For Field Strength: 1A/m



For Field Strength: 100A/m, 1000A/m



Appendix – Information of the Testing Laboratories

We, Bureau Veritas Consumer Products Services (H.K.) Ltd., Taoyuan Branch, were founded in 1988 to provide our best service in EMC, Radio, Telecom and Safety consultation. Our laboratories are accredited and approved according to ISO/IEC 17025.

If you have any comments, please feel free to contact us at the following:

Lin Kou EMC/RF Lab

Tel: 886-2-26052180

Fax: 886-2-26051924

Hsin Chu EMC/RF/Telecom Lab

Tel: 886-3-6668565

Fax: 886-3-6668323

Hwa Ya EMC/RF/Safety Lab

Tel: 886-3-3183232

Fax: 886-3-3270892

Email: service.adt@tw.bureauveritas.com

Web Site: www.bureauveritas-adt.com

The address and road map of all our labs can be found in our web site also.

--- END ---